marathon®

General Purpose Motors

Model No: 112MTFC6536
Catalog No: R325A

General Purpose Motor, 5.50 & 4 HP, 3 Ph, 60 & 50 Hz, 230/460 & 200/400 V, 1800 RPM, 112M Frame, TEFC

©2026 Marathon, All Rights Reserved.

marathon®

Product Information Packet: Model No: 112MTFC6536, Catalog No: R325A General Purpose Motor, 5.50 & 4 HP, 3 Ph, 60 & 50 Hz, 230/460 & 200/400 V, 1800 RPM, 112M Frame, TEFC

Nameplate Specifications

Phase	**3**	Output HP	**5.50 & 4 Hp**
Output KW	**4.1 & 3.0 kW**	Voltage	**230/460 & 200/400 V**
Speed	**1755 & 1460 r/min**	Synchronous RPM	**1800 & 1500 r/min**
Service Factor	**1.15 & 1.15**	Frame	**112M**
Enclosure	**Totally Enclosed Fan Cooled**	Thermal Protection	**No Protection**
Efficiency	**89.5 & 88.5 %**	Ambient Temperature	**40 °C**
Frequency	**60 & 50 Hz**	Current	**14/7 & 12.6/6.3 A**
Power Factor	**81**	Duty	**Continuous**
Insulation Class	**F**	Design Code	**B**
KVA Code	**J**	Drive End Bearing Size	**6206**
Opp Drive End Bearing Size	**6205**	UL	**Recognized**
CSA	**Y**	CE	**Y**
IP Code	**55**	Number of Speeds	**1**


Technical Specifications

Electrical Type	**Squirrel Cage Inverter Rated**	Starting Method	**Line Or Inverter**
Poles	**4**	Rotation	**Reversible**
Resistance Main	**.754 O**	Mounting	**Rigid Base**
Motor Orientation	**Horizontal**	Drive End Bearing	**Ball**
Opp Drive End Bearing	**Ball**	Frame Material	**Cast Iron**
Shaft Type	**IEC**	Overall Length	**18.42 in**
Shaft Diameter	**1 1/9 in**	Shaft Extension	**2.36 in**
Assembly/Box Mounting	**F3**	Inverter Load	**Constant 20:1**

Drawings

Connection Drawing	**005010.01**	Outline Drawing	**SS622368-193307**

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created: 16/10/2026



PART NO.	FRAME	L
193306.60	C20-112M-2	410
193307.60	C20-112M1-4	
193302.60	C20-112M1-6	468

DRAWING NOT TO SCALE

DRAWING REVISION: G	REVISION BY: SV	REV DATE/© DATE: 09/07/2026
REQUEST NUMBER: CR-0027601	APPROVED BY: RMS	DATE: 09/07/2026
REQUEST NUMBER DESCRIPTION: DRAWING TITLE BLOCK UPDATED		

COPYRIGHT (PER REVISION DATE) MARATHON ELECTRIC, LLC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF MARATHON ELECTRIC, LLC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.

TOLERANCES (EXCEPT AS NOTED):

DEC.	INCH	mm	ANGLE
.X	±0.1	[±3]	±7' 30"
.XX	±0.03	[±0.8]	
.XXX	±0.005	[±0.13]	
.XXXX	±0.0005	[±0.013]	

REMOVE BURRS & BREAK SHARP EDGES: .003/.015 [.08/.38] X 45°
CORNER FILLETS: R.02 [.5]
MACHINED SURFACES: 200 INCH / 5.1 mm
mm DIMENSIONS IN [BRACKETS] ARE FOR REFERENCE ONLY

DRAWN BY: MOL	marathon™
DATE: 04-12-2012	
APPROVED BY: SB	DESCRIPTION: OUTLINE IEC 112M - 2,4,6 - TEFC
DATE: 04-12-2012	
REFERENCE	MATERIAL / PROCESS/FINISH
THIRD ANGLE PROJECTION	SIZE: B / DRAWING NUMBER: SS622368 / SHEET: 1 OF 1

Uncontrolled Copy

Data Sheet

Date: 1/3/2019
Customer:
Attention:
Submitted by: FAREEDA DUDEKULA

marathon® electric

112MTFC6536

Submittal


Data @ 460 V

Motor Load Data

Load	0%	25%	50%	75%	100%	115%	125%	LR	
Current (Amps)	3.1	3.5	4.5	5.6	7.0	7.9	8.8	51.0	
Torque (ft-lb)	0.00	4.0	8.2	12.3	16.5	19.2	20.8	34.5	
RPM	1800	1790	1780	1765	1755	1,745	1738	0	
Efficiency (%)		86.5	89.5	90.2	89.5	88.5	87.5		
P.F. (%)	5.5	44.0	65.0	76.0	81.0	83.0	84.0	43.0	

Motor Speed Data

	LR	Pull-Up	BD	Rated	Idle
Speed (RPM)	0	900	1550	1755	1800
Current (Amps)	51.0	48.0	30.5	7.0	3.1
Torque (ft-lb)	34.5	30.0	51.0	16.5	0.00




Information Block

HP	5.5	
Sync. RPM	1800	
Frame	112	
Enclosure	TEFC	
Construction	TFS	
Voltage	230/460#200/400	V
Frequency	60	Hz
Design	B	
LR Code letter	J	
Service Factor	1.15	
Temp Rise @ FL	55	° C
Duty	CONT	
Ambient	40	° C
Elevation	3300	feet
Rotor/Shaft wk²	0.00	Lb-Ft²
Ref Wdg	T08704015 NONE	
Sound Pressure @ 1M	65	dBA
VFD Rating	CONSTANT 20:1	
Outline Dwg	SS622368	
Conn. Diag	005010.01	
Additional Specifications:		
0		
0		

EQUIV CKT (OHMS / PHASE)

R1	R2	X1	X2	Xm
0.0000	0.0000	0.0000	0.0000	0.0000

Speed -Torque Curve



Uncontrolled Copy

CERTIFICATION DATA SHEET

Model#:	112MTFC6536 A	**WINDING#:**	T08704015 NONE 3
CONN. DIAGRAM:	005010.01	**ASSEMBLY:**	F3
OUTLINE:	SS622368		

TYPICAL MOTOR PERFORMANCE DATA

HP	KW	SYNC. RPM	F.L. RPM	FRAME	ENCLOSURE	KVA CODE	DESIGN
5 1/2&4	4.1&2.98	1800	1755&1460	112M	TEFC	J	B

PH	Hz	VOLTS	FL AMPS	START TYPE	DUTY	INSL	S.F	AMB°C	ELEVATION
3	60/50	230/460#200/400	14/7&12.6/6.3	LINE OR INVERTER	CONTINUOUS	F2	1.15/1.15	40	3300

FULL LOAD EFF: 89.5&88.5	3/4 LOAD EFF: 90.2	1/2 LOAD EFF: 89.5	GTD. EFF	ELEC. TYPE	NO LOAD AMPS
FULL LOAD PF: 81&77	3/4 LOAD PF: 76	1/2 LOAD PF: 65	87.5	SQ CAGE INV RATED	6.2 / 3.1

F.L. TORQUE	LOCKED ROTOR AMPS	L.R. TORQUE	B.D. TORQUE	F.L. RISE°C
16.5 LB-FT	102 / 51	34.5 LB-FT 210	51 LB-FT 310	55

SOUND PRESSURE @ 3 FT.	SOUND POWER	ROTOR WK^2	MAX. WK^2	SAFE STALL TIME	STARTS /HOUR	APPROX. MOTOR WGT
65 dBA	75 dBA	- LB-FT^2	- LB-FT^2	20 SEC.	2	- LBS.

*** SUPPLEMENTAL INFORMATION ***

DE BRACKET TYPE	ODE BRACKET TYPE	MOUNT TYPE	ORIENTATION	SEVERE DUTY	HAZARDOUS LOCATION	DRIP COVER	SCREENS	PAINT
STANDARD	STANDARD	RIGID	HORIZONTAL	TRUE	NONE	FALSE	NONE	BLUE (ENAMEL)

BEARINGS		GREASE	SHAFT TYPE	SPECIAL DE	SPECIAL ODE	SHAFT MATERIAL	FRAME MATERIAL
DE	OPE						
BALL 6206	BALL 6205	POLYREX EM	STANDARD IEC	NONE	NONE	1045 HOT ROLLED (C-204)	CAST IRON

THERMO-PROTECTORS				THERMISTORS	CONTROL	SPACE /n HEATERS
THERMOSTATS	PROTECTORS	WDG RTDs	BRG RTDs			
NONE	NOT	NONE	NONE	NONE	FALSE	NONE VOLTS

If Inverter equals NONE, contact factory for further information

INVERTER TORQUE: CONSTANT 20:1
INV. HP SPEED RANGE: 1.5 X BASE SPEED

ENCODER: NONE
NONE NONE
NONE NONE PPR

BRAKE: NONE NONE
NONE P/N NONE
NONE NONE
NONE FT-LB NONE V NONE Hz

*
N
O
T
E
S
*

DATE: 06/22/2017 04:31:06 AM
FORM 3531 REV.3 02/07/99
** Subject to change without notice.