

# Safety Data Sheet



## 1. Identification

<b>Name on Label:</b>	Wipe New Ceramic Protection Headlight Restore		
<b>Product Name:</b>	WIPE NEW 6PK HEADLIGHT CLEAR	<b>Revision Date:</b>	3/4/2025
<b>Product Identifier:</b>	397048	<b>Supersedes Date:</b>	New SDS
<b>Recommended Use:</b>	Headlight Protectant		
<b>Supplier:</b>	Rust-Oleum Corporation 11 Hawthorn Parkway Vernon Hills, IL 60061 USA	<b>Manufacturer:</b>	Rust-Oleum Corporation 11 Hawthorn Parkway Vernon Hills, IL 60061 USA
<b>Preparer:</b>	Regulatory Department		
<b>Emergency Telephone:</b>	24 Hour Hotline: 847-367-7700		

## 2. Hazard Identification

### Classification

#### Symbol(s) of Product



#### Signal Word

Danger

#### Possible Hazards

95% of the mixture consists of ingredient(s) of unknown acute toxicity.

#### GHS Hazard Statements

Flammable Liquid, category 2	H225	Highly flammable liquid and vapour.
Water Reacting Substance, category 3	H261	In contact with water releases flammable gases.
Acute Toxicity, Oral and Inhalation, category 4	H302+H332	Harmful if swallowed or if inhaled.
Skin Corrosion, category 1B	H314	Causes severe skin burns and eye damage.
Skin Sensitizer, category 1	H317	May cause an allergic skin reaction.
STOT, Single Exposure, category 3, NE	H336	May cause drowsiness or dizziness.
Reproductive Toxicity, category 2	H361	Suspected of damaging fertility or the unborn child.

#### GHS Label Precautionary Statements

P201	Obtain special instructions before use.
P210	Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P223	Do not allow contact with water.
P260	Do not breathe dust, fumes, gas, mist, vapours, or spray.
P264	Wash thoroughly after handling.

P271	Use only outdoors or in a well-ventilated area.
P272	Contaminated work clothing should not be allowed out of the workplace.
P280	Wear protective gloves, protective clothing, eye protection, and face protection.
P301+P330+P331	IF SWALLOWED: rinse mouth. Do NOT induce vomiting.
P302+P352	IF ON SKIN: Wash with plenty of soap and water.
P303+P361+P353	IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water [or shower].
P304+P340	IF INHALED: Remove person to fresh air and keep comfortable for breathing.
P305+P351+P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P308+P313	IF exposed or concerned: Get medical advice.
P310	If exposed immediately call a POISON CENTER or doctor/physician.
P321	Specific treatment (see notice on this label).
P333+P313	If skin irritation or rash occurs: Get medical advice.
P370+P378	In case of fire: Extinguish using suitable extinguishing media.
P403+P233	Store in a well-ventilated place. Keep container tightly closed.
P403+P235	Store in a well-ventilated place. Keep cool.
P405	Store locked up.
P501	Dispose of contents and container in accordance with local, regional and national regulations.

**GHS SDS Precautionary Statements**

P240	Ground and bond container and receiving equipment.
P241	Use explosion-proof electrical, ventilating, lighting, or pouring equipment.
P242	Use non-sparking tools.
P243	Take action to prevent static discharges.
P270	Do not eat, drink or smoke when using this product.
P363	Wash contaminated clothing before reuse.

**3. Composition / Information on Ingredients****HAZARDOUS SUBSTANCES**

<u>Chemical Name</u>	<u>CAS-No.</u>	<u>Wt.% Range</u>	<u>GHS Symbols</u>	<u>GHS Statements</u>
Methyl Acetate	79-20-9	45-70	GHS02-GHS07	H225-319-336
Polysilazane Polymer	PROPRIETARY	15-40	GHS05-GHS06-GHS07	H301-314-317
Octamethylcyclotetrasiloxane	556-67-2	5.0-10	GHS08	H361
3-Aminopropyltriethoxysilane	919-30-2	1.0-5.0	GHS05-GHS07	H302+H332-314
Methanol	67-56-1	0.5-1.5	GHS02-GHS06-GHS08	H225-331-370

Actual concentrations of ingredients are withheld as trade secret.

**4. First Aid Measures**

**First Aid - Eye Contact:** Immediately flush eyes with plenty of water for at least 15 minutes holding eyelids open. Get medical attention. Do NOT allow rubbing of eyes or keeping eyes closed. Remove contact lenses, if present and easy to do. Continue rinsing.

**First Aid - Skin Contact:** Immediately flush skin with plenty of water for at least 15 minutes while removing clothing. Get medical attention immediately. Wash clothing separately before reuse. Wash contaminated clothing and decontaminate footwear before reuse.

**First Aid - Inhalation:** Remove to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Get immediate medical attention. Do NOT use mouth-to-mouth resuscitation. If you experience difficulty in breathing, leave the area to obtain fresh air. If continued difficulty is experienced, get medical assistance immediately.

**First Aid - Ingestion:** If swallowed, do not induce vomiting. If victim is conscious and alert, give 2 to 4 cupfuls of water or milk. Call a physician or poison control center immediately. Never give anything by mouth to an unconscious person. Treat symptomatically and supportively. Do not induce vomiting unless advised by a physician. Call nearest Poison Control Center or Physician immediately.

## 5. Fire-Fighting Measures

**EXTINGUISHING MEDIA:** Dry Chemical, Dry Sand

**Unusual Fire and Explosion Hazards:** Closed containers may explode when exposed to extreme heat. Vapors can travel to a source of ignition and flash back. Keep containers tightly closed. DO NOT apply to hot surfaces. Isolate from heat, electrical equipment, sparks and open flame. May not get in touch with water. In contact with water product releases flammable gas and may release toxic, irritating and/or corrosive gases.

**Special Fire Fighting Procedures:** Evacuate area and fight fire from a safe distance. Containers can rupture and release highly toxic material if exposed to heat. Avoid any extinguishing agents that contain water or moisture. Use water spray to keep fire-exposed containers cool. Containers may explode when heated.

**Special Fire and Explosion Hazard (Combustible Dust):** Not a combustible dust.

## 6. Accidental Release Measures

**Steps to Be Taken If Material Is Released or Spilled:** Evacuate the area, remove all sources of ignition and ventilate well. Contain spilled liquid with sand or earth. DO NOT use combustible materials such as sawdust. Eliminate all ignition sources; use explosion-proof equipment. Place material in a container and dispose of according to local, provincial, state and federal regulations. Remove all sources of ignition, ventilate area and remove with inert absorbent and non-sparking tools. Do not flush into surface water or sanitary sewer system. Risk of explosion. Local authorities should be advised if significant spillages cannot be contained.

## 7. Handling and Storage

**Handling:** Wash thoroughly after handling. Wash hands before eating. Remove contaminated clothing and launder before reuse. Use only with adequate ventilation. Follow all SDS and label precautions even after container is emptied because it may retain product residues. Ground and bond containers when transferring material from one vessel to another. Vapor can be ignited by static discharge. Use spark-proof tools and explosion-proof equipment. Avoid breathing fumes, vapors, or mist. Avoid prolonged or repeated contact with skin. Avoid contact with eyes, skin and clothing.

**Storage:** Store in a dry, well ventilated place. Keep container tightly closed when not in use. Never allow product to contact water during storage. Keep containers tightly closed. Isolate from heat, electrical equipment, sparks and open flame. Keep away from heat, sparks, flame and sources of ignition. Avoid excess heat.

**Advice on Safe Handling of Combustible Dust:** No Information

## 8. Exposure Controls / Personal Protection

Chemical Name	CAS-No.	Weight % Less Than	ACGIH TLV- TWA	ACGIH TLV- STEL	OSHA PEL-TWA	OSHA PEL- CEILING
Methyl Acetate	79-20-9	55.0	200 ppm	250 ppm	200 ppm	N.E.
Polysilazane Polymer	PROPRIETARY	35.0	N.E.	N.E.	N.E.	N.E.
Octamethylcyclotetrasiloxane	556-67-2	10.0	N.E.	N.E.	N.E.	N.E.
3-Aminopropyltriethoxysilane	919-30-2	5.0	N.E.	N.E.	N.E.	N.E.
Methanol	67-56-1	5.0	200 ppm	250 ppm	200 ppm	N.E.

### PERSONAL PROTECTION

**Engineering Controls:** Use process enclosures, local exhaust ventilation, or other engineering controls to control airborne levels below recommended exposure limits. Prevent build-up of vapors by opening all doors and windows to achieve cross-ventilation.

**Respiratory Protection:** A respiratory protection program that meets OSHA 1910.134 and ANSI Z88.2 (U.S.) and/or SOR/86-304 Part XII 12.13 and CSA Standard Z180.1 (Canada) requirements must be followed whenever workplace conditions warrant a respirator's use.

**Skin Protection:** Use impervious gloves to prevent skin contact and absorption of this material through the skin.

**Eye Protection:** Use safety eyewear designed to protect against splash of liquids.

**Other Protective Equipment:** Refer to safety supervisor or industrial hygienist for further guidance regarding types of personal protective equipment and their applications.

**Hygienic Practices:** Wash thoroughly with soap and water before eating, drinking or smoking. Remove contaminated clothing immediately and launder before reuse.

**Engineering Measures for Combustible Dust:** No Information

## 9. Physical and Chemical Properties

Physical State	Liquid Bearing Solid Substrate	Decomposition Temperature, °C	N.D.
Color	Clear	pH	N.A.
Odor	Solvent Like	Kinematic Viscosity	N.D.
Odor Threshold	Threshold N.E.	Solubility in Water	Water Reactive
Freezing Point / Melting Point, °C	N.D.	Partition Coefficient, n-octanol/water	N.D.
Boiling Range, °C	56 - 537	Vapor Pressure	N.D.
Flammability	Supports Combustion	Evaporation Rate	Slower than Ether
Lower Explosion Limit, vol%	0.8	Specific Gravity	0.962
Upper Explosion Limit, vol%	16.0	Vapor Density	Heavier than Air
Flash Point, °C	13	Particle Characteristics	N.A.
Auto-Ignition Temperature, °C	N.D.		

(See "Other information" Section for abbreviation legend)

## 10. Stability and Reactivity

**Conditions to Avoid:** Avoid temperatures above 120°F (49°C). Avoid all possible sources of ignition. Avoid contact with metals. Avoid excess heat. Avoid contact with moisture.

**Incompatibility:** Incompatible with strong oxidizing agents, strong acids and strong alkalies. Avoid contact with water. Avoid contact with alcohols. Product slowly corrodes copper, aluminum, zinc, and galvanized surfaces.

**Hazardous Decomposition:** When heated to decomposition, it emits acrid smoke and irritating fumes. Emits hydrogen, ammonia, and ammonia compounds during curing.

**Hazardous Polymerization:** Will not occur under normal conditions.

**Stability:** Sensitive to moisture. The material can slowly hydrolyze in the presence of water to form hydrogen and ammonia gases and condensed siloxane.

## 11. Toxicological Information

**Effects of Overexposure - Eye Contact:** Causes eye burns. Irritating, and may injure eye tissue if not removed promptly. High vapor concentrations can irritate eyes, nose and respiratory passages.

**Effects of Overexposure - Skin Contact:** Prolonged or repeated skin contact may cause irritation. Substance is corrosive. Causes severe skin burns. Causes skin irritation. Allergic reactions are possible. May cause skin sensitization, an allergic reaction, which becomes evident upon re-exposure to this material. Frequent or prolonged contact may irritate the skin and cause a skin rash (dermatitis). Severely irritating; may cause permanent skin damage.

**Effects of Overexposure - Inhalation:** High gas, vapor, mist or dust concentrations may be harmful if inhaled. Avoid breathing fumes, spray, vapors, or mist. High vapor concentrations are irritating to the eyes, nose, throat and lungs.

**Effects of Overexposure - Ingestion:** Corrosive and may cause severe and permanent damage to mouth, throat and stomach. Harmful if swallowed. Poison, may be fatal or cause blindness if swallowed.

**Effects of Overexposure - Chronic Hazards:** May damage fertility or the unborn child. High concentrations may lead to central nervous system effects (drowsiness, dizziness, nausea, headaches, paralysis, and blurred vision) and/or damage. Reports have associated repeated and prolonged occupational overexposure to solvents with permanent brain and nervous system damage. Prolonged or repeated skin contact may cause dermatitis. May cause genetic defects.

**PRIMARY ROUTE(S) OF ENTRY:** Eye Contact, Ingestion, Inhalation, Skin Absorption, Skin Contact

### ACUTE TOXICITY VALUES

The acute effects of this product have not been tested. Data on individual components are tabulated below:

CAS-No.	Chemical Name	Oral LD50	Dermal LD50	Vapor LC50
79-20-9	Methyl Acetate	6482 mg/kg Rat	5000 mg/kg Rabbit	49.2 - 98.4 mg/L Rat

PROPRIETA RY	Polysilazane Polymer	300 mg/kg rat	N.E.	N.E.
556-67-2	Octamethylcyclotetrasiloxane	4800 mg/kg Rat	> 2400 mg/kg Rat	36 mg/L Rat
919-30-2	3-Aminopropyltriethoxysilane	1780 mg/kg Rat	4290 mg/kg Rabbit	N.E.
67-56-1	Methanol	6200 mg/kg Rat	15840 mg/kg Rabbit	N.E.

N.E. - Not Established

## 12. Ecological Information

**Ecological Information:** No ecotoxicity data was found for this product.

## 13. Disposal Considerations

**Disposal:** Do not incinerate closed containers. Dispose of material in accordance to local, state, and federal regulations and ordinances. RCRA Hazardous Waste: This material, when discarded or disposed of, could be a hazardous waste according to federal regulations (40 CFR 261) due to the characteristic of corrosivity (D002). Check state and local regulations for disposal requirements. Chemical additions, processing or otherwise altering this material may make the waste management information presented in this SDS incomplete, inaccurate, or otherwise inappropriate.

## 14. Transport Information

	<u>Domestic (USDOT)</u>	<u>International (IMDG)</u>	<u>Air (IATA)</u>	<u>TDG (Canada)</u>
<b>UN Number:</b>	N.A.	3131	3131	N.A.
<b>Proper Shipping Name:</b>	Water-reactive solid, corrosive in limited quantity	Water-reactive solid, corrosive, n.o.s. (Organic polysilazane compound)	Water-reactive solid, corrosive, n.o.s. (Organic polysilazane compound)	Water-reactive solid, corrosive in limited quantity
<b>Hazard Class:</b>	N.A.	4.3 (8)	4.3 (8)	N.A.
<b>Packing Group:</b>	N.A.	II	II	N.A.
<b>Limited Quantity:</b>	Yes	No	Yes	Yes

## 15. Regulatory Information

### U.S. Federal Regulations:

#### CERCLA - SARA Hazard Category

This product has been reviewed according to the EPA 'Hazard Categories' promulgated under Sections 311 and 312 of the Superfund Amendment and Reauthorization Act of 1986 (SARA Title III) and is considered, under applicable definitions, to meet the following categories:

Flammable (gases, aerosols, liquids, or solids), In contact with water emits flammable gas, Acute Toxicity (any route of exposure), Reproductive toxicity, Skin Corrosion or Irritation, Respiratory or Skin Sensitization, Specific target organ toxicity (single or repeated exposure)

#### SARA Section 313

This product contains the following substances subject to the reporting requirements of Section 313 of Title III of the Superfund Amendment and Reauthorization Act of 1986 and 40 CFR part 372:

<u>Chemical Name</u>	<u>CAS-No.</u>
Methanol	67-56-1

#### Toxic Substances Control Act

This product contains the following chemical substances subject to the reporting requirements of TSCA 12(b) if exported from the United States:

No TSCA 12(b) components exist in this product.

### U.S. State Regulations:

**California Proposition 65****WARNING:**Reproductive Harm - [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).**16. Other Information****HMIS RATINGS**

Health: 2\*    Flammability: 3    Physical Hazard: 0    Personal Protection: X

**NFPA RATINGS**

Health: 2    Flammability: 3    Instability: 0

Volatile Organic Compounds: 1 g/L

SDS REVISION DATE: 3/4/2025

**REASON FOR REVISION:****Legend:**    N.A. - Not Applicable, N.D. - Not Determined, N.E. - Not Established

Rust-Oleum Corporation believes, to the best of its knowledge, information and belief, the information contained herein to be accurate and reliable as of the date of this safety data sheet. However, because the conditions of handling, use, and storage of these materials are beyond our control, we assume no responsibility or liability for personal injury or property damage incurred by the use of these materials. Rust-Oleum Corporation makes no warranty, expressed or implied, regarding the accuracy or reliability of the data or results obtained from their use. All materials may present unknown hazards and should be used with caution. The information and recommendations in this material safety data sheet are offered for the users' consideration and examination. It is the responsibility of the user to determine the final suitability of this information and to comply with all applicable international, federal, state, and local laws and regulations.