

Master MH-32-TTC 32,000 BTU LP Double Tank Top Heater




- Heat up well-ventilated construction sites, workshops, farms, or bring camping, hunting, tailgating, and ice fishing
- Made of rugged steel for years of use
- Variable BTU to efficiently heat-up well-ventilated spaces
- No electricity required
- 1-year limited warranty

**Propane tank not included*

Product Description

You work hard. You play hard. Why would you expect anything less from the equipment you choose? The Master[®] propane tank top space heater is perfect for job sites, farms and emergencies (no electricity required!), but it also warms you up for camping, fishing, tailgating and hunting. Mounted directly to the top of a 20-pound propane tank, this durable heater has a small footprint and is ultra-portable. It uses radiant-style heat, features match-light ignition, and it's wind resistant. **Master—built for power.**



Key Specs

Model Number	MH-32-TTC	Max. Operating Hours	17.2 / 15.4 / 13.4
Brand	Master	Heating Area (sq. ft.)	620 / 700 / 800
Warranty	1-year limited warranty	Volts	120
Max. BTU	32,000	Net Weight (lb.)	5
Fuel Type	20 lb. Propane <i>(not included)</i>	Dimensions (L x W x H) (in.)	17 x 6x 15.5
Fuel Consumption (lb/hr)	1.16 / 1.30 / 1.49	Heater Type	Radiant

Master is a registered trademark of Pinnacle Climate Technologies, Inc.