

Garant**Circular mill, Carbide, Type: 18****Order data**

Order number	217252 18
GTIN	4045197216526
Item class	21Q

Description**Note:**

The actual groove depth $S_{\max}$ is calculated as follows: $(D-d_1) / 2$.

Technical description

maximum cutting depth $S_{\max}$	6.5 mm
Overall length L_{tot}	71.5 mm
Shank type	Weldon
Internal $\varnothing d_1$	9 mm
Overhang L_1	25 mm
Shank $\varnothing D_s$ h6	12 mm
Set of insert screws	219818 (8IP; 1.2 Nm)
smallest hole $\varnothing D$	14 - 22 mm
Shank	DIN 6535 HB
for insert type	P16
Through-coolant	yes
Thread depth	21 mm
Material of milling tool	Carbide
Tool exchange	PowerCard

Type of product

Circular mills

Accessories

Set of insert screws10-piece

219818