

SECTION 1 Identification**1.1. Product identifier**

Product form : Mixture
Trade name : PRIMEGUARD -100 PG RVAF 6/1GAL
Product code : 72710

1.2. Other means of identification

No additional information available

1.3. Recommended use of the chemical and restrictions on use

Use of the substance/mixture : Anti-freezing agents

1.4. Supplier's details

Highline Warren LLC
8700 Trail Lake Drive West
Suite 300
Memphis, TN 38125
USA
T +01 (901) 437-8615
sds@highlinewarren.com

1.5. Emergency phone number

Emergency number : CHEMTREC: +1 (800) 424-9300 International: +01 (703) 527-3887
24 hours a day, 7 days a week

SECTION 2 Hazard Identification**2.1. Classification of the substance or mixture****GHS US classification**

Not classified

2.2. Label elements**GHS US labeling**

No labeling applicable

2.3. Hazards associated with known or reasonably anticipated uses

No additional information available

2.4. Hazards not otherwise classified

No additional information available

2.5. Unknown acute toxicity

56.6% of the mixture consists of ingredient(s) of unknown acute toxicity (Dermal)
56.6% of the mixture consists of ingredient(s) of unknown acute toxicity (Inhalation (vapors))

PRIMEGUARD -100 PG RVAF 6/1GAL

Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS 2024)

SECTION 3 Composition/information on ingredients

3.1. Substances

Not applicable

3.2. Mixtures

This mixture does not contain any substances to be mentioned according to the criteria for section 3.2 of HCS

SECTION 4 First aid measures

4.1. Description of necessary first-aid measures

First-aid measures general	: IF exposed or concerned: Get medical advice/attention.
First-aid measures after inhalation	: Remove person to fresh air and keep comfortable for breathing.
First-aid measures after skin contact	: Get immediate medical advice/attention. Wash skin with plenty of water.
First-aid measures after eye contact	: Get immediate medical advice/attention. Rinse eyes with water as a precaution.
First-aid measures after ingestion	: Immediately call a poison center or doctor/physician. Do NOT induce vomiting unless directed to do so by medical personnel. Call a poison center/doctor/physician if you feel unwell.
Personal protection for first-aid responders.	: First aid workers will be equipped with suitable personal protective equipment.

4.2. Most important symptoms/effects, acute and delayed

Symptoms/effects after inhalation	: Depression of the central nervous system, headaches, dizziness, drowsiness, loss of coordination.
Symptoms/effects after skin contact	: None under normal conditions.
Symptoms/effects after eye contact	: None under normal conditions.
Symptoms/effects after ingestion	: Can cause blindness. Depression of the central nervous system, headaches, dizziness, drowsiness, loss of coordination.

4.3. Indication of immediate medical attention and special treatment needed, if necessary

Other medical advice or treatment	: Treat symptomatically.
-----------------------------------	--------------------------

SECTION 5: Fire-fighting measures

5.1. Suitable (and unsuitable) extinguishing media

Suitable extinguishing media	: Water spray. Dry powder. Foam. Carbon dioxide.
Unsuitable extinguishing media	: Use of heavy stream of water may spread fire.

5.2. Specific hazards arising from the chemical

Fire hazard	: No fire hazard.
Explosion hazard	: No direct explosion hazard.
Hazardous decomposition products in case of fire	: Toxic fumes may be released.

5.3. Special protective equipment and precautions for fire-fighters

Firefighting instructions	: Cool laterally with water containers exposed to flames, even after the fire is extinguished. Do not enter fire area without proper protective equipment, including respiratory protection.
Protection during firefighting	: Do not attempt to take action without suitable protective equipment. Self-contained breathing apparatus. Complete protective clothing.

PRIMEGUARD -100 PG RVAF 6/1GAL

Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS 2024)

SECTION 6 Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

General measures : Stop leak if safe to do so. Notify authorities if product enters sewers or public waters. Absorb spillage to prevent material-damage.

For non-emergency personnel

Protective equipment : Wear recommended personal protective equipment.
Emergency procedures : Ventilate spillage area.

For emergency responders

Protective equipment : Do not attempt to take action without suitable protective equipment. For further information refer to section 8: "Exposure controls/personal protection".
Emergency procedures : Evacuate unnecessary personnel. Stop leak if safe to do so.
Environmental precautions : Avoid release to the environment.

6.2. Methods and materials for containment and cleaning up

For containment : Absorb spilled material with sand or earth. Contain any spills with dikes or absorbents to prevent migration and entry into sewers or streams. Stop leak, if possible without risk.
Methods for cleaning up : Take up liquid spill into absorbent material.
Other information : Dispose of materials or solid residues at an authorized site.

For further information refer to section 13.

SECTION 7 Handling and storage

7.1. Precautions for safe handling

Precautions for safe handling : Ensure good ventilation of the work station. Wear personal protective equipment.
Hygiene measures : Do not eat, drink or smoke when using this product. Always wash hands after handling the product.
Additional hazards when processed : Not expected to present a significant hazard under anticipated conditions of normal use.

7.2. Conditions for safe storage, including incompatibilities

Technical measures : Keep in a cool, well-ventilated place away from heat.
Storage conditions : Keep cool. Protect from sunlight.
Packaging materials : Always store product in container of same material as original container.

SECTION 8 Exposure controls/personal protection

8.1. Control parameters

No additional information available

8.2. Appropriate engineering controls

Appropriate engineering controls : Ensure good ventilation of the work station.
Environmental exposure controls : Avoid release to the environment.

8.3. Individual protection measures, such as personal protective equipment

Personal protective equipment:

Wear eye protection. Wear protective gloves. Wear protective clothing. Wash hands and other exposed areas with mild soap and water before eating, drinking or smoking and when leaving work.

PRIMEGUARD -100 PG RVAF 6/1GAL

Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS 2024)

Hand protection:
Protective gloves
Eye protection:
Safety glasses
Skin and body protection:
Wear suitable protective clothing
Respiratory protection:
In case of insufficient ventilation, wear suitable respiratory equipment

Personal protective equipment symbol(s):



SECTION 9 Physical and chemical properties

9.1. Basic physical and chemical properties

Physical state	: Liquid
Color	: Blue
Odor	: mild
Odor threshold	: No data available
pH	: No data available
Melting point	: Not applicable
Freezing point	: No data available
Boiling point	: No data available
Flash point	: 102 °C
Flammability (solid, gas)	: Not applicable.
Vapor pressure	: No data available
Relative vapor density at 20°C	: No data available
Relative density	: 1.04
Density	: 1.04 g/ml
Solubility	: Soluble.
Partition coefficient n-octanol/water (Log Pow)	: No data available
Auto-ignition temperature	: No data available
Decomposition temperature	: No data available
Viscosity, kinematic	: No data available
Explosion limits	: No data available
Particle characteristics	: No data available

9.2. Data relevant with regard to physical hazard classes (supplemental)

No additional information available

SECTION 10 Stability and reactivity

10.1. Reactivity

The product is non-reactive under normal conditions of use, storage and transport.

PRIMEGUARD -100 PG RVAF 6/1GAL

Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS 2024)

10.2. Chemical stability

Stable under normal conditions.

10.3. Possibility of hazardous reactions

No dangerous reactions known under normal conditions of use.

10.4. Conditions to avoid

None under recommended storage and handling conditions (see section 7).

10.5. Incompatible materials

Strong oxidizing agents.

10.6. Hazardous decomposition products

Under normal conditions of storage and use, hazardous decomposition products should not be produced.

SECTION 11 Toxicological information

Likely routes of exposure : Skin and eye contact. Inhalation.

11.1. Information on toxicological effects

Acute toxicity (oral) : Not classified
Acute toxicity (dermal) : Not classified
Acute toxicity (inhalation) : Not classified

PRIMEGUARD -100 PG RVAF 6/1GAL	
Unknown acute toxicity (GHS US)	56.6% of the mixture consists of ingredient(s) of unknown acute toxicity (Dermal) 56.6% of the mixture consists of ingredient(s) of unknown acute toxicity (Inhalation (vapors))

Skin corrosion/irritation : Not classified

Serious eye damage/irritation : Not classified

Respiratory or skin sensitization : Not classified

Germ cell mutagenicity : Not classified

Carcinogenicity : Not classified

Reproductive toxicity : Not classified

STOT-single exposure : Not classified

STOT-repeated exposure : Not classified

Aspiration hazard : Not classified

Symptoms/effects after inhalation : Depression of the central nervous system, headaches, dizziness, drowsiness, loss of coordination.

Symptoms/effects after skin contact : None under normal conditions.

Symptoms/effects after eye contact : None under normal conditions.

Symptoms/effects after ingestion : Can cause blindness. Depression of the central nervous system, headaches, dizziness, drowsiness, loss of coordination.

SECTION 12 Ecological information

12.1. Ecotoxicity

Ecology - general : The product is not considered harmful to aquatic organisms or to cause long-term adverse effects in the environment.

PRIMEGUARD -100 PG RVAF 6/1GAL

Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS 2024)

Hazardous to the aquatic environment, short-term (acute) : Not classified
Hazardous to the aquatic environment, long-term (chronic) : Not classified

12.2. Persistence and degradability

PRIMEGUARD -100 PG RVAF 6/1GAL	
Persistence and degradability	Not rapidly degradable

12.3. Bioaccumulative potential

No additional information available

12.4. Mobility in soil

No additional information available

12.5. Other adverse effects

Ozone : Not classified
Fluorinated greenhouse gases : No

SECTION 13 Disposal considerations

Regional waste regulation : Disposal must be done according to official regulations.
Waste treatment methods : Dispose of contents/container in accordance with licensed collector's sorting instructions.
Sewage disposal recommendations : Disposal must be done according to official regulations.
Product/Packaging disposal recommendations : Disposal must be done according to official regulations.
Additional information : Do not re-use empty containers.

SECTION 14 Transport information

In accordance with DOT / TDG / IMDG / IATA

DOT	TDG	IMDG	IATA
14.1. UN number			
Not regulated for transport			
14.2. Proper Shipping Name			
Not regulated	Not regulated	Not regulated	Not regulated
14.3. Transport hazard class(es)			
Not regulated	Not regulated	Not regulated	Not regulated
14.4. Packing group			
Not regulated	Not regulated	Not regulated	Not regulated
14.5. Environmental hazards			
Not regulated	Not regulated	Not regulated	Not regulated
No supplementary information available			

14.6. Transport in bulk

Not applicable

PRIMEGUARD -100 PG RVAF 6/1GAL

Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS 2024)

14.7. Special precautions for user

DOT

Not regulated

TDG

Not regulated

IMDG

Not regulated

IATA

Not regulated

SECTION 15 Regulatory information

15.1. Federal regulations

Commercial status of components according to the United States Environmental Protection Agency's Toxic Substances Control Act (TSCA):

No data available

This product or mixture is not known to contain a toxic chemical or chemicals in excess of the applicable de minimis concentration as specified in 40 CFR §372.38(a) subject to the reporting requirements of section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 and 40 CFR Part 372.

15.2. International regulations

CANADA

No additional information available

EU-Regulations

No additional information available

National regulations

No additional information available

15.3. State regulations

California Proposition 65 - This product does not contain any substances known to the state of California to cause cancer, developmental and/or reproductive harm

SECTION 16 Other information

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS 2024)

Revision date : 1/30/2026

Issue date : 11/18/2025

Safety Data Sheet (SDS), USA

This safety data sheet and the information it contains is offered to you in good faith as accurate. We have reviewed any information contained in the data sheet which we have received from outside sources and we believe the information to be correct, but cannot guarantee its accuracy or completeness. Health and safety precautions in this data sheet may not be adequate for all individuals and/or situations. It is the user's obligation to evaluate and use this product in a safe manner and to comply with all applicable laws and regulations. No statement made in this data sheet shall be construed as permission or recommendation for the use of any product in a manner that might infringe existing patents. No warranty is made, either expressed or implied.