ABB BALDOR RELIANCE

Customer information packet

L3504-50

.5/.37KW, 1425RPM, 1PH, 50HZ, 56, 3424LC, TEFC
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/5/2026 3:11:16 PM

Specifications

Enclosure	TEFC
Frame	56
Frame Material	Steel
Frequency	50.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Cap Start, Cap Run
Output @ Frequency	.370 KW @ 50 HZ
Phase	1
Synchronous Speed @ Frequency	1500 RPM @ 50 HZ
Voltage @ Frequency	110.0 V @ 50 HZ
	220.0 V @ 50 HZ
Agency Approvals	C UR US
	CE
	CURUS
	UKCA
	WEEE
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	5.000 A @ 110.0 V
	2.500 A @ 220.0 V
Design Code	-
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	72.7 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None

Part Detail

Revision	G
Type	AC
Mech. spec.	34G375
Base	
Status	PRD/A
Elec. spec.	34WGR778
Layout	34LYG375
Eff. date	06-15-2026
CD Diagram	CD0055
Poles	04
Leads	6#18
Proprietary	False
Created date	10-10-2023

Heater Indicator	No Heater
High Voltage Full Load Amps	2.5 a
Insulation Class	B
Inverter Code	Not Inverter
KVA Code	J
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Quantity/Wire Size	6 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3424LC
Mounting Arrangement	F1
Number of Poles	4
Overall Length	11.97 IN
Power Factor	93
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.25
Shaft Diameter	0.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1425 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1372L								
CAT.NO.	L3504-50							
SPEC.	34G375R778							
HP	.5/.37KW							
VOLTS	110/220							
AMP	5/2.5							
R.P.M. (1/MIN)	1425							
FRAME	56	**HZ**	50		**PH**	1		
SER.F.	1.25	**CODE**	J	**DES**	-	**CL**	B	
NEMA-NOM-EFF	72.7	**PF**	93					
RATING	40C AMB-S1 CONT							
CC			IP44 IC411 19KG					
DE	6203	**ODE**	6203					
ENCL	TEFC	**SN**						
	IE2-50HZ 68(75%),60 (50%)							

Accessories

Part number	Description	Multiplier
34-171	C FACE KIT	A8

AC Induction Motor Performance Data
Record # 101512
Typical performance - not guaranteed values

Winding: 34WGR778-R002	**Type:** 3424LC	**Enclosure:** TEFC

Nameplate Data				**220 V, 50 Hz: High Voltage Connection**	
Rated Output (KW)			.37	**Full Load Torque**	1.811 LB-FT
Volts			110/220	**Start Configuration**	direct on line
Full Load Amps			5/2.5	**Breakdown Torque**	4.92 LB-FT
R.P.M.			1425	**Pull-up Torque**	4.25 LB-FT
Hz	50	**Phase**	1	**Locked-rotor Torque**	5.35 LB-FT
NEMA Design Code	-	**KVA Code**	J	**Starting Current**	18.6 A
Service Factor (S.F.)			1.25	**No-load Current**	1.33 A
NEMA Nom. Eff.	72.7	**Power Factor**	93	**Line-line Res. @ 25ºC**	4.8692 Ω A Ph 4.0443 Ω B Ph
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	53°C
S.F. Amps			6/3	**Temp. Rise @ S.F. Load**	63°C

Load Characteristics 220 V, 50 Hz, 0.37 KW

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	66	79	86	90	92	93	92
Efficiency	44	61.6	69.4	72.8	73.8	73.1	73.8
Speed	1484.9	1473.4	1460.5	1446.1	1429	1408.9	1429
Line amperes	1.47	1.74	2.14	2.58	3.1	3.69	3.1


ABB Motors and Mechanical Inc.

WINDING # 34WGR778


0.37 KW 1 PH 50 HZ 1425 RPM 220 V 3424LC

TORQUES(LB-FT): PO=4.92 PU=4.25 LR=5.35 LRA=18.6

Typical performance - not guaranteed values.



34LYG375




34LYG375

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION

REV. DESC: LOAD TO SOLIDWORKS			BALDOR - RELIANCE®
REV: E	VERSION: 04	REVISED: 03:58:39 08/09/2022	TDR: 000001194274
34LYG375	MODEL NO. 34LYG375		REF: -
	BY: ENFRAJ0		HORZ 34LC NEMA 56 TEFC

CD0055



	LINE A	LINE B	JOIN
HIGH STD	1	4,5	2,3,8
HIGH OPP	1	4,8	2,3,5
LOW STD	1,3,8	2,4,5	–
LOW OPP	1,3,5	2,4,8	–

NOTES:

1. STANDARD ROTATION IS CCW FACING END OPPOSITE SHAFT EXTENSION.
2. OPTIONAL THERMOSTAT IS PROVIDED WHEN SPECIFIED.
3. MULTIPLE CAPACITORS ARE CONNECTED IN PARALLEL UNLESS OTHERWISE SPECIFIED.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: D	BY: JLP	REVISED: 04/08/99 1:17	TDR: 0178636
CD0055		FILE: AAA00007414	MDL: –
		MTL: –	TYPE LC, DV, REV, 6 LEADS

CD0055