



## AYP350, Compression Pin Adapter, 350 kcmil, AL9CU

By Burndy  
Catalog # [AYP350](#)

350 kcmil, Aluminum Termination, Straight Pin, .57" Pin Dia, 1.34" Pin Length



### Features

- All-aluminum electro-tin plated design eliminates possible bi-metallic corrosion
- Provides the shortest connector length design possible permitting easy installation in equipment with limited working space
- Solid electro-tin plated aluminum plug
- Proper electrical connection made easily and eliminates the "how tight is tight" issue
- Solid plug has equivalent cross-sectional area as current carrying equivalent copper wire permitting use of larger aluminum wire to connect equipment
- Offset plug design available in sizes 2/0 through 750 kcmil providing flexibility and maximizing the use of limited space while eliminating interference between conductors and equipment
- Electro-tin plating resists corrosion
- Factory pre-filled with PENETROX oxide inhibiting compound with conductive metallic particles to penetrate aluminum oxide between strands and forms an air-tight connection
- EPDM rubber covers supplied with each connector and rated for 600V eliminating taping
- Only 5 die sets are required to install the complete line from #6 to 750 kcmil reducing inventory requirements
- Supplied in plastic convenience pack so cover and connector are kept together and free of foreign material until opened
- Connectors are clearly marked with catalog number, wire size, along with a color-coded die index providing clear, easy to use information

### Application

Wire Termination

### Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Certification - CSA Approved Yes

### Conductor

Conductor - Material	ALUMINUM / COPPER
Wire Size	350 KCMIL
Conductor - AL Str Size	350 KCMIL
Conductor - AL Str Size Range	350 kcmil
Conductor - Copper Str Size	350 KCMIL
Conductor - Copper DLO Size Range	313 kcmil
Conductor - Copper Str Compact Size	350 KCMIL
Conductor - Copper DLO Size	313 KCMIL
Conductor Size	350 KCMIL
Conductor Type	CODE/FLEX
Conductor - Copper Str Size Range	350 kcmil
Conductor - Copper Flex I Size	-

### Configuration

Physical Attribute - Number of Crimps Required	2
Connector Type	INLINE PIN

### Current

Voltage Rating	35 kV
Voltage - Maximum	35000 V

### Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - P inch	1.34 in
Dimension - L Length Overall mm	70 mm
Width	1.1 in
Dimension - A Outside	1.10 in
Diameter inch	
Dimension - Strip Length inch Length	1-1/8 2.75 in
Equivalent Pin Size	250 kcmil
Dimension - B Length fraction	1-1/16 in
Dimension - B Length inch	1.07 in

Dimension - B Outside	0.57 in
Diameter inch	
Height	1.1 in
Dimension - Length Overall	2.75 in
inch	
Dimensions	2.75 in x 1.1 in x 1.1 in

Type	Aluminum Pin Adapters
Material	Aluminum
Plating Type	Tin
Finish Type	Tin-Plated
UPC 12 Digit	781810737705
UPC 14 Digit GTIN	00781810737705

### General

Insulation Type	EPDM Rubber
Trade Name	HYPLUG™
Die Index	299
Insulation	Y
Terminal Type	Pin
Plated	Y
Color Code	Brown
Pin Type	Solid
Sub Brand	HYPLUG
UPC	781810737705

### Logistics

Minimum Pack Quantity	1
Pallet Quantity	2960
Carton Quantity	10

### Operational

Temperature Rating	194
--------------------	-----

### Product Assets

[Catalog \[English\]](#)



A Hubbell brand