

Garant**HiPer-Drill base body, 12×D, Ø DC: 43mm****Order data**

Order number	231620 43
GTIN	4062406641771
Item class	21S

Description**Version:**

- **Very high feed rates and maximum performance due to optimally matched geometries and materials.**
- **Precise positioning of the cutter insert due to Vee insert seating and secure clamping by the centre bore.**
- **High concentricity when assembled.**
- **Shank support for optimum stability in operation.**

Polished flutes.

Application:

Stationary and rotating use. For holes up to IT9 accuracy.

Note:

Further sizes up to Ø 50.99 mm available on request.

The insert screw must be replaced after every fifth change of cutter insert.

For process reliability when using the drill, initial pilot drilling to 1.5×D with the drill No. 231600 with the same cutter insert size and type is necessary. **The generation of a pilot hole improves process reliability.**

Clamp in a hydraulic chuck (such as No. 302026 size 20) for optimum radial run-out.

For optimum stability, clamp the drill so the overhang is as short as possible.

Reduce feed rates f by 10 % and v_c values by 40 %.

For process reliability when using the drill, initial pilot drilling to 1.5×D with the drill No. 231600 with the same cutter insert size and type is necessary. **The generation of a pilot hole improves process reliability.**

Technical description

Overall length L	670 mm
Dia. range D_c	43 - 44.99 mm

Series	HiPer-Drill
Reach L ₁	540 mm
Shank length L _s	70 mm
Number of cutting edges Z	2
Clamping screw	231999 25IP
Shank Ø D _s	40 mm
Version	12xD
Shank	ISO 9766
Use for drilling	limited cross-drilling
Use for drilling	limited drilling through a stack
Use for drilling	limited oblique spot drilling
Use for drilling	limited drilling with oblique exit
Through-coolant	yes
Type of product	Indexable drill

Accessories

Torx Plus® screw Drive 25IP	231999 25IP
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 25IP	674252 25IP