

SAFETY DATA SHEET

SECTION 1) CHEMICAL PRODUCT AND MANUFACTURER'S IDENTIFICATION

Product ID: 496335
Product Name: ZenaMax
Revision Date: Mar 16, 2023 **Date Printed:** Mar 16, 2023
Version: 5.0 **Supersedes Date:** May 23, 2022
Manufacturer's Name: Zenex International
Address: 1 Zenex Circle Cleveland, OH, US, 44146
Emergency Phone: 1-800-535-5053
Information Phone Number: (440)-232-4155
Fax:
Product/Recommended Uses: All Purpose Cleaner

SECTION 2) HAZARDS IDENTIFICATION

Classification

Gases Under Pressure Liquefied Gas
Eye Irritation - Category 2B

Pictograms



Signal Word

Warning

Hazardous Statements - Physical

H280 - Contains gas under pressure; may explode if heated

Hazardous Statements - Health

H320 - Causes eye irritation

Precautionary Statements - General

P101 - If medical advice is needed, have product container or label at hand.
P102 - Keep out of reach of children.
P103 - Read label before use.

Precautionary Statements - Prevention

P264 - Wash hands thoroughly after handling.

Precautionary Statements - Response

P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P337 + P313 - If eye irritation persists: Get medical advice/attention.

Precautionary Statements - Storage

P410 + P403 - Protect from sunlight. Store in a well-ventilated place.

Precautionary Statements - Disposal

No precautionary statement available.

Hazards Not Otherwise Classified (HNOC)

No data available.

SECTION 3) COMPOSITION/INFORMATION ON INGREDIENTS

CAS	Chemical Name	% By Weight
106-97-8	BUTANE	1% - 5%
111-76-2	ETHYLENE GLYCOL MONOBUTYL ETHER	1% - 3%
74-98-6	PROPANE	1% - 3%
1336-21-6	AMMONIUM HYDROXIDE	0% - 1%

Specific chemical identity and/or exact percentage (concentration) of the composition has been withheld to protect confidentiality.

SECTION 4) FIRST-AID MEASURES

Inhalation

Remove source of exposure or move person to fresh air and keep comfortable for breathing. If breathing is difficult, trained personnel should administer emergency oxygen if advised to do so by the POISON CENTER/doctor. If breathing has stopped, trained personnel should begin rescue breathing or, if the heart has stopped, immediately start cardiopulmonary resuscitation (CPR) or automated external defibrillation (AED). If you feel unwell/If concerned: Get medical advice/attention.

Eye Contact

Rinse eyes cautiously with lukewarm, gently flowing water for 15 minutes, while holding the eyelids open. Remove contact lenses, if present and easy to do. Take care not to rinse contaminated water into the unaffected eye or onto the face. If eye irritation persists: Get medical advice/attention.

Skin Contact

Wipe off with a towel. Wash with soap and water. Get medical attention if irritation persists.

Ingestion

Ingestion is not a likely route of exposure. Get medical attention if you feel unwell.

Most Important Symptoms/Effects, Acute and Delayed

No data available.

Indication of Immediate Medical Attention and Special Treatment Needed

No data available.

SECTION 5) FIRE-FIGHTING MEASURES

Suitable Extinguishing Media

Foam, alcohol foam, carbon dioxide, dry chemical, water fog.

Unsuitable Extinguishing Media

Water may be ineffective but can be used to cool containers exposed to heat or flame.

Specific Hazards in Case of Fire

Closed containers may explode from internal pressure build-up when exposed to extreme heat and discharge contents. Liquid content of container will not support combustion. Overexposure to decomposition products may cause a health hazard. Symptoms may not be

readily apparent. Obtain medical attention. Hazardous decomposition products include carbon dioxide, carbon monoxide, and other toxic fumes.

Fire-fighting Procedures

Water may be used to cool containers to prevent pressure build-up and explosion when exposed to extreme heat.

Special Protective Actions

Wear goggles and use a self-contained breathing apparatus. If water is used, fog nozzles are preferred.

SECTION 6) ACCIDENTAL RELEASE MEASURES

Emergency Procedure

Ventilate area. Remove all sources of ignition.

Recommended Equipment

See section 8 for specifics on protective personal equipment (PPE).

Personal Precautions

Avoid breathing vapors. Ventilate area. Wear safety glasses and gloves.

Environmental Precautions

Stop spill/release if it can be done safely.

Methods and Materials for Containment and Cleaning up

Contain and collect spillage with non-combustible, absorbent material e.g. sand, earth, vermiculite or diatomaceous earth and place in container for disposal according to local regulations.

SECTION 7) HANDLING AND STORAGE

General

Do not puncture or incinerate (burn) cans. Do not stick pins, nails, or any other sharp objects into opening on top of can. Do not spray in eyes. Do not take internally.

Ventilation Requirements

Use in a well-ventilated place.

Storage Room Requirements

Store and use in a cool, dry, well-ventilated area. Do not store above 120°F. See product label for additional information.

SECTION 8) EXPOSURE CONTROLS/PERSONAL PROTECTION

Eye protection

Wear safety glasses with side shields. Eyewash stations and showers should be available in areas where this material is used and stored.

Skin Protection

Use solvent-resistant protective gloves for prolonged or repeated contact.

Respiratory protection

In restricted areas, use approved chemical/mechanical filters designed to remove a combination of particles and vapor. In confined areas, use an approved air line respirator or hood. A self-contained breathing apparatus is required for vapor concentrations above PEL/TLV limits.

Appropriate Engineering Controls

Ventilation should be sufficient to prevent inhalation of any vapors.

Chemical Name	OSHA TWA (mg/m3)	OSHA TWA (ppm)	OSHA STEL (mg/m3)	OSHA STEL (ppm)	OSHA Carcinogen	OSHA Skin designation	OSHA Tables (Z1, Z2, Z3)	ACGIH TWA (mg/m3)
BUTANE								
ETHYLENE GLYCOL	240	50				1	1	

MONOBUTYL ETHER								
PROPANE	1800	1000					1	

Chemical Name	ACGIH TWA (ppm)	ACGIH STEL (mg/m3)	ACGIH STEL (ppm)	ACGIH Carcinogen	ACGIH TLV Basis	ACGIH Notations	NIOSH TWA (mg/m3)	NIOSH TWA (ppm)
BUTANE			1000 (EX)		CNS impair		1900	800
ETHYLENE GLYCOL MONOBUTYL ETHER	20			A3	Eye & URT irr	A3; BEI	24	5
PROPANE			Simple asphyxiant (D), explosion hazard (EX)		Asphyxia		1800	1000

Chemical Name	NIOSH STEL (mg/m3)	NIOSH STEL (ppm)	NIOSH Carcinogen
BUTANE			
ETHYLENE GLYCOL MONOBUTYL ETHER			
PROPANE			

(C) - Ceiling limit, A3 - Confirmed Animal Carcinogen with Unknown Relevance to Humans, BEI - Substances for which there is a Biological Exposure Index or Indices, CNS - Central nervous system, impair - Impairment, irr - Irritation, URT - Upper respiratory tract

SECTION 9) PHYSICAL AND CHEMICAL PROPERTIES

Physical and Chemical Properties

Density	8.61 lb/gal
Density VOC	0.43 lb/gal
% VOC	4.99%
Appearance	clear liquid
Odor Threshold	N.A.
Odor Description	Mint
pH	11.40
Water Solubility	Soluble
Flammability	Will not burn
Flash Point Symbol	N.A.
Flash Point	>200.0 °F
Viscosity	N.A.
Lower Explosion Level	N.A.
Upper Explosion Level	N.A.
Vapor Density	Slower than ether
Melting Point	N.A.
Freezing Point	N.A.
Low Boiling Point	N.A.
High Boiling Point	N.A.

Decomposition Pt	N.A.
Auto Ignition Temp	N.A.
Evaporation Rate	Slower than ether

SECTION 10) STABILITY AND REACTIVITY

Stability

The product is stable under normal storage conditions.

Conditions To Avoid

High temperatures.

Incompatible Materials

None known.

Hazardous Reactions/Polymerization

None known.

Hazardous Decomposition Products

Hazardous decomposition products may include carbon dioxide, carbon monoxide, and other toxic fumes.

SECTION 11) TOXICOLOGICAL INFORMATION

Skin Corrosion/Irritation

Based on available data, the classification criteria are not met.

Likely Route of Exposure

Inhalation, ingestion, skin absorption.

Serious Eye Damage/Irritation

Causes eye irritation

Carcinogenicity

Based on available data, the classification criteria are not met.

Germ Cell Mutagenicity

Based on available data, the classification criteria are not met.

Reproductive Toxicity

Based on available data, the classification criteria are not met.

Respiratory/Skin Sensitization

Based on available data, the classification criteria are not met.

Specific Target Organ Toxicity - Single Exposure

Based on available data, the classification criteria are not met.

Specific Target Organ Toxicity - Repeated Exposure

Based on available data, the classification criteria are not met.

Aspiration Hazard

Based on available data, the classification criteria are not met.

Acute Toxicity

Based on available data, the classification criteria are not met.

Likely Routes of Exposure

Inhalation, Ingestion, Skin contact, Eye contact

SECTION 12) ECOLOGICAL INFORMATION

Toxicity

Based on available data, the classification criteria are not met.

Persistence and Degradability

Readily biodegradable.

Bioaccumulative Potential

No data available.

Mobility in Soil

No data available.

Other Adverse Effects

No data available.

Results of the PBT and vPvB assessment

Readily biodegradable.

SECTION 13) DISPOSAL CONSIDERATIONS

Waste Disposal

Under RCRA, it is the responsibility of the user of the product, to determine at the time of disposal whether the product meets RCRA criteria for hazardous waste. Waste management should be in full compliance with federal, state, and local laws. Empty containers retain product residue which may exhibit hazards of material, therefore do not pressurize, cut, glaze, weld or use for any other purposes. Return drums to reclamation centers for proper cleaning and reuse.

SECTION 14) TRANSPORT INFORMATION

	IATA Information	IMDG Information	U.S. DOT Information
UN number:	UN1950	UN1950	UN1950
Proper shipping name:	Aerosols, flammable	Aerosols	Aerosols
Hazard class:	2.1	2.1	2.1
Packaging group:	N.A.	N.A.	N.A.
Note / Special Provision:	(LTD QTY)	(LTD QTY)	(LTD QTY)

SECTION 15) REGULATORY INFORMATION

CAS	Chemical Name	% By Weight	Regulation List
106-97-8	BUTANE	1% - 5%	SARA312, VOC, TSCA, ACGIH
111-76-2	ETHYLENE GLYCOL MONOBUTYL ETHER	1% - 3%	SARA313, CERCLA, SARA312, VOC, TSCA, ACGIH, OSHA, ,
74-98-6	PROPANE	1% - 3%	SARA312, VOC, TSCA, ACGIH, OSHA
1336-21-6	AMMONIUM HYDROXIDE	0% - 1%	SARA313, CERCLA, SARA312, TSCA

SECTION 16) OTHER INFORMATION


Glossary

ACGIH- American Conference of Governmental Industrial Hygienists; ANSI- American National Standards Institute; Canadian TDG- Canadian Transportation of Dangerous Goods; CAS- Chemical Abstract Service; Chemtrec- Chemical Transportation Emergency Center (US); CHIP- Chemical Hazard Information and Packaging; DSL- Domestic Substances List; EC- Equivalent Concentration; EH40 (UK)- HSE Guidance Note EH40 Occupational Exposure Limits; EPCRA- Emergency Planning and Community Right-To-Know Act; ESL- Effects screening levels; HMIS- Hazardous Material Information Service; LC- Lethal Concentration; LD- Lethal Dose; NFPA- National Fire Protection Association; OEL- Occupational Exposure Limits; OSHA- Occupational Safety and Health Administration, US Department of Labor; PEL- Permissible Exposure Limit; SARA (Title III)- Superfund Amendments and Reauthorization Act; SARA 313- Superfund Amendments and Reauthorization Act, Section 313; SCBA- Self-Contained Breathing Apparatus; STEL- Short Term Exposure Limit; TCEQ- Texas Commission on Environmental Quality; TLV- Threshold Limit Value; TSCA- Toxic Substances Control Act Public Law 94- 469; TWA- Time Weighted Value; US DOT- US Department of Transportation; WHMIS- Workplace Hazardous Materials Information System.

HMIS

Health	/ 1
FLAMMABILITY	1
Physical Hazard	0
Personal Protection	

NFPA



(*) - Chronic effects

Caution: HMIS® ratings are based on a 0-4 rating scale, with 0 representing minimal hazards or risks, and 4 representing significant hazards or risks

Version 5.0:

Revision Date: Mar 16, 2023

DISCLAIMER

To the best of our knowledge, the information contained herein is accurate. However, neither the above named supplier nor any of its subsidiaries assumes any liability whatsoever for the accuracy or completeness of the information contained herein. Final determination of suitability of any material is the sole responsibility of the user. All materials may present unknown hazards and should be used with caution. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that exist. The above information pertains to this product as currently formulated, and is based on the information available at this time. Addition of reducers or other additives to this product may substantially alter the composition and hazards of the product. Since conditions of use are outside our control, we make no warranties, express or implied, and assume no liability in connection with any use of this information.