ABB BALDOR RELIANCE

Customer information packet

VLECP83769T-4

32M 2P TEFC VER 213LP CHEM PROC, SP#32-8
Class - CLI GP A,B,C,D
Division - Division II

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/5/2026 5:54:50 PM

Specifications

Enclosure	TEFC
Frame	213LP
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP A,B,C,D
Haz Area Division	Division II
Motor Letter Type	Three Phase
Output @ Frequency	7.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
Agency Approvals	CSA EEV NEMA PREMIUM UR CSA
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	6
Current @ Voltage	8.600 A @ 460.0 V
Design Code	B
Drip Cover	Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.7 %
Electrically Isolated Bearing	Not Electrically Isolated
Enclosure Modification	841
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Haz Area Temp Code	T3C

Part Detail

Revision	J
Type	AC
Mech. spec.	07D516
Base	
Status	PRD/A
Elec. spec.	07WGY929
Layout	07LYD516
Eff. date	06-18-2026
CD Diagram	CD0006
Poles	02
Leads	3#14
Proprietary	False
Created date	03-25-2019

Heater Indicator	No Heater
High Voltage Full Load Amps	8.6 a
Insulation Class	F
Inverter Code	Inverter Duty
IP Rating	IP56
KVA Code	H
Lifting Lugs	Vertical Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	5400 rpm
Motor Lead Quantity/Wire Size	3 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0732M
Mounting Arrangement	W6
Number of Poles	2
Overall Length	24.71 IN
Power Factor	88
Product Family	Chem Process S/P 32-8 IEEE 841
Pulley End Bearing Type	Roller
Pulley Face Code	P-Base
Pulley Shaft Indicator	P-Base Groove & Key
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	3510 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None

Winding Thermal 2	None

Nameplate

NP4328									
CAT.NO.	VLECP83769T-4								
SPEC.	07D516Y929G1								
HP	7.5 TE			**IP**	56				
VOLTS	460								
AMPS	8.9								
R.P.M.	3480								
FRAME	213LP	**HZ**	60			**PH**	3		
SER.F.	1.15	**CODE**	H	**DES.**	B		**CLASS**	F	
RATING	40C AMB-CONT								
SN									
DE	6309	**ODE**	7306						
NEMA NOM. EFF.	89.5	**P.F.**	89						
GUAR. MIN. EFF.	87.5	**CC**	010A						
T. CODE	T3C	**TEMP=**	160						

NP3186							
SPEC.	07D516Y929G1						
ABMA DE BRG	45BC03X30X						
ABMA ODE BRG	30BT03X30X						
GREASE	POLYREX EM						
MOTOR WEIGHT	171	**ROTOR BARS**	28	**STATOR BARS**	36		
MAX. R.P.M.	5400	**MAX. KVAR**	0.34				
INV.TYPE	PWM						
T=	160						
CHP	60	**TO**	90				
CT	6	**TO**	60				
VT	6	**TO**	60				
HTR-VOLTS	N/A	**HTR-AMPS**	N/A				
HTR-WATTS	N/A	**MAX. SPACE HEATER TEMP.**			N/A		


AC Induction Motor Performance Data
Record # 95372
Typical performance - not guaranteed values


Winding: 07WGY929-R034	**Type:** 0732M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: Single Voltage Motor**	
Rated Output (HP)			7.5	**Full Load Torque**	11.38 LB-FT
Volts			460	**Start Configuration**	direct on line
Full Load Amps			8.9	**Breakdown Torque**	40.1 LB-FT
R.P.M.			3480	**Pull-up Torque**	18 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	21.6 LB-FT
NEMA Design Code	B	**KVA Code**	H	**Starting Current**	62 A
Service Factor (S.F.)			1.15	**No-load Current**	2.79 A
NEMA Nom. Eff.	89.5	**Power Factor**	89	**Line-line Res. @ 25ºC**	1.1813 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	20°C
S.F. Amps				**Temp. Rise @ S.F. Load**	24°C
				Locked-rotor Power Factor	31.7
				Rotor inertia	0.292 lb-ft²

Load Characteristics 460 V, 60 Hz, 7.5 HP


% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	60	79	86	89	90	91	90
Efficiency	86	90.4	91.2	90.7	89.8	88.5	90.2
Speed	3574	3551	3528	3503	3476	3446	3487
Line amperes	3.53	4.96	6.84	8.87	11	13.3	10.1



ABB Motors and Mechanical Inc.
WINDING # 07WGY929
7.5 HP 3 PH 60 HZ 3480 RPM 460 V 0732M
Typical performance - not guaranteed values.
TORQUES(LB-FT): PO=40.1 PU=18 LR=21.6 LRA=62
TORQUE
RPM
KW
AMPS
EFF
PF
%EFF %PF
TORQUE (LB-FT)
RPM
KW
AMPS
PERCENT OF RATED OUTPUT (7.5 HP)
11/5/2026 ACPERF, record # 95372


07LYD516
(717-756) = 24.73[628]
9.53[242]
2.72[69]
2.76[70]
.72[18]
.750[19.0]
.745[18.9]
.377[9.6]
.375[9.5]
GREASE FITTING
W/PLASTIC CAP
(EA. END)
.38 [10] KEYWAY
2.03 [52] LONG
(USABLE)
Ø13.25
[337]
Ø9.88[251]
(MAX)
8.253[209.6]
8.250[209.5]
1.250[31.7]
1.245[31.6]
Ø 1.6250[41.3]
1.6245[41.3]
.001 A
.281
PLUG
GROUND
LUG
SS DRAIN
FITTING
(PU END ONLY)
GREASE RELIEF
(EA. END)
12.26[311]
9.48[241]
6.625
45°
45°
7.70[196]
DRAIN
HOLE
LEAD HOLE
1.50 N.P.T.
4 HOLES
Ø.44 [11] ON
Ø9.12 [232] B.C.
7.44[189]
SMALL SIDE OF
INTER RACE SHOULD BE
TOUCHING EACH OTHER
WAVY WASHER
ON DRIVE END
OPPOSITE DRIVE END
DRIVE END DETAIL
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CONVERT AUTOCAD DRW TO SWD DRW
REV: A
VERSION: 01
REVISED: 09:23:03 01/02/2023
TDR: 000001201569
MODEL NO. 07LYD516
REF: -
BY: ENALEM0
B
BALDOR - RELIANCE®
VER 213-5LP TEFC 307M W6 CP IEEE841 7306 DUPLEX
07LYD516


CD0006

TYPICAL WYE–CONNECTED MOTOR





TYPICAL DELTA–CONNECTED MOTOR



NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: E	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\141	REVISED: 10:24:49 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1