

11147 Super-Tugger® 6001 Adapter Package

- Adapt 6001 Super-Tugger to Super-Tugger® with Wheeled Carriage and Boom for faster and easier cable puller setups
- Wheeled carriage and boom provides fast setup with no anchors to set or chains to mount
- Boom uses 3" rigid steel conduit for easy length adjustment to pull 10 feet (3m) of cable out of the box fast and easy
- Optional Elbow Unit and Boom available to reach into manholes or pull up to 20 feet (6 m) of cable out of the box

SPECIFICATIONS:

Weight	198 lb (90 kg)
Length	91-1/2" (232 cm)
Width	27" (69 cm)
Height	38-1/2" (98 cm)
Use With	Greenlee 6001 Cable Pullers
Load Rating	6500 lb (28.9 kN)

CAT. NO.	UPC NO.	DESCRIPTION
11147	783310111474	Super-Tugger® 640/6001 Adapter Package Includes wheeled carriage, 4 ft (1.2 m) boom, boom adapter, nose unit, 2-1/2", 3" and 4" slip-in couplings and 2", 3" and 4" screw-on couplings

NOTE: Properly rated rope is critical to cable pulling. See page 225 for rope selection by rating.

Package Components

			SUPER-TUGGER – 6,500 LB			
			110 VAC			
CAT. NO.	UPC NO.	DESCRIPTION	6001	6004	6005	11147
6001	783310296270	Cable Puller w/Force Gauge 120 VAC, 60 Hz	X	X	X	–
6037	783310356059	Floor Mount	–	X	X	–
29631	783310296317	Vise Chains	X	X	X	–
11145	783310111450	Boom Mount	–	X	X	X
00791	783310007913	4' (1.2 m) Boom Tube	–	X	X	X
00864	783310008644	Nose Unit	–	X	X	X
00863	783310008637	Elbow Unit	–	–	X	X
00835	783310008354	3' (.9 m) Boom Tube	–	–	X	–
03661	783310036616	2" Screw-On Coupling	–	–	–	X
00781	783310007814	2-1/2" Screw-On Coupling	–	X	X	–
00782	783310007821	3" Screw-On Coupling	–	X	X	X
00783	783310007838	3-1/2" Screw-On Coupling	–	X	X	–
00784	783310007845	4" Screw-On Coupling	–	X	X	X
00799	783310007999	Adapter for Screw-On Coupling	–	X	X	–
00804	783310008040	2-1/2" Slip-In Coupling	–	X	X	X
00811	783310008118	3" Slip-In Coupling	–	X	X	X
00815	783310008156	3-1/2" Slip-In Coupling	–	X	X	–
00820	783310008200	4" Slip-In Coupling	–	X	X	X
11152	783310111528	Storage Trays (2)	–	X	X	X
8012	783310008729	12" Hook Sheave	–	–	–	–