


SmartRack Roof-Mounted Fan Panel for Wide Rack Enclosure Cabinets - 6 120V Fans, 630 CFM, 5-15P Plug

MODEL NUMBER: SRFANROOFWD



Pre-mounted rack cooling fans increase ventilation through your server cabinet to help prevent equipment from overheating.

Features

Rack Cooling Fans for 30 in. Wide Enclosures

The SmartRack® SRFANROOFWD is a roof-mounted panel containing six 120V high-performance fans. Designed specifically for SmartRack's 30-inch-wide rack enclosures, these fans help keep rack-mounted equipment cool to maintain top performance and avoid failures that can lead to costly downtime, damage or data loss. The SRFANROOFWD removes warm air at rates up to 630 CFM.

Plug-and-Play Construction for Easy Installation

All necessary toolless mounting hardware is included. The SRFANROOFWD is made from heavy-duty cold-rolled steel with a black finish. The six-foot power cord with NEMA 5-15P plug connects to any compatible wall outlet, PDU or UPS system.

Specifications

OVERVIEW	
UPC Code	037332283351
Accessory Type	Cooling Accessories; Fan Panel
Accessory Class	Cooling Accessories
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Nominal Input Voltage Description	120V AC 50/60 Hz
Input Connection Type	NEMA 5-15P
Input Plug Features	NEMA 5-15P

Highlights

- Helps boost rack equipment performance by increasing airflow through the enclosure
- Includes 6 high-performance 630 CFM fans pre-mounted in cold-rolled steel roof panel
- Plug-and-play operation with all necessary toolless mounting hardware included
- Specially designed for 30 in. wide SmartRack enclosures for AI servers

System Requirements

SmartRack enclosure with 30 in. width and standard 42 in. depth

Package Includes

SRFANROOFWD SmartRack Roof-Mounted Fan Panel



Powering Business Worldwide

TRIPP LITE
SERIES

Voltage Compatibility (VAC)	120
Input Frequency	50/60 Hz
Input Cord Length (ft.)	6
Input Cord Length (m)	1.83
COOLING	
Cooling Type	Passive
USER INTERFACE, ALERTS & CONTROLS	
Switches	Lighted ON/OFF rocker switch
PHYSICAL	
Shipping Dimensions (hwd / in.)	3.75 x 31.10 x 38.58
Shipping Dimensions (hwd / cm)	9.52 x 78.99 x 97.99
Shipping Weight (lbs.)	23.00
Shipping Weight (kg)	10.43
Unit Dimensions (hwd / in.)	2.700 x 27.750 x 35.500
Unit Dimensions (hwd / cm)	6.858 x 70.485 x 90.170
Unit Weight (lbs.)	20
Unit Weight (kg)	9.07
STANDARDS & COMPLIANCE	
Product Certifications	CAN/CSA-C22.2 No. 60950-1 (Canada); CAN/CSA-C22.2 No. 62368-1 (Canada); UL 60950-1; UL 62368-1
Product Compliance	RoHS; EIA/ECA-310-E
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.