


Cut protection glove with CRF® technology and PU-dipped palm. Good grip on dry/moist surfaces.

## TEGERA® 433

Learn more

## DURABLE, FLEXIBLE, AND SILICONE-FREE

A versatile cut protection glove with CRF® technology and high durability. Smooth and comfortable for, for example, fine assembly work. The glove has a PU-dipped palm with a smooth finish that provides good grip on dry/moist surfaces. Silicone free.

### CHARACTERISTICS

- Good fingertip sensitivity
- Flexible
- Very durable
- Good grip
- Comfortable

### FUNCTIONS

- Silicone-free

CRF®

OEKO TEX® STANDARD 100 SE 14-214 RISE



*All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.*

## PREVENTS RISK OF

Cut injuries, Scratches, lacerations, Contact with dirt

## PRIMARY ENVIRONMENTS OF USE

Cut risk environments, Dry environments, Moist environments, Dirty environments

## PRIMARY AREAS OF USE

Assembly, Building and construction, Engineering, Installation work, Machine operating, Transport work, Warehouse work

## PRIMARY INDUSTRIES OF USE

Automotive manufacturing, Automotive repair and maintenance, Basic metals manufacturing, Building and construction, Electrical equipment manufacturing, Machinery and equipment manufacturing, Metal manufacturing and fabrication, Transport equipment manufacturing, Transportation and logistics

## TYPE OF WORK

Medium weight

## SPECIFICATION

**TYPE** Cut resistant gloves
**CATEGORY** Cat. II
**KNITTING GAUGE (GG)** 13
**LINING MATERIAL** CRF® Technology, HPPE, Nylon, Spandex
**LENGTH** 220-270 mm
**DEXTERITY** 5
**GRIP DESIGN** Smooth finish
**COLOUR** Grey
**PAIRS PER: BUNDLE/CARTON** 12/72
**DISPLAY TYPE** Bulk pack
**DIPPING** Palm-dipped
**DIPPING MATERIAL** PU
**CUFF STYLE** Knitwrist cuff
**CUFF MATERIAL** Textile
**CUT RESISTANCE (EN ISO 13997)** Cut resistance level B
**CUT RESISTANCE (EN ISO 13997) TDM:** 6.5 N
**INNER MATERIAL SPECIFICATION** HPPE (High performance polyethylene), Nylon, Elastane
**OUTER MATERIAL SPECIFICATION** Polyurethane

## COMPLIANCE

CE Cat. II

EAC TP TC 019:2011

EN ISO 21420:2020

EN 388:2016+A1:2018 4X43B

ANSI A2 CUT

ANSI 6 ABR

## FEATURES

Cut protection

| SIZE | | ARTICLE NUMBER | EAN |
|---|---|---|---|
| 5 | XXS | 433-5 | 7340118374123 |
| 6 | XS | 433-6 | 7340118374215 |
| 7 | S | 433-7 | 7340118374307 |
| 8 | M | 433-8 | 7340118374390 |
| 9 | L | 433-9 | 7340118374482 |
| 10 | XL | 433-10 | 7340118374574 |
| 11 | XXL | 433-11 | 7340118374666 |
| 12 | 3XL | 433-12 | 7340118374758 |

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com



*All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.*