Safety Data Sheet

RUST-OLEUM CORPORATION
* Trusted Quality Since 1921 *
www.rustoleum.com

1. Identification

Name on Label: Glitter

Product Name: SPECLT SSPR 6PK GLTR RAINBOW

Revision Date: 12/10/2025

Product Identifier: 398582

Supercedes Date: 8/15/2025

Recommended Use: Topcoat / Aerosols

Supplier:
Rust-Oleum Corporation
11 Hawthorn Parkway
Vernon Hills, IL 60061
USA

Manufacturer:
Rust-Oleum Corporation
11 Hawthorn Parkway
Vernon Hills, IL 60061
USA

Preparer: Regulatory Department

Emergency Telephone: 24 Hour Hotline: 847-367-7700

2. Hazard Identification

Classification

Symbol(s) of Product



Signal Word
Danger

Possible Hazards
81% of the mixture consists of ingredient(s) of unknown acute toxicity.

GHS Hazard Statements

Aerosol, category 1	H222	Extremely flammable aerosol.
	H229	Pressurized container: may burst if heated.
Skin Irritation, category 2	H315	Causes skin irritation.
Eye Irritation, category 2A	H319	Causes serious eye irritation.
STOT, Single Exposure, category 3, NE	H336	May cause drowsiness or dizziness.
Carcinogenicity, category 2	H351	Suspected of causing cancer.
Reproductive Toxicity, category 2	H361	Suspected of damaging fertility or the unborn child.
STOT, Repeated Exposure, category 1	H372	Causes damage to organs through prolonged or repeated exposure.

GHS Label Precautionary Statements

P201	Obtain special instructions before use.
P210	Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P211	Do not spray on an open flame or other ignition source.
P251	Do not pierce or burn, even after use.

P260	Do not breathe dust, fumes, gas, mist, vapours, or spray.
P264	Wash thoroughly after handling.
P271	Use only outdoors or in a well-ventilated area.
P280	Wear protective gloves, protective clothing, eye protection, and face protection.
P302+P352	IF ON SKIN: Wash with plenty of soap and water.
P304+P340	IF INHALED: Remove person to fresh air and keep comfortable for breathing.
P305+P351+P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P308+P313	IF exposed or concerned: Get medical advice.
P312	Call a POISON CENTER or physician if you feel unwell.
P321	Specific treatment (see notice on this label).
P332+P313	If skin irritation occurs: Get medical advice/attention.
P337+P317	If eye irritation persists: Get medical help.
P362+P364	Take off contaminated clothing and wash it before reuse.
P403+P233	Store in a well-ventilated place. Keep container tightly closed.
P405	Store locked up.
P410+P412	Protect from sunlight. Do not expose to temperatures exceeding 50°C / 122°F.
P501	Dispose of contents and container in accordance with local, regional and national regulations.

GHS SDS Precautionary Statements

P270	Do not eat, drink or smoke when using this product.

3. Composition / Information on Ingredients

HAZARDOUS SUBSTANCES

Chemical Name	CAS-No.	Wt.% Range	GHS Symbols	GHS Statements
Heptane, branched, cyclic and linear	426260-76-6	45-70	GHS07-GHS08	H304-315-319-336-351-361
Propane	74-98-6	10-30	GHS04	H280
n-Butane	106-97-8	3.0-7.0	GHS04	H280
Cyclohexane	110-82-7	1.0-5.0	GHS02-GHS07-GHS08	H225-304-315-336
Stoddard Solvent	8052-41-3	1.0-5.0	GHS08	H304-372
Methanol	67-56-1	0.5-1.5	GHS02-GHS06-GHS08	H225-331-370
Hexane	110-54-3	0.1-1.0	GHS02-GHS07-GHS08	H225-304-315-336-361-372
Aluminum Flake	7429-90-5	0.1-1.0	GHS02	H228-250-261
Toluene	108-88-3	0.1-1.0	GHS02-GHS07-GHS08	H225-304-315-332-336-361-373

Actual concentrations of ingredients are withheld as trade secret.

4. First Aid Measures

First Aid - Eye Contact: Immediately flush eyes with plenty of water for at least 15 minutes holding eyelids open. Get medical attention. Do NOT allow rubbing of eyes or keeping eyes closed. Remove contact lenses, if present and easy to do. Continue rinsing.

First Aid - Skin Contact: Immediately flush skin with plenty of water for at least 15 minutes while removing clothing. Get medical attention immediately. Wash clothing separately before reuse.

First Aid - Inhalation: Remove to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Get immediate medical attention. Do NOT use mouth-to-mouth resuscitation. If you experience difficulty in breathing, leave the area to obtain fresh air. If continued difficulty is experienced, get medical assistance immediately.

First Aid - Ingestion: If swallowed, do not induce vomiting. If victim is conscious and alert, give 2 to 4 cupfuls of water or milk. Call a physician or poison control center immediately. Never give anything by mouth to an unconscious person. Treat symptomatically and supportively. Do not induce vomiting unless advised by a physician. Call nearest Poison Control Center or Physician immediately.

5. Fire-Fighting Measures

EXTINGUISHING MEDIA: Aqueous Film Forming Foam, Carbon Dioxide, Dry Chemical, Dry Sand, Water Fog

Unusual Fire and Explosion Hazards: Water spray may be ineffective. Closed containers may explode when exposed to extreme heat. Vapors may form explosive mixtures with air. Vapors can travel to a source of ignition and flash back. Isolate from heat, electrical equipment, sparks and open flame. Perforation of the pressurized container may cause bursting of the can. FLASH POINT IS LESS THAN -7°C (20°F). EXTREMELY FLAMMABLE LIQUID AND VAPOR!

Special Fire Fighting Procedures: Water may be used to cool closed containers to prevent buildup of steam. If water is used, fog nozzles are preferred. Evacuate area and fight fire from a safe distance. Containers can rupture and release highly toxic material if exposed to heat. Substance is non-combustible but reacts with many metals to form explosive hydrogen gas. Use water spray to keep fire-exposed containers cool. Containers may explode when heated.

Special Fire and Explosion Hazard (Combustible Dust): Not a combustible dust.

6. Accidental Release Measures

Steps to Be Taken If Material Is Released or Spilled: Contain spilled liquid with sand or earth. DO NOT use combustible materials such as sawdust. Remove all sources of ignition, ventilate area and remove with inert absorbent and non-sparking tools. Dispose of according to local, state (provincial) and federal regulations. Do not incinerate closed containers. Avoid runoff into sewers and waterways. Provide ventilation and approach spill from upwind using proper personal protective equipment as indicated in Section 8.

7. Handling and Storage

Handling: Wash thoroughly after handling. Wash hands before eating. Remove contaminated clothing and launder before reuse. Use only with adequate ventilation. Follow all SDS and label precautions even after container is emptied because it may retain product residues. Avoid breathing fumes, vapors, or mist. Do not get in eyes, on skin or clothing. Do not puncture or incinerate (burn) container, even after use.

Storage: Contents under pressure. Do not store above 120°F (49°C). Store large quantities in buildings designed and protected for storage of flammable aerosols. Keep away from heat, sparks, flame and sources of ignition.

Advice on Safe Handling of Combustible Dust: No Information

8. Exposure Controls / Personal Protection

Chemical Name	CAS-No.	Weight % Less Than	ACGIH TLV-TWA	ACGIH TLV-STEL	OSHA PEL-TWA	OSHA PEL-CEILING
Heptane, branched, cyclic and linear	426260-76-6	60.0	N.E.	N.E.	N.E.	N.E.
Propane	74-98-6	15.0	N.E.	N.E.	1000 ppm	N.E.
n-Butane	106-97-8	10.0	N.E.	1000 ppm	N.E.	N.E.
Cyclohexane	110-82-7	5.0	100 ppm	N.E.	300 ppm	N.E.
Stoddard Solvent	8052-41-3	5.0	100 ppm	N.E.	500 ppm	N.E.
Methanol	67-56-1	5.0	200 ppm	250 ppm	200 ppm	N.E.
Hexane	110-54-3	1.0	50 ppm	N.E.	500 ppm	N.E.
Aluminum Flake	7429-90-5	1.0	1 mg/m3	N.E.	15 mg/m3	N.E.
Toluene	108-88-3	1.0	20 ppm	N.E.	200 ppm	300 ppm

PERSONAL PROTECTION

Engineering Controls: Use process enclosures, local exhaust ventilation, or other engineering controls to control airborne levels below recommended exposure limits. Use explosion-proof ventilation equipment. Facilities storing or utilizing this material should be equipped with an eyewash facility and a safety shower. Prevent build-up of vapors by opening all doors and windows to achieve cross-ventilation.

Respiratory Protection: A respiratory protection program that meets OSHA 1910.134 and ANSI Z88.2 (U.S.) and/or SOR/86-304 Part XII 12.13 and CSA Standard Z180.1 (Canada) requirements must be followed whenever workplace conditions warrant a respirator's use. A NIOSH/MSHA approved air purifying respirator with organic vapor cartridge or canister may be permissible under certain circumstances where airborne concentrations are expected to exceed exposure limits.

Skin Protection: Use impervious gloves to prevent skin contact and absorption of this material through the skin.

Eye Protection: Use safety eyewear designed to protect against splash of liquids.

Other Protective Equipment: Refer to safety supervisor or industrial hygienist for further guidance regarding types of personal protective equipment and their applications.

Hygienic Practices: Wash thoroughly with soap and water before eating, drinking or smoking. Remove contaminated clothing immediately and launder before reuse.

Engineering Measures for Combustible Dust: No Information

9. Physical and Chemical Properties

Physical State	Liquid	**Decomposition Temperature, °C**	N.D.
Color	Multiple Colors	**pH**	N.A.
Odor	Solvent Like	**Kinematic Viscosity**	N.D.
Odor Threshold	Threshold N.E.	**Solubility in Water**	Slight
Freezing Point / Melting Point, °C	N.D.	**Partition Coefficient, n-octanol/water**	N.D.
Boiling Range, °C	-37 - 537	**Vapor Pressure**	N.D.
Flammability	Supports Combustion	**Evaporation Rate**	Faster than Ether
Lower Explosion Limit, vol%	0.1	**Specific Gravity**	0.682
Upper Explosion Limit, vol%	9.5	**Vapor Density**	Heavier than Air
Flash Point, °C	-96	**Particle Characteristics**	N.A.
Auto-Ignition Temperature, °C	N.D.		

(See "Other information" Section for abbreviation legend)

10. Stability and Reactivity

Conditions to Avoid: Avoid temperatures above 120°F (49°C). Avoid all possible sources of ignition. Flammable hydrogen gas will evolve when product comes in contact with water or damp air. Heat will be generated. The amount of heat generated will depend upon the volume of material in contact. Avoid contact with metals. Avoid excess heat.

Incompatibility: Incompatible with strong oxidizing agents, strong acids and strong alkalies. Product slowly corrodes copper, aluminum, zinc, and galvanized surfaces.

Hazardous Decomposition: When heated to decomposition, it emits acrid smoke and irritating fumes. Contains solvents which may form carbon monoxide, carbon dioxide, and formaldehyde.

Hazardous Polymerization: Will not occur under normal conditions.

Stability: This product is stable under normal storage conditions.

11. Toxicological Information

Effects of Overexposure - Eye Contact: Can cause severe eye irritation. Causes eye burns. Causes eye and skin irritation which may lead to dermatitis with repeated exposures. Irritating, and may injure eye tissue if not removed promptly. High vapor concentrations can irritate eyes, nose and respiratory passages.

Effects of Overexposure - Skin Contact: Substance is corrosive. Causes severe skin burns. May be absorbed through the skin in harmful amounts. Severely irritating; may cause permanent skin damage.

Effects of Overexposure - Inhalation: High gas, vapor, mist or dust concentrations may be harmful if inhaled. Avoid breathing fumes, spray, vapors, or mist. High vapor concentrations are irritating to the eyes, nose, throat and lungs.

Effects of Overexposure - Ingestion: Corrosive and may cause severe and permanent damage to mouth, throat and stomach. Harmful if swallowed. Poison, may be fatal or cause blindness if swallowed.

Effects of Overexposure - Chronic Hazards: High concentrations may lead to central nervous system effects (drowsiness, dizziness, nausea, headaches, paralysis, and blurred vision) and/or damage. Reports have associated repeated and prolonged occupational overexposure to solvents with permanent brain and nervous system damage. May cause genetic defects. May damage fertility or the unborn child.

PRIMARY ROUTE(S) OF ENTRY: Eye Contact, Ingestion, Inhalation, Skin Absorption, Skin Contact

ACUTE TOXICITY VALUES
The acute effects of this product have not been tested. Data on individual components are tabulated below:

CAS-No.	Chemical Name	Oral LD50	Dermal LD50	Vapor LC50
426260-76-6	Heptane, branched, cyclic and linear	5500 mg/kg	N.E.	N.E.
106-97-8	n-Butane	N.E.	N.E.	658 mg/L Rat
110-82-7	Cyclohexane	12705 mg/kg Rat	>2000 mg/kg Rabbit	>32.9 mg/L Rat
8052-41-3	Stoddard Solvent	N.E.	>3000 mg/kg Rabbit	25
67-56-1	Methanol	6200 mg/kg Rat	15840 mg/kg Rabbit	N.E.
110-54-3	Hexane	25000 mg/kg Rat	3000 mg/kg Rabbit	N.E.
108-88-3	Toluene	5000 mg/kg Rat	12000 mg/kg Rabbit	12.5 mg/L Rat

N.E. - Not Established

12. Ecological Information

Ecological Information: No ecotoxicity data was found for this product.

13. Disposal Considerations

Disposal: Dispose of material in accordance to local, state, and federal regulations and ordinances. Do not incinerate closed containers. This product as supplied is a US EPA defined ignitable hazardous waste. Dispose of unusable product as a hazardous waste (D001) in accordance with local, state, and federal regulation. RCRA Hazardous Waste: This material, when discarded or disposed of, could be a hazardous waste according to federal regulations (40 CFR 261) due to the characteristic of corrosivity (D002). Check state and local regulations for disposal requirements. Chemical additions, processing or otherwise altering this material may make the waste management information presented in this SDS incomplete, inaccurate, or otherwise inappropriate.

14. Transport Information

	Domestic (USDOT)	International (IMDG)	Air (IATA)	TDG (Canada)
UN Number:	N.A.	1950	1950	1950
Proper Shipping Name:	Paint and Related Spray Products in Ltd Qty	Aerosols	Aerosols, flammable	AEROSOLS, flammable
Hazard Class:	N.A.	2	2.1	2.1
Packing Group:	N.A.	N.A.	N.A.	N.A.
Limited Quantity:	Yes	Yes	Yes	Yes

15. Regulatory Information

U.S. Federal Regulations:

CERCLA - SARA Hazard Category

This product has been reviewed according to the EPA 'Hazard Categories' promulgated under Sections 311 and 312 of the Superfund Amendment and Reauthorization Act of 1986 (SARA Title III) and is considered, under applicable definitions, to meet the following categories:

Carcinogenicity, Reproductive toxicity, Skin Corrosion or Irritation, Serious eye damage or eye irritation, Specific target organ toxicity (single or repeated exposure)

SARA Section 313

This product contains the following substances subject to the reporting requirements of Section 313 of Title III of the Superfund Amendment and Reauthorization Act of 1986 and 40 CFR part 372:

Chemical Name	CAS-No.
Cyclohexane	110-82-7
Methanol	67-56-1
Hexane	110-54-3
Aluminum Flake	7429-90-5
Toluene	108-88-3

Toxic Substances Control Act

This product contains the following chemical substances subject to the reporting requirements of TSCA 12(b) if exported from the United States:

No TSCA 12(b) components exist in this product.

16. Other Information

HMIS RATINGS

Health:	2*	**Flammability:**	4	**Physical Hazard:**	0	**Personal Protection:**	X

NFPA RATINGS

Health:	2	**Flammability:**	4	**Instability:**	0

Maximum Incremental Reactivity: 0.91

SDS REVISION DATE: 12/10/2025

REASON FOR REVISION:

Revision Description Changed
Product Composition Changed
Substance and/or Product Properties Changed in Section(s):
01 - Identification
02 - Hazard Identification
03 - Composition / Information on Ingredients
09 - Physical & Chemical Properties
11 - Toxicological Information
15 - Regulatory Information
16 - Other Information
Substance Hazard Threshold % Changed
Revision Statement(s) Changed

Legend: N.A. - Not Applicable, N.D. - Not Determined, N.E. - Not Established

Rust-Oleum Corporation believes, to the best of its knowledge, information and belief, the information contained herein to be accurate and reliable as of the date of this safety data sheet. However, because the conditions of handling, use, and storage of these materials are beyond our control, we assume no responsibility or liability for personal injury or property damage incurred by the use of these materials. Rust-Oleum Corporation makes no warranty, expressed or implied, regarding the accuracy or reliability of the data or results obtained from their use. All materials may present unknown hazards and should be used with caution. The information and recommendations in this material safety data sheet are offered for the users' consideration and examination. It is the responsibility of the user to determine the final suitability of this information and to comply with all applicable international, federal, state, and local laws and regulations.