Revision Number: 003.1 **Issue date:** 07/11/2017

1. PRODUCT AND COMPANY IDENTIFICATION

Product name: LOCTITE MR 5438 PLASTIC PIPE SEALANT known as LOCTITE® NO MORE LEAKS™ White
IDH number: 1537780
Product type: Sealant
Item number: 1537780
Restriction of Use: None identified
Region: United States
Company address:
Henkel Corporation
One Henkel Way
Rocky Hill, Connecticut 06067
Contact information:
Telephone: +1 (860) 571-5100
MEDICAL EMERGENCY Phone: Poison Control Center
1-877-671-4608 (toll free) or 1-303-592-1711
TRANSPORT EMERGENCY Phone: CHEMTREC
1-800-424-9300 (toll free) or 1-703-527-3887
Internet: www.henkelna.com

2. HAZARDS IDENTIFICATION

EMERGENCY OVERVIEW	
DANGER:	FLAMMABLE LIQUID AND VAPOR. MAY BE FATAL IF SWALLOWED AND ENTERS AIRWAYS. CAUSES SKIN IRRITATION. CAUSES SERIOUS EYE IRRITATION. MAY CAUSE RESPIRATORY IRRITATION.

HAZARD CLASS	HAZARD CATEGORY
FLAMMABLE LIQUID	3
SKIN IRRITATION	2
EYE IRRITATION	2A
SPECIFIC TARGET ORGAN TOXICITY - SINGLE EXPOSURE	3
ASPIRATION HAZARD	1

PICTOGRAM(S)



Precautionary Statements

Prevention: Keep away from heat, sparks, open flames, hot surfaces - no smoking. Keep container tightly closed. No release into water. Use explosion-proof equipment. Use non-sparking tools. Take action to prevent static discharges. Avoid breathing vapors, mist, or spray. Wash affected area thoroughly after handling. Use only outdoors or in a well-ventilated area. Wear protective gloves, eye protection, and face protection.

Response: IF SWALLOWED: Immediately call a physician or poison control center. If on skin (or hair): Take off immediately all contaminated clothing. IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing. Call a POISON CENTER or physician if you feel unwell. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Do NOT induce vomiting. If skin irritation occurs: Get medical attention. If eye irritation persists: Get medical attention. Take off contaminated clothing. In case of fire: Use foam, dry chemical or carbon dioxide to extinguish.

Storage: Store in a well-ventilated place. Keep container tightly closed. Store in a well-ventilated place. Keep cool. Store locked up.

Disposal: Dispose of contents and/or container according to Federal, State/Provincial and local governmental regulations.

Classification complies with OSHA Hazard Communication Standard (29 CFR 1910.1200) and is consistent with the provisions of the United Nations Globally Harmonized System of Classification and Labeling of Chemicals (GHS).

See Section 11 for additional toxicological information.

3. COMPOSITION / INFORMATION ON INGREDIENTS

Hazardous Component(s)	CAS Number	Percentage*
Talc	14807-96-6	30 - 40
Rosin, fumaric acid, pentaerythritol polymer	65997-11-7	20 - 30
2-Propanol	67-63-0	10 - 20
Oleic acid 5.5EO	9004-96-0	10 - 20
Titanium dioxide	13463-67-7	1 - 5
Quartz (SiO2)	14808-60-7	0.1 - 1

* Exact percentages may vary or are trade secret. Concentration range is provided to assist users in providing appropriate protections.

4. FIRST AID MEASURES

Inhalation: Move to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Get medical attention.

Skin contact: Immediately flush skin with plenty of water (using soap, if available). Remove contaminated clothing and footwear. Get medical attention. Wash clothing before reuse.

Eye contact: Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.

Ingestion: Never give anything by mouth to an unconscious person. DO NOT induce vomiting unless directed to do so by medical personnel. Get medical attention.

Symptoms: See Section 11.

5. FIRE FIGHTING MEASURES

Extinguishing media: Water spray (fog), foam, dry chemical or carbon dioxide.

Special firefighting procedures: Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear. In case of fire, keep containers cool with water spray.

Unusual fire or explosion hazards: None

Hazardous combustion products: Oxides of carbon. Toxic and irritating vapors.

6. ACCIDENTAL RELEASE MEASURES

Use personal protection recommended in Section 8, isolate the hazard area and deny entry to unnecessary and unprotected personnel.

Environmental precautions: Do not allow product to enter sewer or waterways.

Clean-up methods: Remove all sources of ignition. Evacuate and ventilate spill area; dike spill to prevent entry into water system; wear full protective equipment during clean-up. Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, saw dust). Scrape up as much material as possible. Store in a partly filled, closed container until disposal. Refer to Section 8 "Exposure Controls / Personal Protection" prior to clean up.

7. HANDLING AND STORAGE

Handling: Use only with adequate ventilation. Prevent contact with eyes, skin and clothing. Do not breathe vapor and mist. Wash thoroughly after handling. Keep container closed. Refer to Section 8.

Storage: Keep in a cool, well ventilated area away from heat, sparks and open flame. Keep container tightly closed until ready for use.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Employers should complete an assessment of all workplaces to determine the need for, and selection of, proper exposure controls and protective equipment for each task performed.

Hazardous Component(s)	ACGIH TLV	OSHA PEL	AIHA WEEL	OTHER
Talc	2 mg/m3 TWA Respirable fraction.	0.1 mg/m3 TWA Respirable. 2.4 MPPCF TWA Respirable. 20 MPPCF TWA	None	50 ppm
Rosin, fumaric acid, pentaerythritol polymer	None	None	None	None
2-Propanol	200 ppm TWA 400 ppm STEL	400 ppm (980 mg/m3) PEL	None	None
Oleic acid 5.5EO	None	None	None	None
Titanium dioxide	10 mg/m3 TWA	15 mg/m3 PEL Total dust. 15 MPPCF TWA Respirable fraction. 15 mg/m3 TWA Total dust. 50 MPPCF TWA Total dust. 5 mg/m3 TWA Respirable fraction.	None	None
Quartz (SiO2)	0.025 mg/m3 TWA Respirable fraction.	2.4 MPPCF TWA Respirable. 0.1 mg/m3 TWA Respirable. 0.05 mg/m3 TWA (Respirable dust.) (Respirable dust.) 0.025 mg/m3 OSHA_ACT (Respirable dust.) 0.05 mg/m3 PEL Respirable dust.	None	None

Engineering controls: Provide adequate local exhaust ventilation to maintain worker exposure below exposure limits.

Respiratory protection: Use a NIOSH approved air-purifying respirator if the potential to exceed established exposure limits exists.

Eye/face protection:	Safety goggles or safety glasses with side shields. Full face protection should be used if the potential for splashing or spraying of product exists. Safety showers and eye wash stations should be available.
Skin protection:	Use chemical resistant, impermeable clothing including gloves and either an apron or body suit to prevent skin contact.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical state:	Liquid, Paste
Color:	White
Odor:	Alcoholic
Odor threshold:	Not available.
pH:	Not applicable
Vapor pressure:	33 mm hg (68 °F (20°C))
Boiling point/range:	180 °F (82.2 °C)None
Melting point/ range:	Not available.
Specific gravity:	1.37
Vapor density:	2.07
Flash point:	36 °C (96.8 °F)
Flammable/Explosive limits - lower:	2.3 %
Flammable/Explosive limits - upper:	12.7 %
Autoignition temperature:	398.3 °C (748.94 °F) Estimated
Flammability:	Not applicable
Evaporation rate:	7.7 (Ether = 1)
Solubility in water:	Partially soluble
Partition coefficient (n-octanol/water):	Not determined
VOC content:	15.2 % EPA Method 24
Viscosity:	Not available.
Decomposition temperature:	Not available.

10. STABILITY AND REACTIVITY

Stability:	Stable under normal conditions of storage and use.
Hazardous reactions:	Will not occur.
Hazardous decomposition products:	Oxides of carbon. Irritating organic fragments.
Incompatible materials:	Oxidizing agents.
Reactivity:	Not available.
Conditions to avoid:	Elevated temperatures. Heat, flames, sparks and other sources of ignition. Store away from incompatible materials.

11. TOXICOLOGICAL INFORMATION

Relevant routes of exposure: Skin, Inhalation, Eyes, Ingestion

Potential Health Effects/Symptoms

Inhalation: Inhalation of vapors or mists of the product may be irritating to the respiratory system. Abrasion of cured material such as by sanding or grinding could release respirable particles of silica quartz, a cancer hazard by inhalation. Normal use of this product causes no such release.

Skin contact: Causes skin irritation.

Eye contact: Causes serious eye irritation.

Ingestion: Principal hazard of ingestion is aspiration into the lungs and subsequent pneumonitis. May be harmful or fatal if swallowed.

Hazardous Component(s)	LD50s and LC50s	Immediate and Delayed Health Effects
Talc	None	Irritant, Lung, Some evidence of carcinogenicity
Rosin, fumaric acid, pentaerythritol polymer	None	No Records
2-Propanol	Oral LD50 (Rat) = 5,045 mg/kg Oral LD50 (Mouse) = 3,600 mg/kg Oral LD50 (Rabbit) = 6,410 mg/kg Oral LD50 (Rat) = 4.7 g/kg Oral LD50 (Mouse) = 4.5 g/kg Oral LD50 (Rabbit) = 8.0 g/kg Oral LD50 (Rabbit) = 5.03 g/kg Dermal LD50 (Rabbit) = 12,800 mg/kg	Allergen, Central nervous system, Irritant
Oleic acid 5.5EO	None	Irritant
Titanium dioxide	None	Irritant, Respiratory, Some evidence of carcinogenicity
Quartz (SiO2)	None	Immune system, Lung, Some evidence of carcinogenicity

Hazardous Component(s)	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen (Specifically Regulated)
Talc	No	Group 2B	No
Rosin, fumaric acid, pentaerythritol polymer	No	No	No
2-Propanol	No	No	No
Oleic acid 5.5EO	No	No	No
Titanium dioxide	No	Group 2B	No
Quartz (SiO2)	Known To Be Human Carcinogen.	Group 1	Yes

12. ECOLOGICAL INFORMATION

Ecological information: Not available.

13. DISPOSAL CONSIDERATIONS

Information provided is for unused product only.

Recommended method of disposal: Follow all local, state, federal and provincial regulations for disposal.

Hazardous waste number: D001: Ignitable.

14. TRANSPORT INFORMATION

The transport information provided in this section only applies to the material/formulation itself, and is not specific to any package/configuration.

U.S. Department of Transportation Ground (49 CFR)

Proper shipping name: Resin solution
Hazard class or division: 3
Identification number: UN 1866
Packing group: III

International Air Transportation (ICAO/IATA)

Proper shipping name: Resin solution
Hazard class or division: 3
Identification number: UN 1866
Packing group: III
Exceptions: Consumer Commodity, ID 8000, Class 9, (Not more than 500 ml)

Water Transportation (IMO/IMDG)

Proper shipping name: RESIN SOLUTION
Hazard class or division: 3
Identification number: UN 1866
Packing group: III

15. REGULATORY INFORMATION

United States Regulatory Information

TSCA 8 (b) Inventory Status: All components are listed or are exempt from listing on the Toxic Substances Control Act Inventory.
TSCA 12 (b) Export Notification: None above reporting de minimis

CERCLA/SARA Section 302 EHS: None above reporting de minimis.
CERCLA/SARA Section 311/312: Fire, Immediate Health, Delayed Health
CERCLA/SARA Section 313: None above reporting de minimis.
CERCLA Reportable quantity: 2-Propanol (CAS# 67-63-0) 100 lbs. (45.4 kg)

California Proposition 65: This product contains a chemical known in the State of California to cause cancer.

Canada Regulatory Information

CEPA DSL/NDSL Status: All components are listed on or are exempt from listing on the Canadian Domestic Substances List.

16. OTHER INFORMATION

This safety data sheet contains changes from the previous version in sections: 3, 8, 11

Prepared by: Cara R. Rivera, Regulatory Affairs Specialist

Issue date: 07/11/2017

DISCLAIMER: The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation and its affiliates ("Henkel") does not assume responsibility for any results obtained by persons over whose methods Henkel has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any Henkel's products. In light of the foregoing, Henkel specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel's products. Henkel further disclaims any liability for consequential or incidental damages of any kind, including lost profits.