

Material Safety Data Sheet 材料安全数据表

Report No.:

报告编号:

CMC251104045M01

Name of sample:

样品名称:

Cylindrical Lithium-ion Rechargeable Cell

圆柱形锂离子可充电电池

Model:

型号:

HYLN IMR18650-1500mAh

Type:

规格:

3.7V 1500mAh 5.55Wh

Client:

委托单位:

Henan Hengyi lithium energy technology Co., Ltd

河南恒一锂电科技有限公司

Address:


地址:

Building 3, Xinhua Industrial Park, Longmen Avenue,
Xinhua District, Pingdingshan City, Henan, P.R.China

中国河南平顶山市新华区龙门大道新华区产业园 3 号楼

Tested by 主检人:

(Testing Engineer 测试工程师)



Jinsheng Li 李金生

Approved by 批准人:

(Technical Director 技术总监)



Barry He 何清

Inspected by 审核人:

(Department Manager 部门经理)



Dylan Dou 窦明波

Seal of CMC:

CMC 印章:



Date of Issue:

签发日期:

2026.01.01

CMC Testing International (Shenzhen) Co., Ltd.

众检检验认证(深圳)有限公司

Material Safety Data Sheet

材料安全数据表

Section 1- Identification of the Substance/Preparation and of the Company/Undertaking

第一部分 物质及企业标识

Name of Sample 样品名称	Cylindrical Lithium-ion Rechargeable Cell 圆柱形锂离子可充电电池	Weight 重量	39.5g
		Size 尺寸(D×H)	(18.3×65.6)mm
Model 型号	HYLN IMR18650-1500mAh		
Manufacturer 制造商	Henan Hengyi lithium energy technology Co., Ltd 河南恒一锂电科技有限公司		
Manufacturer's Address 制造商地址	Building 3, Xinhua Industrial Park, Longmen Avenue, Xinhua District, Pingdingshan City, Henan, P.R.China 中国河南平顶山市新华区龙门大道新华区产业园 3 号楼		
Contact Person 联系人	Mr. Li 李先生		
E-mail 邮箱	546800169@qq.com		
Fax 传真	--		
24h Emergency Phone No. 24h 紧急联络电话	+86-13525376185		

Section 2- Hazards Identification

第二部分 危险性概述

Classification of Danger 危险性类别	See section 14. 见第十四部分。
Primary Route(s) of Exposure 侵入途径	Eye, skin contact, ingestion. 眼睛，皮肤接触，摄入。
Health Hazard 健康危害	The batteries are not hazardous when used according to the instructions of manufacturer under normal conditions. In case of abuse, there's Hazard of rupture, fire, heat, leakage of internal components, which could cause casualty loss. Abuses including but not limited to the following cases: charged for long time, short circuited, put into fire, whacked with hard object, punctured with acute object, crushed, and broken. 正常条件下根据制造商的说明使用电池不会产生危害。使用不当的情况下，有破裂、起火、发烫、内部成分泄漏的危险，并可能造成意外损失。使用不当的行为包括但不限于下列情况：长时间充电、短路、投入火中、硬物撞击、尖物刺破、破碎，和破裂。

Section 3- Composition/Information on Ingredients

第三部分 成分/组成信息

Chemical Name 化学名称	Concentration or concentration ranges (%) 浓度或浓度范围(%)	CAS Number CAS 号(化学文摘索引登记号)
Lithium nickel cobalt Al 镍钴铝酸锂	39.5	113066-89-0
Carbon Black 炭黑	1.44	1333-86-4
Polyvinylidene Fluoride (PVDF) 聚偏氟乙烯	0.7	24937-79-9
Graphite 石墨	20.6	7782-42-5
Carboxymethyl cellulose 羧甲基纤维素	0.39	9004-32-4
Styrene-Butadiene Rubber (SBR) 丁苯橡胶	0.49	9003-55-8
Polyethylene 聚乙烯	2.24	9002-88-4
Lithium hexafluorophosphate 六氟磷酸锂	14.38	21324-40-3
Copper 铜	9.34	7440-50-8
Aluminum 铝	3.39	7429-90-5
Nickel 镍	0.93	7440-02-0
Fe 铁	6.6	7439-89-6

Labeling according to EC directives.

标签根据 EC 指令。

No symbol and Hazard phrase are required.

不需要象形符号和危险短语。

Note: CAS number is Chemical Abstract Service Registry Number.

注意: CAS 号是化学文摘服务注册号码。

N/A=Not apply.

N / A=不适用。

Section 4- First Aid Measures

第四部分 急救措施

Eye 眼睛	Flush eyes with plenty of water for at least 15 minutes, occasionally lifting the upper and lower eyelids. Get medical aid. 万一接触，立即用大量的清水冲洗至少 15 分钟，翻起上下眼睑，直到化学的残留物消失为止，迅速就医。
Skin 皮肤	Remove contaminated clothes and rinse skin with plenty of water or shower for 15 minutes. Get medical aid. 万一接触，用大量水冲洗至少 15 分钟，同时除去污染的衣物和鞋子，迅速就医。
Inhalation 吸入	Remove from exposure and move to fresh air immediately. Use oxygen if available. 立即从暴露处移至空气清新处，如果呼吸困难给予输氧，立即就医。
Ingestion 食入	Induce vomiting unless patient is unconscious. Call a physician. 如果当事人仍然清醒可以采取催吐的方法，并且立即就医。

Section 5- Fire Fighting Measures

第五部分 消防措施

Characteristics of Hazard 危险特性	The product causes burns of eyes, skin and mucous membranes. Thermal decomposition can lead to release of irritating gases and vapors. 该产品会导致眼睛，皮肤和粘膜灼伤。热分解可能导致释放刺激性气体和蒸汽。
Hazardous Combustion Products 燃烧产生的危险物品	Carbon dioxide. 二氧化碳。
Fire-extinguishing Methods and Extinguishing Media 灭火方法及灭火剂	Use extinguishing measures that are appropriate to local circumstances and the surrounding environment. 使用适合当地情况和周围环境的灭火措施。
Attention in Fire-extinguishing 灭火注意事项	Wear self-contained breathing apparatus in pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear. 因为压强关系，要穿戴可呼吸式全身防护装备，MSHA/NIOSH（经认证或等效的），以及佩戴全套防护装置。

Section 6- Accidental Release Measures

第六部分 泄露应急处理

Personal Precautions, protective equipment, and emergency procedures 个人预防措施、防护装备和应急程序	In case of rupture. Attention! Corrosive material. Avoid contact with skin, eyes and clothing. Ensure adequate ventilation. Use personal protective equipment as required. Evacuate personnel to safe areas. Keep people away from and upwind of spill/leak. Refer to protective measures listed in Sections 7 and 8. 万一破裂。注意！腐蚀性物质。避免接触皮肤，眼睛或衣服。确保空气流通。根据需要，使用个人防护装备。将人员撤离到安全区域。让人们远离溢出/泄漏处和处于逆风。参考第七部分和第八部分中列出的防护措施。
Environmental Precautions 环境保护措施	Prevent product from contaminating soil and from entering sewers or waterways. 防止产品污染土壤和进入下水道或水道。

Methods and materials for Containment 方法和材料控制	Stop the leak if safe to do so. Contain the spilled liquid with dry sand or earth. Clean up spills immediately. 出于安全, 阻止泄漏, 可以用干砂或泥土来遏制液体溢出, 立即清理溢出物。
Methods and materials for cleaning up 清理的方法和材料	Absorb spilled material with an inert absorbent (dry sand or earth). Scoop contaminated absorbent into an acceptable waste container. Collect all contaminated absorbent and dispose of according to directions in Section 13. Scrub the area with detergent and water; collect all contaminated wash water for proper disposal. 用惰性吸收剂(干砂或泥土)吸收溢出的材料。污染物转移到可接受的废物容器中。收集所有受污染的吸收剂, 按照第十三部分的说明进行处理。用洗涤剂和水清洁污染区域, 收集所有受污染的洗涤水, 妥善处理。

Section 7- Handling and Storage

第七部分 操作处置与储存

Handling 操作	The battery may explode or cause burns, if disassembled, crushed or exposed to fire or high temperatures. Do not short or install with incorrect polarity. 拆解、挤压、直接放入火中或高温条件下, 电池可能发生爆炸和燃烧。禁止短路或将电池正负极错误的安装在设备中。
Storage 储存	Store in a cool, dry, well-ventilated area away from incompatible substances. Store locked up. Keep out of the reach of children. 储藏于阴凉, 干燥, 通风处, 远离接触会发生反应的材料。存储锁定。放在儿童无法接触的地方。
Other Precautions 其他要注意的防范措施	In case of rupture. Handle in accordance with good industrial hygiene and safety practice. Avoid contact with skin, eyes or clothing. Use personal protection equipment. 万一破裂。按照良好的工业卫生和安全规范进行操作。避免接触皮肤, 眼睛或衣服。使用个人防护设备。

Section 8 - Exposure Controls/Personal Protection

第八部分 接触控制和个体防护

Engineering Controls 工程控制	Use adequate ventilation to keep airborne concentrations low. If used under conditions that generate particulates, the ACGIH TLV-TWA of 3mg/m ³ respirable fraction (10mg/m ³ total) should be observed. 保证空气流通使空气密度保持在低水平。如果在会生成微粒的情况下使用, 应仔细观察 3mg/m ³ ACGIH TLV-TWA 3 的吸入量 (总量为 10mg/m ³)。
Personal Protective Equipment 个人防护设备	Eye and Face Protection: None required for consumer use. If there is a Hazard of contact: Tight sealing safety goggles. Face protection shield. 眼睛和脸部保护: 消费者无需使用。如果有接触危险: 密封安全护目镜。面部防护罩。 Skin and Body Protection: None required for consumer use. If there is a Hazard of contact: Wear protective gloves and protective clothing. 皮肤和身体防护: 消费者无需使用。如果有接触危险: 穿戴防护手套和防护服。 Respiratory Protection: No protective equipment is needed under normal use conditions. If exposure limits are exceeded or irritation is experienced, ventilation and evacuation may be required. 呼吸系统防护: 正常使用条件下不需要防护设备。如果超过暴露限值或发生刺激, 可能需要通风和疏散。

Section 9- Physical and Chemical Properties

第九部分 理化特性

Physical State 物理状态	Appearance: Cylinder 外形: 圆柱体
	Color: Multi-colors 颜色: 多种颜色
	Odour: If leaking, smells of medical ether. 气味: 泄漏时, 医用乙醚的气味。
Change in condition: 变化的条件:	
pH 酸碱度	Not applicable as supplied. 不适用。
Flash Point 闪点	Not applicable unless individual components exposed. 除非单个的组件暴露, 否则不适用。
Flammability 易燃度	Not applicable unless individual components exposed. 除非单个的组件暴露, 否则不适用。
Relative density: 相对密度	Not applicable unless individual components exposed. 除非单个的组件暴露, 否则不适用。
Solubility (water) 溶解性 (水溶性)	Not applicable unless individual components exposed. 除非单个的组件暴露, 否则不适用。
Solubility (other) 溶解性 (其他)	Not applicable unless individual components exposed. 除非单个的组件暴露, 否则不适用。

Section 10 – Stability and Reactivity

第十部分 稳定性和反应性

Chemical Stability 化学稳定性	Stable under recommended storage conditions. 在推荐的储存条件下可以保持稳定。
Possibility of Hazardous Reactions 危险反应的可能性	None under normal processing. 正常处理下没有。
Conditions to Avoid 应避免的条件	Exposure to air or moisture over prolonged periods. 暴露在空气中或长时间受潮。
Incompatible materials 不相容材料	Acids, Oxidizing agents, Bases. 酸, 氧化剂, 碱。
Hazardous Decomposition Products 有危害分解物	Carbon oxides. 二氧化碳。

Section 11 – Toxicological Information

第十一部分 毒理学信息

Irritation 刺激	In the event of exposure to internal contents, vapour fumes may be very irritating to the eyes and skin. 内部物质暴露的情况下，蒸汽烟雾可能对眼睛和皮肤的刺激性。
Sensitization 致敏	Not Available. 不适用。
Reproductive Toxicity 再生毒性	Not Available. 不适用。
Toxicologically Synergistic Materials 协同材料毒理学	Not Available. 不适用。

Section 12-Ecological Information

第十二部分 生态学信息

General note: 通用信息:	Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system. 不允许未稀释或大量的产品接触地下水、水道或污水处理系统。
Anticipated behavior of a chemical product in environment/possible environmental impact/ecotoxicity 化学产品在环境/可能的环境预期的行为的一种生态毒性	Not Available. 不适用。

Section 13 – Disposal Considerations

第十三部分 废弃处置

Waste Treatment 废弃处置方法	Recycle or dispose of in accordance with government, state & local regulations. 建议遵照国家和地方法规处置或再利用。
Attention for Waste Treatment 废弃注意事项	Deserted batteries shouldn't be treated as ordinary trash. Shouldn't be thrown into fire or placed in high temperature. Shouldn't be dissected, pierced, crushed or treated similarly. Best disposal method is recycling. 废电池不能被当作普通垃圾。不能扔进火中或置于高温下。不能解体，刺穿，破碎或类似的处理。最好的处理办法是回收利用。

Section 14 – Transport Information

第十四部分-运输信息

ICAO / IATA: 国际民间航空组织/国际航空运输协会:	Can be shipped by air in accordance with International Civil Aviation Organization (ICAO), TI or International Air Transport Association (IATA), DGR Packing Instructions (PI) 965 Section IB, PI 966 Section II and PI 967 Section II appropriate of IATA DGR 67th (2026 Edition) for transportation. 货物可根据民用航空组织 (ICAO), TI 或国际航空运输协会 (IATA), DGR 67th (2026 版) 包装说明 (PI) 965 Section IB, PI 966 Section II 和 PI 967 Section II 相关规定进行空运。		
UN number 联合国货物编号 (UN 编号)	UN3480		
Proper Shipping Name 运输专用名称	Lithium ion batteries 锂离子电池		
Remark 备注	Suggested limited to a maximum of 30% SoC 荷电状态不得超过其额定容量的 30%		
Class or Div 危险性类别	9	Packing grade 包装等级	/
UN number 联合国货物编号 (UN 编号)	UN3481		
Proper Shipping Name 运输专用名称	Lithium ion batteries packed with equipment / 锂离子电池与设备包装在一起 Lithium ion batteries contained in equipment / 锂离子电池安装在设备中		
Class or Div 危险性类别	9	Packing grade 包装等级	/
Special precautions which a user needs to be aware of, or needs to comply with, in connection with transport or conveyance either within or outside their premises. 无论是对内还是对外的运输或运输方式, 用户都需要注意或遵守的特殊预防措施。			
IMDG CODE 国际海运危险货物规则	The batteries are not restricted to IMDG Code 2024 Edition (Amdt 42-24) according to special provision 188. 根据特殊规定 188, 该电池不受 IMDG Code 2024 版 (Amdt 42-24) 限制。		
UN number 联合国货物编号 (UN 编号)	UN3480/UN3481		
Proper Shipping Name 运输专用名称	Lithium ion batteries / 锂离子电池 Lithium ion batteries packed with equipment / 锂离子电池与设备包装在一起 Lithium ion batteries contained in equipment / 锂离子电池安装在设备中		
Class or Div 危险性类别	9	Packing grade 包装等级	/
EmS No. 危险品应急措施编号	F-A: 一般灭火程序 S-I: 易燃固体 (可重包装)		
ADR/ ADN 欧洲国际陆运危险货物协定 / 关于内陆水道国际运输危险货物的欧洲协定:	The batteries are not subject to the provisions of United Nations Economic Commission for Europe (UNECE) ADR/ADN if they meet the requirements of special provision 188 of Chapter 3.3. Applicable as from 1 January 2025. 自 2025 年 1 月 1 日起适用于联合国欧洲经济委员会 (UNECE) ADR / ADN, 如果电池符合第 3.3 章第 188 条的特殊要求, 则电池不受限制。		

In addition, to be permitted in transport each lithium cell and battery types must have passed the applicable tests set out in Subsection 38.3 of the UN Manual of Tests and Criteria. The batteries should be well protected against short circuits.

此外，每个锂电芯和电池类型都必须通过联合国《试验和标准手册》第 38.3 节规定的适用测试。电池应做好防短路措施。

Section 15 – Regulatory Information

第十五部分 法规信息

Dangerous Goods Regulations

《危险物品规则》

Recommendations on the Transport of Dangerous Goods-Model Regulations (24th revised edition)

联合国《关于危险货物运输的建议书 规章范本》（24th 修订版）

UNITED NATIONS "Manual of Tests and Criteria"

联合国《试验和标准手册》

International Air Transport Association (IATA)

《国际航空运输协会》（IATA）

International Maritime Dangerous Goods (IMDG Code 2024 Edition Amdt 42-24)

《国际海运危险货物规则》（IMDG Code 2024 版 Amdt 42-24）

Technical Instructions for the Safe Transport of Dangerous Goods

《危险货物安全运输技术指南》

Classification and code of dangerous goods (GB 6944-2012)

《危险货物分类和品名编号》- GB 6944-2012

2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

2012《职业安全与健康标准》危险通信标准（29 CFR 1910.1200）

Toxic Substance Control Act (TSCA)

《有毒物质控制法》（TSCA）

Code of Federal Regulations

《联邦条例》

In accordance with all Federal, State and local laws

符合所有联邦、州和地方法律


Section 16 – Additional Information

第十六部分 其他信息

MSDS creation date: 2026

Version: 1.0

Sample photo 样品照片:



To the best of our knowledge, the information contained herein is accurate. However, neither the above named supplier nor any of its subsidiaries assumes any liability whatsoever for the accuracy or completeness of the information contained herein. Final determination of suitability of any material is the sole responsibility of the user. All materials may present unknown hazards and should be used with caution. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that exist.

本份 MSDS 中的信息只是基于我们当前所拥有的相关材料的信息而编制的，只是为了描述本品的健康、安全与环境需求，以使各有关方面能更好地了解和信任本产品。这些信息只是提供给您，以供考虑、研究和确认。其中的一些危害预防措施描述并非是唯一的。所以本份 MSDS 不能作为使用本品实现任何特定目的的保证。各有关使用者有责任预先完成本品的安全性及其他方面的测试，以评判其是否满足您的使用目的。

*****End of report*****

*****报告结束*****

Testing laboratory: CMC Testing International (Shenzhen) Co., Ltd.

检测单位: 众检检验认证(深圳)有限公司

Address: 1-3/F., Building 7, He'er Hongben Industrial Zone, Dawangshan Community, Shajing Subdistrict, Baoan District, Shenzhen, Guangdong, China

地址: 广东省深圳市宝安区沙井街道大王山社区和二鸿奔工业区 7 栋一层二层三层

Tel (电话): 400-1668-320 E-mail: info@cmczi-lab.com <http://www.cmczi-lab.com>