



MOTICAM S Series

MOTICAM S20 Plus





MOTICAM S Series

MOTICAM S20 Plus

Sensor type	Sony Exmor R back-illuminated SCMOS
Sensor size	1"
Imaging area	15.86mm (Diagonal)
Capture resolution	20MP
Live display mode through USB	5472x3648, 2736x1824 pixels
Pixel size	2.4x2.4µm
Scan mode	Progressive
Shutter Mode	Rolling shutter
Data transfer	USB 3.1
Max. frames per second (fps)	5440x3648 @ 15fps, 2736x1824 @ 50fps, 1824x1216 @ 60fps
Exposure time	15 µsec to 2 sec
Operating temperature	From -10 to +60 Degrees Celsius non condensing
Sensitivity	461mV(G) @ 1/30 sec
Support device	TWAIN, SDK and DirectShow Driver
Supported OS	Windows 7/8/10, MAC OSX, Linux or higher
Minimum computer requirements	2GHz dualcore - RAM memory 2GB - Video memory min. 512 MB
Lens mount	C-Mount
Software	Motic Images Plus 3.1 for Windows 10, MAC OSX10.9, Linux UBUNTU1604 or higher
Functions	Still image and video capture, live and still image measurement, image adjustments, white balance, automatic & manual exposure, individual objective calibration system.
Power supply	5V (From USB Port)
Package includes	CS ring adaptor, USB 3.1 cable, Motic 4-dot calibration slide, Motic Images Plus 3.1 for PC/OSX/Linux

**Frames per second under optimal lighting conditions and in compliance with computer technical requirements.*