



Revision Number: 001.1

Issue date: 03/12/2020

1. PRODUCT AND COMPANY IDENTIFICATION


Product name:	LOCTITE SI 5019 BL AE 190ML EV	IDH number:	2634174
Product type/use:	Silicone	Item number:	2634174
Restriction of Use:	None identified	Region:	United States
Company address:	Contact information:		
Henkel Corporation	Telephone: +1 (860) 571-5100		
One Henkel Way	MEDICAL EMERGENCY Phone: Poison Control Center		
Rocky Hill, Connecticut 06067	1-877-671-4608 (toll free) or 1-303-592-1711		
	TRANSPORT EMERGENCY Phone: CHEMTREC		
	1-800-424-9300 (toll free) or 1-703-527-3887		
	Internet: www.henkelna.com		

2. HAZARDS IDENTIFICATION

EMERGENCY OVERVIEW

WARNING: CONTAINS GAS UNDER PRESSURE; MAY EXPLODE IF HEATED.
CAUSES SKIN IRRITATION.
CAUSES SERIOUS EYE IRRITATION.

HAZARD CLASS	HAZARD CATEGORY
GASES UNDER PRESSURE	Compr. Gas
SKIN IRRITATION	2
EYE IRRITATION	2A



Precautionary Statements

Prevention: Wash affected area thoroughly after handling. Wear protective gloves, eye protection, and face protection.

Response: IF ON SKIN: Wash with plenty of water. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If skin irritation occurs: Get medical attention. If eye irritation persists: Get medical attention. Take off contaminated clothing.

Storage: Protect from sunlight. Store in a well-ventilated place.

Disposal: Not prescribed

Classification complies with OSHA Hazard Communication Standard (29 CFR 1910.1200) and is consistent with the provisions of the United Nations Globally Harmonized System of Classification and Labeling of Chemicals (GHS).

See Section 11 for additional toxicological information.

3. COMPOSITION / INFORMATION ON INGREDIENTS

Hazardous Component(s)	CAS Number	Percentage*
Silicon dioxide	7631-86-9	5 - 10
1,1-Difluoroethane	75-37-6	1 - 5
29H,31H-phthalocyaninato(2-)-N29,N30,N31,N32 copper	147-14-8	1 - 5
Methylsilanetriyl triacetate	4253-34-3	0.1 - 1
Triacetoxyethylsilane	17689-77-9	0.1 - 1

* Exact percentages may vary or are trade secret. Concentration range is provided to assist users in providing appropriate protections.

4. FIRST AID MEASURES

Inhalation:	Move to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. If symptoms develop and persist, get medical attention.
Skin contact:	Wash with soap and water. Wash clothing before reuse. If symptoms develop and persist, get medical attention.
Eye contact:	Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. If symptoms develop and persist, get medical attention.
Ingestion:	Do not induce vomiting. Get medical attention. Never give anything by mouth to an unconscious person.
Symptoms:	See Section 11.

5. FIRE FIGHTING MEASURES

Extinguishing media:	Foam, dry chemical or carbon dioxide.
Special fire fighting procedures:	Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear. Water should be used to cool closed containers to prevent pressure build-up and possible autoignition or explosion when exposed to extreme heat.
Unusual fire or explosion hazards:	Contents under pressure. Do not puncture or incinerate pressurized containers.
Hazardous combustion products:	Oxides of carbon. Oxides of silicon. Formaldehyde. Irritating organic vapours.

6. ACCIDENTAL RELEASE MEASURES

Use personal protection recommended in Section 8, isolate the hazard area and deny entry to unnecessary and unprotected personnel.

Environmental precautions:	Do not allow product to enter sewer or waterways.
Clean-up methods:	Ensure adequate ventilation. Wear appropriate personal protective equipment. Keep unnecessary personnel away. Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, saw dust). Scrape up as much material as possible. Store in a partly filled, closed container until disposal. Refer to Section 8 "Exposure Controls / Personal Protection" prior to clean up.

7. HANDLING AND STORAGE

Handling:	Prevent contact with eyes, skin and clothing. Do not breathe vapor and mist. Wash thoroughly after handling. Do not puncture or incinerate pressurized containers. Refer to Section 8.
Storage:	Keep in a cool, well ventilated area away from heat, sparks and open flame. Keep container tightly closed until ready for use.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Employers should complete an assessment of all workplaces to determine the need for, and selection of, proper exposure controls and protective equipment for each task performed.

Hazardous Component(s)	ACGIH TLV	OSHA PEL	AIHA WEEL	OTHER
Silicon dioxide	6 mg/m ³ TWA	20 MPPCF TWA 0.8 mg/m ³ TWA	None	3 mg/m ³ TWA Respirable fraction.
1,1-Difluoroethane	None	None	1,000 ppm (2,700 mg/m ³) TWA	None
29H,31H-phthalocyaninato(2-)-N29,N30,N31,N32 copper	0.2 mg/m ³ TWA (as Cu) Fume. 1 mg/m ³ TWA (as Cu) Dust and mist.	None	None	None
Methylsilanetriyl triacetate	None	None	None	None
Triacetoxethylsilane	None	None	None	None

Engineering controls:	Provide adequate local exhaust ventilation to maintain worker exposure below exposure limits.
Respiratory protection:	Use NIOSH approved respirator if there is potential to exceed exposure limit(s).
Eye/face protection:	Safety goggles or safety glasses with side shields. Safety showers and eye wash stations should be available.
Skin protection:	Use chemical resistant, impermeable clothing including gloves and either an apron or body suit to prevent skin contact.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical state:	Aerosol
Color:	Blue
Odor:	Acetic acid
Odor threshold:	Not available.
pH:	Not available.
Vapor pressure:	Not available.
Boiling point/range:	Not available.
Melting point/range:	Not available.
Specific gravity:	1.03
Vapor density:	Not available.
Flash point:	< -50 °C (< -58°F) ASTM D3278 Setaflash Closed Cup
Flammable/Explosive limits - lower:	Not available.
Flammable/Explosive limits - upper:	Not available.
Autoignition temperature:	Not available.
Flammability:	Not applicable
Evaporation rate:	Not available.
Solubility in water:	Not available.
Partition coefficient (n-octanol/water):	Not available.
VOC content:	3.90 %
Viscosity:	Not available.
Decomposition temperature:	Not available.

10. STABILITY AND REACTIVITY

Stability:	Stable under normal conditions of storage and use.
Hazardous reactions:	None under normal processing.
Hazardous decomposition products:	Oxides of carbon. Oxides of silicon. Formaldehyde. Irritating organic vapours.
Incompatible materials:	Not available.
Reactivity:	Not available.
Conditions to avoid:	Do not puncture, incinerate, or expose to temperatures above 48.9 °C (120 °F). Heat, flames, sparks and other sources of ignition. Store away from incompatible materials.

11. TOXICOLOGICAL INFORMATION

Relevant routes of exposure: Skin, Inhalation, Eyes, Ingestion

Potential Health Effects/Symptoms

Inhalation: Inhalation of vapors or mists of the product may be irritating to the respiratory system. When heated to temperatures exceeding 300° F (150° C) in the presence of air, silicones may form formaldehyde vapors. Formaldehyde is a potential cancer hazard and a known skin and respiratory sensitizer. Vapors irritate the eyes, nose and throat. Safe handling conditions may be maintained by keeping formaldehyde vapor concentrations below the OSHA permissible limit. Acetic acid produced during cure may irritate eyes, nose and throat.

Skin contact: Causes skin irritation.

Eye contact: Causes serious eye damage.

Ingestion: May cause gastrointestinal tract irritation if swallowed.

Hazardous Component(s)	LD50s and LC50s	Immediate and Delayed Health Effects
Silicon dioxide	Oral LD50 (Rat) = > 22,500 mg/kg Oral LD50 (Mouse) = > 15,000 mg/kg	Nuisance dust
1,1-Difluoroethane	None	Cardiac, Central nervous system, Developmental, Irritant, Respiratory
29H,31H-phthalocyaninato(2-)-N29,N30,N31,N32 copper	None	No Target Organs
Methylsilanetriyl triacetate	None	Irritant, Allergen
Triacetoxylethylsilane	None	No Target Organs

Hazardous Component(s)	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen (Specifically Regulated)
Silicon dioxide	No	No	No
1,1-Difluoroethane	No	No	No
29H,31H-phthalocyaninato(2-)-N29,N30,N31,N32 copper	No	No	No
Methylsilanetriyl triacetate	No	No	No
Triacetoxylethylsilane	No	No	No

12. ECOLOGICAL INFORMATION

Ecological information: Not available.

13. DISPOSAL CONSIDERATIONS

Information provided is for unused product only.

Recommended method of disposal: Follow all local, state, federal and provincial regulations for disposal.

Hazardous waste number: D001: Ignitable.

14. TRANSPORT INFORMATION

The transport information provided in this section only applies to the material/formulation itself, and is not specific to any package/configuration.

U.S. Department of Transportation Ground (49 CFR)

Proper shipping name: Aerosols
Hazard class or division: 2.1
Identification number: UN 1950
Packing group: None

International Air Transportation (ICAO/IATA)

Proper shipping name: Aerosols, flammable
Hazard class or division: 2.1
Identification number: UN 1950
Packing group: None
Exceptions: ID8000, (Not more than 500 ml), May Qualify as Consumer Commodity

Water Transportation (IMO/IMDG)

Proper shipping name: AEROSOLS
Hazard class or division: 2.1
Identification number: UN 1950
Packing group: None
Exceptions: Limited quantity (Not more than 1 L).

15. REGULATORY INFORMATION**United States Regulatory Information**

TSCA 8 (b) Inventory Status: All components are listed as active or are exempt from listing on the Toxic Substances Control Act (TSCA) inventory.

TSCA 12 (b) Export Notification: None above reporting de minimis

CERCLA/SARA Section 302 EHS: None above reporting de minimis.
CERCLA/SARA Section 311/312: Immediate Health, Delayed Health, Fire, Pressure
CERCLA/SARA Section 313: None above reporting de minimis.

California Proposition 65: This product contains a chemical known to the State of California to cause birth defects or other reproductive harm.

Canada Regulatory Information

CEPA DSL/NDSL Status: All components are listed on or are exempt from listing on the Canadian Domestic Substances List.

16. OTHER INFORMATION

This safety data sheet contains changes from the previous version in sections: 2,3,8,11,15

Prepared by: Product Safety and Regulatory Affairs

Issue date: 03/12/2020

DISCLAIMER: The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation and its affiliates ("Henkel") does not assume responsibility for any results obtained by persons over whose methods Henkel has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any Henkel's products. In light of the foregoing, Henkel specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel's products. Henkel further disclaims any liability for consequential or incidental damages of any kind, including lost profits.

This Safety Data Sheet has been generated based on OSHA Hazard Communication Standard (29 CFR 1910.1200) and provides information in accordance with U.S. federal law only. No warranty or representation of any kind is given with respect to the substantive or export laws of any other jurisdiction or country. Please confirm that the information provided herein conforms to the substantive export or other law of any other jurisdiction prior to export. Please contact Henkel Product Safety and Regulatory Affairs for additional assistance.