



TEGERA® INFINITY 8806

Learn more

SOFT, KNUCKLE DIPPED CUT B GLOVE

Dexterous cut resistant glove, level B, suitable for precision work. Ultra-light thanks to 18 gg knitted with CRF® cut resistant technology. Knuckle dipped with super soft nitrile foam and coated palm that provides good grip on greasy and oily surfaces. Reinforced thumb crotch for improved longevity. Protection against contact heat up to 100°C/212°F. Skin friendly with Derma-test and Oeko-Tex certificate.

CHARACTERISTICS

- Good fingertip sensitivity
- Flexible
- Durable
- Good grip
- Comfortable

FUNCTIONS

- Withstands contact heat up to 100°C
- Approved for handling foodstuffs
- Reinforcement between index finger and thumb
- Oil and grease resistant
- Thin

CRF®

ORIGINAL EXCELLENT dermatest 2019 dermatest-guarantee.de

OEKO TEX® STANDARD 100 SE 14-214 RISE

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Cut injuries, Abrasion injuries, Blisters, Grazes, Scratches, lacerations, Contact with dirt, Drying out, Chapping, Contact with oil and fat

PRIMARY ENVIRONMENTS OF USE

Cut risk environments, Moist environments, Oily and greasy environments, Dirty environments

PRIMARY AREAS OF USE

Fine assembly, Assembly, Machine operating, Building and construction, Carpentry, Installation work, HVAC installation, Sheet-metal work, Engineering, Transport work, Machine driving, Warehouse work, Airport work, Metalwork, Glass industry work, Repair work, Paper industry work, Service work, Shop work

PRIMARY INDUSTRIES OF USE

Agriculture, forestry and fishing, Automotive manufacturing, Automotive repair and maintenance, Basic metals manufacturing, Building and construction, Electrical equipment manufacturing, Electricity and gas supply, Facility management services, Glass, ceramics and construction materials, Machinery and equipment manufacturing, Metal manufacturing and fabrication, Mining and quarrying, Public safety, security and defence, Pulp and paper, Retail and wholesale, Transport equipment manufacturing, Transportation and logistics, Warehousing

TYPE OF WORK

Medium weight

SPECIFICATION

TYPE Cut resistant gloves, Heat protection gloves
CATEGORY Cat. II
COLLECTION Infinity
KNITTING GAUGE (GG) 18
LINING MATERIAL Carbon, CRF® Technology, HPPE, Nylon, Stainless steel fibre yarn
LENGTH 220-270 mm
DEXTERITY 5
GRIP DESIGN Foam grip pattern
COLOUR Grey
PAIRS PER: BUNDLE/CARTON 6/120
DISPLAY TYPE Bulk pack
DIPPING 3/4 dipped
DIPPING MATERIAL Nitrile, Nitrile foam, Waterbased PU
CUFF STYLE Knitwrist cuff
CUFF MATERIAL Textile
CUT RESISTANCE (EN ISO 13997) Cut resistance level B
CUT RESISTANCE (EN ISO 13997) TDM: 9.1 N
INNER MATERIAL SPECIFICATION Nylon, HPPE (High performance polyethylene), Stainless steel fibre yarn, Carbon thread
OUTER MATERIAL SPECIFICATION Nitrile

COMPLIANCE

CE Cat. II
TP TC 019:2011

UKCA Cat. II
EN ISO 21420:2020

EAC

EN 388:2016+A1:2018 4X42B

EN 407:2020 (No flame protection) X1XXXX

ANSI A2 CUT

ANSI 4 ABR

Contact heat rating valid for palm area only

FEATURES

Cut protection

SIZE		ARTICLE NUMBER	EAN
6	XS	8806-6	7340118384191
7	S	8806-7	7340118319506
8	M	8806-8	7340118319513
9	L	8806-9	7340118319520
10	XL	8806-10	7340118319483
11	XXL	8806-11	7340118319490

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.