ABB BALDOR RELIANCE

Customer information packet

EM4108T-G

30HP, 3520RPM, 3PH, 60HZ, 286TS, 0950M, TEFC, F
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/5/2026 3:15:43 PM

Specifications

Enclosure	TEFC
Frame	286TS
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	30.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
	230.0 V @ 60 HZ
Agency Approvals	CSA
	CSA EEV
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	68.000 A @ 230.0 V
	74.000 A @ 208.0 V
	34.000 A @ 460.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.7 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None

Part Detail

Revision	L
Type	AC
Mech. spec.	09J963
Base	
Status	PRD/A
Elec. spec.	09WGT474
Layout	09LYJ963
Eff. date	06-27-2024
CD Diagram	CD0180
Poles	02
Leads	9#10
Proprietary	False
Created date	11-09-2017

Heater Indicator	No Heater
High Voltage Full Load Amps	34.0 a
Insulation Class	H
Inverter Code	Inverter Ready
KVA Code	J
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 10 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0950M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	24.70 IN
Power Factor	89
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	3520 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None

Winding Thermal 2	None

Nameplate

NP3443LUA											
CAT.NO.	EM4108T-G			**CUST. P/N**						**ENCL**	TEFC
SPEC.	09J963T474G1	**CC**	010A	**FRAME**	286TS		**SER.NO.**				
HP	30		**CLASS**	H	**HZ**	60					
R.P.M.	3520		**PH.**	3	**DES.**	A					
VOLTS	230/460			**CODE**	J		**ODE BRG**	6208	**DE BRG**	6311	
AMPS	68/34										
RATING	40C AMB-CONT			**NEMA NOM. EFF.**	91.7			**GREASE**	POLYREX EM		
P.F.	89	**SER.F.**	1.15	**CT6-60H(10:1)VT3-60H(20:1**							
USABLE AT	50HZ 30HP 190/380V 82/41A			SF1.0							
VOLTS	**AMPS**			**MAX. SPACE HEATER TEMP.**							

AC Induction Motor Performance Data
Record # 67901
Typical performance - not guaranteed values

Winding: 09WGT474-R003	**Type:** 0950M	**Enclosure:** TEFC

Nameplate Data			**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)		30	**Full Load Torque**	44.65 LB-FT
Volts		230/460	**Start Configuration**	direct on line
Full Load Amps		68/34	**Breakdown Torque**	173 LB-FT
R.P.M.		3520	**Pull-up Torque**	87.6 LB-FT
Hz	60 **Phase**	3	**Locked-rotor Torque**	104 LB-FT
NEMA Design Code	A **KVA Code**	J	**Starting Current**	283 A
Service Factor (S.F.)		1.15	**No-load Current**	10.9 A
NEMA Nom. Eff.	91.7 **Power Factor**	89	**Line-line Res. @ 25ºC**	0.2527 Ω
Rating - Duty		40C AMB-CONT	**Temp. Rise @ Rated Load**	79°C
S.F. Amps			**Temp. Rise @ S.F. Load**	97°C
			Locked-rotor Power Factor	28

Load Characteristics 460 V, 60 Hz, 30 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	58	78	86	89	90	91	90
Efficiency	87.7	91.8	92.4	92.1	91.3	90.2	91.6
Speed	3580.7	3562.2	3542.3	3521	3497.7	3471	3507
Line amperes	13.7	19.4	26.4	34.2	42.4	51.3	39.1


ABB Motors and Mechanical Inc.


WINDING # 09WGT474

30 HP 3 PH 60 HZ 3520 RPM 460 V 0950M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=173 PU=87.6 LR=104 LRA=283





09LYJ963
(932 - 964) = 2 POLE
(932 - 966) = 4, 6, & 8 POLE
24.77
11.27
3.37
3.25
NAMEPLATE
.38 KEY
1.88 LONG
Ø 1.625
1.624
V-RING
SLINGER
AUTO DRAIN
(EA. END)
8 HOLES
Ø .53
9.50
9.50
.92
11.00
4.75
12.84
13.63
12.20
6.63
2.73
13.63
7.00
6.94
LEAD HOLE
Ø 2.00
5.50
5.50
9.66
6.38
12.75
INT SH GND
BP5306
PU BRG RET DETAIL
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: LIFECYCLE, REPLACE 09SF1117A05 W/09SF1116A02
REV: F
VERSION: 06
REVISED: 03:14:50 02/21/2022
TDR: 000001186130
MODEL NO. 09LYJ963
REF: -
BY: ENFRAJ0
B
BALDOR - RELIANCE®
HORZ TEFC 284-6TS W/AEGIS INT SH GND
09LYJ963

CD0180







NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0180

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: D	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\148	REVISED: 10:25:29 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, DV, 9 LEADS, DELTA CONNECTION

SH 1 of 1