ABB BALDOR RELIANCE

Customer information packet

L3515T

2HP, 3450RPM, 1PH, 60HZ, 145T, 3535L, TEFC, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/5/2026 5:02:33 PM

Specifications

Enclosure	TEFC
Frame	145T
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Cap Start, Induction Run
Output @ Frequency	2.000 HP @ 60 HZ
Phase	1
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	115.0 V @ 60 HZ
	230.0 V @ 60 HZ
Agency Approvals	CURUS
	C UR US
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	11.500 A @ 230.0 V
	12.000 A @ 208.0 V
	23.000 A @ 115.0 V
Design Code	L
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	74.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater

Part Detail

Revision	Y
Type	AC
Mech. spec.	35Y521
Base	
Status	PRD/A
Elec. spec.	35WG0506
Layout	35LYY521
Eff. date	01-13-2026
CD Diagram	CD0001
Poles	02
Leads	4#14 A PH,2#18 B PH
Proprietary	False
Created date	12-07-2009

High Voltage Full Load Amps	11.5 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	K
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	4 @ 14 AWG, A PH
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3535L
Mounting Arrangement	F1
Number of Poles	2
Overall Length	14.16 IN
Power Factor	82
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	0.875 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	3450 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None

Winding Thermal 2	None

Nameplate

NP1256L									
CAT.NO.	L3515T								
SPEC.	35Y521-0506G1								
HP	2								
VOLTS	115/230								
AMP	23/11.5								
RPM	3450								
FRAME	145T	**HZ**	60			**PH**	1		
SER.F.	1.15	**CODE**	K	**DES**	L	**CLASS**	F		
NEMA-NOM-EFF	74	**PF**	82						
RATING	40C AMB-CONT								
CC									
DE	6205	**ODE**	6203						
ENCL	TEFC	**SN**							

Accessories

Part number	Description	Multiplier
35-8762	C FACE KIT	A8
35EP1506A01SP	D-FLANGE KIT	A8


AC Induction Motor Performance Data
Record # 20312
Typical performance - not guaranteed values


Winding: 35WG0506-R001	**Type:** 3535L	**Enclosure:** TEFC

Nameplate Data			**230 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)		2	**Full Load Torque**	3 LB-FT
Volts		115/230	**Start Configuration**	direct on line
Full Load Amps		23/11.5	**Breakdown Torque**	9 LB-FT
R.P.M.		3450	**Pull-up Torque**	6 LB-FT
Hz	60 **Phase**	1	**Locked-rotor Torque**	7.5 LB-FT
NEMA Design Code	L **KVA Code**	K	**Starting Current**	78 A
Service Factor (S.F.)		1.15	**No-load Current**	6 A
NEMA Nom. Eff.	74 **Power Factor**	82	**Line-line Res. @ 25ºC**	0.864 Ω A Ph 1.26 Ω B Ph
Rating - Duty		40C AMB-CONT	**Temp. Rise @ Rated Load**	82°C
S.F. Amps			**Temp. Rise @ S.F. Load**	91°C


Load Characteristics 230 V, 60 Hz, 2 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	50	65	75	81	85	87	83
Efficiency	49.1	64.2	70.5	73.4	74.3	74.1	73.9
Speed	3569	3548	3524	3499	3471	3438	3482
Line amperes	6.65	7.75	9.2	10.9	12.9	15.1	12.1


ABB Motors and Mechanical Inc.
WINDING # 35WG0506
2 HP 1 PH 60 HZ 3450 RPM 230 V 3535L
Typical performance - not guaranteed values.
TORQUES(LB-FT): PO=9 PU=6 LR=7.5 LRA=78
TORQUE
RPM
WATTS
AMPS
EFF
PF
%EFF %PF
TORQUE (LB-FT)
RPM
WATTS
AMPS
PERCENT OF RATED OUTPUT (2 HP)
11/5/2026 ACPERF, record # 20312


35LYY521
510-520 = 12.29
521-528 = 13.29
529-535 = 14.16
536-546 = 15.54
GREASE FITTING
(EA. END)
2.50
2.25
NAMEPLATE
.19 KEY
1.38 LONG
Ø7.19
Ø.8750
.8745
3.75
6 HOLES
Ø.34
4.00
2.25
5.00
.50
5.94
6.61
5.75
2.25
6.77
3.50
3.44
LEAD HOLE
Ø1.09
2.75
2.75
4.63
3.25
6.50
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: UPDATE 3D MODEL BOM PER REV D, NO CHG TO 2D PRINT
REV: C
VERSION: 03
REVISED: 01:19:00 03/09/2022
TDR: 000001187335
MODEL NO. 35LYY521
REF: -
BY: USBUFRA
B
BALDOR - RELIANCE®
STD HORZ 143-5T TEFC 35L 2 POLE "W" BASE, W/1.09 LEAD HOLE
SH 1 OF 1
35LYY521

CD0001



	LINE A	LINE B	JOIN
HIGH STD	1	4,5	2,3,8
HIGH OPP	1	4,8	2,3,5
LOW STD	1,3,8	2,4,5	–
LOW OPP	1,3,5	2,4,8	–

NOTES:

1. STANDARD ROTATION IS CCW FACING END OPPOSITE SHAFT EXTENSION.
2. OPTIONAL THERMOSTAT IS PROVIDED WHEN SPECIFIED.
3. MULTIPLE CAPACITORS ARE CONNECTED IN PARALLEL UNLESS OTHERWISE SPECIFIED.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: D	BY: JLP	REVISED: 04/08/99 1:16	TDR: 0178636
CD0001		FILE: AAA00007405	MDL: –
		MTL: –	TYPE L, DV, REV, 6 LEADS

CD0001