ABB BALDOR RELIANCE

Customer information packet

VXT3302TS

30HP, 3525RPM, 3PH, 60HZ, 286TSC, 1048M, TEFC
Class - CLI GP A,B,C,D
Division - Division II

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/5/2026 1:15:20 PM

Specifications

Enclosure	TEFC
Frame	286TSC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP A,B,C,D
Haz Area Division	Division II
Motor Letter Type	Three Phase
Output @ Frequency	30.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
	230.0 V @ 60 HZ
Agency Approvals	CCSA US
	CCSAUSEEV
	CSA EEV
	NEMA PREMIUM
	NEMA_PREMIUM
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	6
Current @ Voltage	68.000 A @ 230.0 V
	76.000 A @ 208.0 V
	34.000 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.7 %

Part Detail

Revision	G
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	10WGZ501
Layout	10LYE310
Eff. date	06-28-2024
CD Diagram	CD0180
Poles	02
Leads	9#10
Proprietary	False
Created date	08-03-2020

Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Haz Area Temp Code	T3
Heater Indicator	No Heater
High Voltage Full Load Amps	34.0 a
Insulation Class	F
Inverter Code	Inverter Duty
IP Rating	NONE
KVA Code	G
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	5400 rpm
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	1048M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	26.39 IN
Power Factor	90
Product Family	General Purpose
Pulley Face Code	C-Face
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Speed	3525 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP4163L									
CAT.NO.	VXT3302TS					**I.P.**	54		
SPEC.	10-0001436					**ENCL**	TEFC		
FRAME	286TSC		**H.P.**	30					
VOLTS	230/460		**P.F.**	90					
F.L. AMPS	68/34			**RATING**	40C AMB-CONT				
R.P.M.	3525								
HZ.	60	**PH.**	3	**CLASS**	F				
SER.F.	1.15	**DES.**	B	**SL HZ**	1.3				
NEMA NOM. EFF.	91.7	**WK2**	2.07						
DE	6311	**ODE**	6309						
MAG. CUR.	17.4/8.7								
INV TYPE	PWM	**CHP**	60	**TO**	90	**T. CODE**	T3		
CT	6	**TO**	60	**VT**	3	**TO**	60		
CC	010A	**SN**							
	USABLE AT 50HZ 25HP 190/380V								
	70/35A SF1.0								


AC Induction Motor Performance Data
Record # 55452
Typical performance - not guaranteed values


Winding: 10WGZ501-R001	**Type:** 1048M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			30	**Full Load Torque**	44.8 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			68/34	**Breakdown Torque**	135 LB-FT
R.P.M.			3520	**Pull-up Torque**	47 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	65.2 LB-FT
NEMA Design Code	B	**KVA Code**	G	**Starting Current**	212 A
Service Factor (S.F.)			1.15	**No-load Current**	8.74 A
NEMA Nom. Eff.	91.7	**Power Factor**	90	**Line-line Res. @ 25ºC**	0.24052 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	69°C
S.F. Amps				**Temp. Rise @ S.F. Load**	85°C
				Locked-rotor Power Factor	23.2


Load Characteristics 460 V, 60 Hz, 30 HP


% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	67	83	88	90	90	90	90
Efficiency	87	91.3	92	91.7	90.9	89.7	91.2
Speed	3583	3565.7	3547.3	3526.7	3504.4	3479.1	3513
Line amperes	12.4	18.7	26.1	34.1	43.1	52.5	39.5



ABB Motors and Mechanical Inc.
WINDING # 10WGZ501
30 HP 3 PH 60 HZ 3520 RPM 460 V 1048M
Typical performance - not guaranteed values.
TORQUES(LB-FT): PO=135 PU=47 LR=65.2 LRA=212
TORQUE
RPM
KW
AMPS
EFF
PF
%EFF %PF
TORQUE (LB-FT)
RPM
KW
AMPS
PERCENT OF RATED OUTPUT (30 HP)
11/5/2026 ACPERF, record # 55452


10LYE310
(1030-1060) = 26.43
12.93
3.00
GREASE & RELIEF (EA END)
.25
.38 KEY
2.00 LONG
Ø14.77
10.500
10.497
Ø1.625
1.624
11.16
SLINGER
15.50
13.19
7.59
45°
45°
3.00
LEAD HOLE Ø2.00
10.56
4 HOLES
.50-13 TAP
.88 DEEP
Ø9.00 BC.
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CONVERT AUTOCAD DRW TO SWD
REV: B
VERSION: 02
REVISED: 10:43:01 07/26/2023
TDR: 000001211833
MODEL NO. 10LYE310
REF: -
BY: ENALEM0
B
BALDOR - RELIANCE®
VERT TEFC 284-6TSC W/STL FAN COVER & 37FN3002A03
10LYE310

CD0180







NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0180

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: D	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\148	REVISED: 10:25:29 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, DV, 9 LEADS, DELTA CONNECTION

SH 1 of 1