

SAFETY DATA SHEET

Issuing Date 15-Dec-2011

Revision Date 16-Feb-2026

Revision Number 3



The supplier identified below generated this SDS using the UL SDS template. UL did not test, certify, or approve the substance described in this SDS, and all information in this SDS was provided by the supplier or was reproduced from publically available regulatory data sources. UL makes no representations or warranties regarding the completeness or accuracy of the information in this SDS and disclaims all liability in connection with the use of this information or the substance described in this SDS. The layout, appearance and format of this SDS is © 2014 UL LLC. All rights reserved.

1. IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

Product identifier

Product Name Wipex Odor Absorbing Gel

Other means of identification

Synonyms None

Recommended use of the chemical and restrictions on use

Recommended Use Air Freshener (Solid, Gel, Paper)

Uses advised against No information available

Details of the supplier of the safety data sheet

Supplier Name Punati Chemical Corp

Supplier Address 1160 N. Opdyke
Auburn Hills
MI
48326
US

Supplier Phone Number Phone:2482760101
Fax:2482760103

Supplier Email info@punati.com

Emergency telephone number

Company Emergency Phone Number 248-276-0101

2. HAZARDS IDENTIFICATION



Classification

This chemical is not considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200).

GHS Label elements, including precautionary statements**Emergency Overview**

The product contains no substances which at their given concentration, are considered to be hazardous to health.

Appearance Gel, multiple colors**Physical state** Solid Gel Consistency**Odor** Multiple fragrances**Precautionary Statements - Prevention**

Not applicable

Precautionary Statements - Response

None

Precautionary Statements - Storage

None

Precautionary Statements - Disposal

None

Hazards not otherwise classified (HNOC)

Not applicable

Unknown Toxicity

6.82 % of the mixture consists of ingredient(s) of unknown toxicity

Other information

PROLONGED OR REPEATED CONTACT MAY DRY SKIN AND CAUSE IRRITATION

May cause slight eye irritation

Interactions with Other Chemicals

No information available.

3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical name	CAS No	Weight-%	Trade Secret
Sodium stearate	822-16-2	3 - 7	
Propylene Glycol	57-55-6	1 – 2	
TRADE SECRET		~1	*
Water	7732-18-5	> 90	
Plant-based surfactant			*
Fragrance made with essential oils			*

*The exact percentage (concentration) of composition has been withheld as a trade secret

4. FIRST AID MEASURES**First aid measures**

Eye contact	Rinse thoroughly with plenty of water, also under the eyelids. If symptoms persist, call a physician.
Skin contact	Wash with soap and water.
Inhalation	Remove to fresh air.
Ingestion	Rinse mouth immediately and drink plenty of water. Never give anything by mouth to an unconscious person.

Most important symptoms and effects, both acute and delayed

Most Important Symptoms and Effects	No information available.
--	---------------------------

Indication of any immediate medical attention and special treatment needed

Notes to Physician	Treat symptomatically.
---------------------------	------------------------

5. FIRE-FIGHTING MEASURES

Suitable Extinguishing Media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media

CAUTION: Use of water spray when fighting fire may be inefficient.

Specific hazards arising from the chemical

No information available.

Explosion Data

Sensitivity to Mechanical Impact None.

Sensitivity to Static Discharge None.

Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal precautions Avoid contact with eyes.

Environmental precautions

Environmental precautions See Section 12 for additional Ecological Information.

Methods and material for containment and cleaning up

Methods for containment Prevent further leakage or spillage if safe to do so.

Methods for cleaning up Soak up with inert absorbent material. Pick up and transfer to properly labeled containers.

7. HANDLING AND STORAGE

Precautions for safe handling

Handling Handle in accordance with good industrial hygiene and safety practice.

Conditions for safe storage, including any incompatibilities

Storage Keep containers tightly closed in a dry, cool and well-ventilated place.

Incompatible Products Strong oxidizing agents. Acids. Chlorinated compounds.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION



Control parameters**Exposure Guidelines**

The following ingredients are the only ingredients of the product above the cut-off level (or level that contributes to the hazard classification of the mixture) which have an exposure limit applicable in the region for which this safety data sheet is intended or other recommended limit. At this time, the other relevant constituents have no known exposure limits from the sources listed here

Chemical name	ACGIH TLV	OSHA PEL	NIOSH IDLH
Sodium stearate 822-16-2	TWA: 10 mg/m ³ except stearates of toxic metals	-	

ACGIH TLV: American Conference of Governmental Industrial Hygienists - Threshold Limit Value OSHA PEL: Occupational Safety and Health Administration - Permissible Exposure Limits NIOSH IDLH Immediately Dangerous to Life or Health

Other Exposure Guidelines

Vacated limits revoked by the Court of Appeals decision in AFL-CIO v. OSHA, 965 F.2d 962 (11th Cir., 1992)

Appropriate engineering controls**Engineering Measures**

Showers
Eyewash stations
Ventilation systems

Individual protection measures, such as personal protective equipment**Eyeface protection**

No special protective equipment required.

Skin and body protection

No special protective equipment required.

Respiratory protection

If exposure limits are exceeded or irritation is experienced, NIOSH/MSHA approved respiratory protection should be worn. Positive-pressure supplied air respirators may be required for high airborne contaminant concentrations. Respiratory protection must be provided in accordance with current local regulations.

Hygiene Measures

Handle in accordance with good industrial hygiene and safety practice.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical and Chemical Properties

Physical state	Solid Gel Consistency, Solid	Odor	Multiple Fragrances Rain
Appearance	Blue Multiple Colors Purple		Lavender
Color	No information available	Odor Threshold	No information available
Property	Values	Remarks	Method
pH	8.5	None known	
Melting / freezing point	No data available	None known	
Boiling point / boiling range	No data available	None known	
Flash Point	No data available	None known	
Evaporation Rate	No data available	None known	
Flammability (solid, gas)	No data available	None known	
Flammability Limit in Air			

Upper flammability limit	No data available	
Lower flammability limit	No data available	
Vapor pressure	No data available	None known
Vapor density	No data available	None known
Specific Gravity	0.99	None known
Water Solubility	Partially soluble	None known
Solubility in other solvents	No data available	None known
Partition coefficient: n-octanol/water	No data available	None known
Autoignition temperature	No data available	None known
Decomposition temperature	No data available	None known
Kinematic viscosity	No data available	None known
Dynamic viscosity	No data available	None known
Explosive properties	No data available	
Oxidizing properties	No data available	

Other Information

Softening Point	No data available
VOC Content (%)	No data available
Particle Size	No data available
Particle Size Distribution	

10. STABILITY AND REACTIVITY

Reactivity

No data available.

Chemical stability

Stable under recommended storage conditions.

Possibility of Hazardous Reactions

None under normal processing.

Conditions to avoid

None known based on information supplied.

Incompatible materials

Strong oxidizing agents. Acids. Chlorinated compounds.

Hazardous Decomposition Products

Carbon oxides.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure**Product Information****Inhalation**

Specific test data for the substance or mixture is not available.



Eye contact	Specific test data for the substance or mixture is not available.
Skin contact	Specific test data for the substance or mixture is not available.
Ingestion	Specific test data for the substance or mixture is not available.

Component Information

Chemical name	Oral LD50	Dermal LD50	Inhalation LC50
Propylene Glycol 57-55-6	= 20 g/kg (Rat)	= 20800 mg/kg (Rabbit)	-

Information on toxicological effects

Symptoms No information available.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Sensitization No information available.

Mutagenic Effects No information available.

Carcinogenicity The table below indicates whether each agency has listed any ingredient as a carcinogen.

IARC (International Agency for Research on Cancer)

Group 3 - Not Classifiable as to Carcinogenicity in Humans

OSHA (Occupational Safety and Health Administration of the US Department of Labor)

X - Present

Reproductive toxicity No information available.

STOT - single exposure No information available.

STOT - repeated exposure No information available.

Chronic Toxicity No known effect based on information supplied.

Target Organ Effects Eyes. Respiratory system. Skin. Blood. Kidney. Liver. Spleen. Systemic Toxicity. Cardiovascular system.

Aspiration Hazard No information available.

Numerical measures of toxicity Product Information

The following values are calculated based on chapter 3.1 of the GHS document

ATEmix (inhalation-dust/mist)

5,260.90 mg/l

12. ECOLOGICAL INFORMATION

Ecotoxicity

The environmental impact of this product has not been fully investigated.

Chemical name	Toxicity to Algae	Toxicity to Fish	Toxicity to Microorganisms	Daphnia Magna (Water Flea)
Propylene Glycol 57-55-6	96h EC50: = 19000 mg/L (Pseudokirchneriella subcapitata)	96h LC50: = 51600 mg/L (Oncorhynchus mykiss) 96h LC50: 41 - 47 mL/L (Oncorhynchus mykiss) 96h LC50: = 51400 mg/L (Pimephales promelas) 96h LC50: = 710 mg/L (Pimephales promelas)	-	24h EC50: > 10000 mg/L 48h EC50: > 1000 mg/L

Persistence and Degradability

No information available.

Bioaccumulation

Other adverse effects

No information available.

13. DISPOSAL CONSIDERATIONS

Waste treatment methods

Disposal methods

This material, as supplied, is not a hazardous waste according to Federal regulations (40 CFR 261). This material could become a hazardous waste if it is mixed with or otherwise comes in contact with a hazardous waste, if chemical additions are made to this material, or if the material is processed or otherwise altered. Consult 40 CFR 261 to determine whether the altered material is a hazardous waste. Consult the appropriate state, regional, or local regulations for additional requirements.

Contaminated Packaging

Dispose of contents/containers in accordance with local regulations.

14. TRANSPORT INFORMATION

DOT

Proper Shipping Name
Hazard Class

NOT REGULATED
NON REGULATED
N/A

TDG

Not regulated

MEX

Not regulated



<u>ICAO</u>	Not regulated
<u>IATA</u>	Not regulated
Proper Shipping Name	NON REGULATED
Hazard Class	N/A
<u>IMDG/IMO</u>	Not regulated
Hazard Class	N/A
<u>RID</u>	Not regulated
<u>ADR</u>	Not regulated
<u>ADN</u>	Not regulated

15. REGULATORY INFORMATION

International Inventories

TSCA	Complies
DSL	All components are listed either on the DSL or NDSL.

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory
DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

US Federal Regulations

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product contains a chemical or chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

SARA 311/312 Hazard Categories

Acute Health Hazard	No
Chronic Health Hazard	No
Fire Hazard	No
Sudden release of pressure hazard	No
Reactive Hazard	No

CWA (Clean Water Act)

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

CERCLA

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material

US State Regulations

California Proposition 65

This product does not contain any Proposition 65 chemicals.

U.S. State Right-to-Know Regulations

.



Chemical name	New Jersey	Massachusetts	Pennsylvania	Rhode Island	Illinois
Propylene Glycol 57-55-6	X		X		

International Regulations**Mexico****National occupational exposure limits****Canada****WHMIS Hazard Class**

Not determined

16. OTHER INFORMATION

NFPA	Health Hazards	1	Flammability	0	Instability	0	Physical and Chemical Hazards	-
HMIS	Health Hazards	1	Flammability	0	Physical Hazard	0	Personal Protection	X

Prepared ByWipex
1-561-338-3338
15-Dec-2011**Issuing Date**

February 16, 2026

Revision Date

No information available

Revision Note

Feb-2026

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet