
Master Industraial MHD-42D-C 42” High Capacity Direct-Drive Barrel Fan—16,250 CFM, 3/4 HP, 120 Volt



- Great for garages, barns, workshops, and factories
- All metal construction rugged enough for most applications
- Industry leading high airflow for up to 16,250 CFM
- Direct-drive motor for minimum maintenance
- 1-year limited warranty

Product Description

Get ready for an unrivaled cooling solution. The Master 42” High Capacity Direct-Drive Barrel Fan will blow you away with the massive amount of air it moves and its quiet, direct-drive operation. When you need to save on A/C and cool a giant indoor or outdoor space, this fan has you covered. With solid wheels for portability and the durable all metal construction you demand, you know you’re getting the best. This is a true workhorse air circulator. ***Master – built for power.***



©2025 Pinnacle Climate Technologies

Features and Benefits

- Great for garages, barns, workshops, or factories
- All metal construction
- High airflow for up to 16,250 CFM
- 3/4 HP industrial motor
- Built-in handle
- One-Bolt Service™ Access
- Powder-coated safety guards
- Direct-Drive motor for minimal maintenance
- Solid wheels for easy portability
- 1-year limited warranty

Key Specs

Model Number	MHD-42D-C
Brand	Master Industrial
Warranty	1-year limited warranty
Net Weight (lb.)	85
Air Flow (CFM)	16,250 / 13,000
Blade Material	Aluminum
Cord Length (ft.)	8

Motor Size (HP)	3/4
Volts	120
Amps	4.7
Hertz	60
Product Dimensions (L x W x H) (in.)	44 x 16 x 45
Product Shipping Dimensions (L x W x H) (in.)	44 x 21 x 45
Shipping Weight (lb.)	87

Master is a registered trademark of Pinnacle Climate Technologies, Inc.

©2025 Pinnacle Climate Technologies