

Spring Retractable Fuel Hose Reels



3/4", 1", 1 1/4", 1 1/2" I.D.

- Ideal for mobile and permanent-mount applications
- Suitable for a wide variety of fuel applications including E85
- Incorporates metal forms to ensure the greatest possible strength
- Latch and ratchet are made of heavy duty cast aluminum to limit the opportunity for premature wear
- Equipped with FKM seals
- Reels are all supplied with our ball-bearing style swivel



FHD79035 OLP

Model with hose & bumper	Shipping Weight		Hose I.D.		Hose O.D.		Hose Length		Max Pressure		NPT(M) Hose Outlet	NPT(F) Reel Inlet	NPT(F) Reel Outlet	Size Index Page	Size Index #
	lbs	kg	in	mm	in	mm	ft	m	psi	bar	in	in	in		
Low Pressure Fuel Reels Maximum Temperature 150 °F (65 °C)															
F7925 OLP	47	21	3/4	19	1.188	30	25	8	*50	3	3/4	3/4	3/4	12	---
FHD79035 OLP	79	36	3/4	19	1.188	30	35	11	*50	3	3/4	3/4	3/4	13	2
FSD13035 OLP	102	46	3/4	19	1.188	30	35	11	*50	3	3/4	1	3/4	17	1
F83050 OLP	89	40	3/4	19	1.188	30	50	15	*50	3	3/4	3/4	3/4	14	1
FSD13050 OLP	110	50	3/4	19	1.188	30	50	15	*50	3	3/4	1	3/4	17	1
FD83075 OLP	115	52	3/4	19	1.188	30	75	23	*50	3	3/4	3/4	3/4	14	2
FD84035 OLP	94	43	1	25	1.500	38	35	11	*50	3	1	1	1	14	3
FSD14035 OLP	105	48	1	25	1.500	38	35	11	*50	3	1	1	1	17	1
FD84050 OLP	115	52	1	25	1.500	38	50	15	*50	3	1	1	1	14	3
FSD14050 OLP	127	58	1	25	1.500	38	50	15	*50	3	1	1	1	17	2
FE9450 OLPBW	157	71	1	25	1.500	38	50	15	*50	3	1	1	1	16	1

*Models equipped with UL330 and cUL Nitrile synthetic rubber (ORS) hose. 250 psi minimum burst (17 Bar). Flow rates of fuel hose are reduced by 30% with addition of internal spring type bend restrictors. For example, flow rate of F7925 OLP with internal bend restrictors is 9.0 GPM at 40 psi; flow without internal bend restrictors is 13.0 GPM at 40 psi.

Model without hose & bumper	Shipping Weight		Hose Capacity			Max Pressure		NPT(F) Reel Inlet	NPT(F) Reel Outlet	Size Index Page	Size Index #
	lbs	kg	I.D.	O.D.	Length	psi	bar	in	in		
Low Pressure Fuel Reels Maximum Temperature 210 °F (99 °C)											
F7900 OLP	45	20	3/4	19	1.188 30	25	8	500 35	3/4	3/4	12 ---
FHD79005 OLP	54	24	3/4	19	1.188 30	35	11	500 35	3/4	3/4	13 2
F83000 OLP	74	34	3/4	19	1.188 30	50	15	500 35	3/4	3/4	14 1
FD83000 OLP	82	37	3/4	19	1.188 30	75	23	500 35	3/4	3/4	14 2
FSD14000 OLP	85	39	1	25	1.500 38	35	11	500 35	1	1	17 1
FD84000 OLP	84	38	1	25	1.500 38	50	15	500 35	1	1	14 3
FSD14005 OLP	92	42	1	25	1.500 38	50	15	500 35	1	1	17 2
FE9400 OLPBW	115	52	1	25	1.500 38	50	15	500 35	1	1	16 1
FF9500 OLPBW	125	57	1 1/4	32	1.750 44	50	15	600 41	1 1/2	1 1/4	16 5
FF9600 OLPBW	135	61	1 1/2	38	2.000 51	50	15	600 41	1 1/2	1 1/2	16 5

Hose Assemblies	Hose I.D.		Hose O.D.		Hose Length		Max Pressure		End Fittings		Shipping Weight	
	in	mm	in	mm	ft	m	psi	bar	in - NPT(M)		lbs	kg
Low Pressure Fuel Inlet Hose 4 spiral poly yarn braid												
S600451-2	1	25	1.500	38	2	0.6	50	3	1 x 1		1.7	0.8
Low Pressure Fuel Outlet Hoses 4 spiral poly yarn braid												
S600160-1	3/4	19	1.188	30	25	8	50	3	3/4 x 3/4		17.5	7.9
S600160-4	3/4	19	1.188	30	35	11	50	3	3/4 x 3/4		24.5	11.1
S600160-2	3/4	19	1.188	30	50	15	50	3	3/4 x 3/4		35.0	15.9
S600160-3	3/4	19	1.188	30	75	23	50	3	3/4 x 3/4		52.5	23.8
S600451-35	1	25	1.500	38	35	11	50	3	1 x 1		30.0	13.6
S600451-50	1	25	1.500	38	50	15	50	3	1 x 1		42.0	19.1

Caution: Be sure working pressure required does not exceed above ratings. Misapplication can result in serious operator injury.



S600451-35



S600160-2

NEW! Reel Covers

See page 41



Interactive Reel Catalog

Visit reelcraft.com/catalog for complete product specifications, parts, and accessories.



Pivot Bases & Swing Brackets

See page 43



Hose Bumper Stops

See page 40