



**HYDRO-FORCE™**

# SAFETY DATA SHEET

**Supersedes Date:** 01-Dec-2015

**Revision Date:** 03-May-2016

**Version:** 2

## 1. IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

### Product identifier

**Product Label Name** Advanced Protector with Teflon Carpet Protector

### Other means of identification

**UPC Code(s)** Not applicable

**Product code** CP16

**Synonyms** None

### Recommended use of the chemical and restrictions on use

**Recommended Use** Surface protector

**Uses advised against** Follow label instructions. Not recommended for any use except intended use. Do not atomize or use as aerosol.

### Supplier's details

#### **Supplier Address**

Hydro-Force  
4282 South 590 West  
Salt Lake City, UT 84123  
USA

#### **Manufacturer Address**

Hydro-Force  
4282 South 590 West  
Salt Lake City, UT 84123  
USA

### Emergency telephone number

**Company Phone Number** 1-800-948-1779

**Company Emergency Phone Number** United States: 1-800-535-5053 (INFOTRAC – 24 hours, 7 days a week)

**Emergency telephone** International: 1-352-323-3500 (INFOTRAC – 24 hours, 7 days a week)

Poison Control 1-800-222-1222 (24 hour)

## 2. HAZARDS IDENTIFICATION

### Classification

#### **OSHA Regulatory Status**

This chemical is not considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Not a dangerous substance or mixture according to the Globally Harmonized System (GHS)

### GHS Label elements, including precautionary statements

#### **Emergency Overview**

The product contains no substances which at their given concentration, are considered to be hazardous to health

No GHS pictogram required

**Appearance** Hazy liquid

**Physical state** liquid

**Odor** Odorless



**Indication of immediate medical attention and special treatment needed, if necessary**

**Notes to physician** Treat symptomatically.

## 5. FIRE-FIGHTING MEASURES

**Suitable Extinguishing Media**

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

**Unsuitable Extinguishing Media** CAUTION: Use of water spray when fighting fire may be inefficient.

**Specific hazards arising from the chemical**

No information available.

**Hazardous Combustion Products** No information available.

**Explosion Data**

**Sensitivity to Mechanical Impact** None.

**Sensitivity to Static Discharge** None.

**Protective Equipment and Precautions for Firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

## 6. ACCIDENTAL RELEASE MEASURES

**Personal precautions, protective equipment and emergency procedures**

**Personal precautions** Use personal protective equipment. Evacuate personnel to safe areas. Keep people away from and upwind of spill/leak.

**Advice for emergency responders** For personal protection see section 8.

**Environmental precautions**

**Environmental precautions** See Section 12 for additional Ecological Information. Do not flush into surface water or sanitary sewer system. Prevent further leakage or spillage if safe to do so. Prevent product from entering drains.

**Methods and materials for containment and cleaning up**

**Methods for Containment** Prevent further leakage or spillage if safe to do so.

**Methods for cleaning up** Use personal protective equipment. Dam up. Cover liquid spill with sand, earth or other noncombustible absorbent material. Take up mechanically, placing in appropriate containers for disposal. Clean contaminated surface thoroughly. Soak up with inert absorbent material. Pick up and transfer to properly labeled containers.

## 7. HANDLING AND STORAGE

**Precautions for safe handling**

**Advice on safe handling** Use only in area provided with appropriate exhaust ventilation. Wear personal protective equipment. Do not breathe vapors or spray mist.

**Conditions for safe storage, including any incompatibilities**

<b>Technical measures/Storage conditions</b>	Keep containers tightly closed in a cool, well-ventilated place. Keep in properly labeled containers.
<b>Packaging material</b>	Keep product in packaging product is initially sold in.
<b>Incompatible products</b>	None known based on information supplied.

## 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

### Control parameters

**Exposure Guidelines** This product does not contain any hazardous materials with occupational exposure limits established by the region specific regulatory bodies.

### Appropriate engineering controls

**Engineering Measures** Showers  
Eyewash stations  
Ventilation systems.

### Individual protection measures, such as personal protective equipment

**Eye/Face Protection** Tightly fitting safety goggles. Face-shield.

**Skin and body protection** No special protective equipment required.

**Respiratory protection** If exposure limits are exceeded or irritation is experienced, NIOSH/MSHA approved respiratory protection should be worn. Positive-pressure supplied air respirators may be required for high airborne contaminant concentrations. Respiratory protection must be provided in accordance with current local regulations.

**Hygiene measures** When using, do not eat, drink or smoke. Provide regular cleaning of equipment, work area and clothing. Do not eat, drink or smoke when using this product. Remove and wash contaminated clothing before re-use.

## 9. PHYSICAL AND CHEMICAL PROPERTIES

### Physical and chemical properties

<b>Physical state</b>	liquid	<b>Odor</b>	odorless
<b>Appearance</b>	Hazy liquid	<b>Odor threshold</b>	No information available
<b>Color</b>	Amber		
<b><u>Property</u></b>	<b><u>Values</u></b>	<b><u>Remarks • Method</u></b>	
<b>pH</b>	7.5		
<b>Melting point</b>	No information available		
<b>Boiling point/boiling range</b>	> 100 °C / > 212° F		
<b>Flash Point</b>	> 94 °C / > 201 °F		
<b>Evaporation rate</b>	No information available		
<b>Flammability (solid, gas)</b>	No information available		
<b>Flammability Limits in Air</b>			
<b>Upper Flammability Limit</b>	No information available		
<b>Lower Flammability Limit</b>	No information available		
<b>Vapor pressure</b>	17.5		
<b>Vapor density</b>	0.7	Air=1	
<b>Specific Gravity</b>	1.050		
<b>Water solubility</b>	Soluble in water		
<b>Solubility in other solvents</b>	No information available		
<b>Partition coefficient: n-octanol/water</b>	No information available		
<b>Autoignition temperature</b>	No information available		



<b>Carcinogenicity</b>	No information available.
<b>Reproductive toxicity</b>	No information available.
<b>Developmental Toxicity</b>	No information available.
<b>STOT - single exposure</b>	No information available.
<b>STOT - repeated exposure</b>	No information available.
<b>Chronic toxicity</b>	Avoid repeated exposure. May cause adverse liver effects.
<b>Target Organ Effects</b>	Blood, Central nervous system, Eyes, Hematopoietic System, Kidney, Liver, Respiratory system, Skin.
<b>Aspiration hazard</b>	No information available.

#### **Numerical measures of toxicity - Product Information**

The following values are calculated based on chapter 3.1 of the GHS document .

<b>ATEmix (oral)</b>	> 5000 mg/kg
<b>ATEmix (dermal)</b>	> 5000 mg/kg

## **12. ECOLOGICAL INFORMATION**

### **Ecotoxicity**

0% of the mixture consists of components(s) of unknown hazards to the aquatic environment.

### **Persistence and degradability**

No information available.

### **Bioaccumulation**

No information available.

### **Other adverse effects**

No information available

## **13. DISPOSAL CONSIDERATIONS**

### **Waste treatment**

#### **Waste Disposal Methods**

Disposal should be in accordance with applicable regional, national and local laws and regulations.

#### **Contaminated packaging**

Do not re-use empty containers.

## **14. TRANSPORT INFORMATION**

**DOT** Not regulated

**IATA** Not regulated

**IMDG** Not regulated

## **15. REGULATORY INFORMATION**

### **International Inventories**

<b>TSCA</b>	Complies
<b>DSL/NDSL</b>	Complies

### **Legend:**

**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory

**DSL/NDSL** - Canadian Domestic Substances List/Non-Domestic Substances List

### **US Federal Regulations**

**SARA 313**

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372.

**SARA 311/312 Hazard Categories**

<b>Acute Health Hazard</b>	Yes
<b>Chronic Health Hazard</b>	No
<b>Fire Hazard</b>	No
<b>Sudden Release of Pressure Hazard</b>	No
<b>Reactive Hazard</b>	No

**Clean Water Act**

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42).

**CERCLA**

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material.

**US State Regulations**

**California Proposition 65**

This product does not contain any Proposition 65 chemicals.

**U.S. State Right-to-Know Regulations**

Chemical Name	New Jersey	Massachusetts	Pennsylvania
None			

**U.S. EPA Label information**

EPA Pesticide Registration Number Not applicable

**16. OTHER INFORMATION**

<b>NFPA</b>	Health hazard 1	Flammability 1	Instability 0	Physical and chemical hazards -
<b>HMIS</b>	Health hazard 1	Flammability 1	Physical Hazard 0	Personal protection X

**Prepared By** Hydro-Force  
 Environmental Health & Safety Manager  
**Revision Date** 03-May-2016  
**Revision Note**  
 No information available

**Disclaimer**

The (M)SDS is intended to provide a brief summary of our knowledge and guidance regarding the use of this material. The information contained here has been compiled from sources considered by Bridgewater LLC to be dependable and is accurate to the best of the Company's knowledge. It is not meant to be an all-inclusive document on worldwide hazard communication regulations.

This information is offered in good faith. Each user of this material needs to evaluate the conditions of use and design the appropriate protective mechanisms to prevent employee exposures, property damage or release to the environment. Bridgewater LLC assumes no responsibility for injury to the recipient of third persons, or for any damage to any property resulting from misuse of the product.

**End of Material Safety Data Sheet**

