ABB BALDOR RELIANCE

Customer information packet

CXL05142A

1HP, 1730RPM, 1PH, 60HZ, 56C, 3524L, XPFC, F1, N
Class - CLI GP D
Division - Division I

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/5/2026 5:06:30 PM

Specifications

Enclosure	XPFC
Frame	56C
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP D
Haz Area Division	Division I
Motor Letter Type	Cap Start, Induction Run
Output @ Frequency	1.000 HP @ 60 HZ
Phase	1
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	115.0 V @ 60 HZ
	230.0 V @ 60 HZ
Agency Approvals	UL
	CSA
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	12.400 A @ 115.0 V
	6.200 A @ 230.0 V
Design Code	L
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	67.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	6.2 a
Insulation Class	B

Part Detail

Revision	F
Type	AC
Mech. spec.	35S154
Base	
Status	PRD/A
Elec. spec.	35WGF092
Layout	35LYS154
Eff. date	10-19-2026
CD Diagram	CD0008
Poles	04
Leads	3#16 A PH,3#18 B&J,1#14 #4TH Y
Proprietary	False
Created date	11-14-2024

Inverter Code	Not Inverter
KVA Code	L
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	3 @ 16 AWG, A PH
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	X3524L
Mounting Arrangement	F1
Number of Poles	4
Overall Length	15.17 IN
Power Factor	77
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.00
Shaft Diameter	0.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1730 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	Automatic Thermal Overload
Winding Thermal 1 Location	EP
Winding Thermal 2	None

Nameplate

NP2204XPSL							
NO.		**CC**					
SER.							
SPEC.	35S154F092						
CAT.NO.	CXL05142A						
HP	1	**T. CODE**	T3C				
VOLTS	115/230						
AMPS	12.4/6.2						
RPM	1730						
HZ	60	**PH**	1	**CL**	B		
SER.F.	1.00	**DES**	L	**CODE**	L		
RATING	40C AMB-CONT						
FRAME	56C	**NEMA-NOM-EFF**	67				
USABLE AT 208V	N/A	**PF**	77				
BLANK							

AC Induction Motor Performance Data
Record # 115224
Typical performance - not guaranteed values

Winding: 35WGF092-R001	**Type:** 3524L	**Enclosure:** XPFC

Nameplate Data				**115 V, 60 Hz: Low Voltage Connection**	
Rated Output (HP)			1	**Full Load Torque**	3.042 LB-FT
Volts			115/230	**Start Configuration**	direct on line
Full Load Amps			12.4/6.2	**Breakdown Torque**	8.59 LB-FT
R.P.M.			1730	**Pull-up Torque**	7.38 LB-FT
Hz	60	**Phase**	1	**Locked-rotor Torque**	11.3 LB-FT
NEMA Design Code	L	**KVA Code**	L	**Starting Current**	80 A
Service Factor (S.F.)			1	**No-load Current**	7.98 A
NEMA Nom. Eff.	67	**Power Factor**	77	**Line-line Res. @ 25ºC**	0.71477 Ω A Ph 1.875 Ω B Ph
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	67°C

Load Characteristics 115 V, 60 Hz, 1 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**
Power Factor	40	56	68	77	82	86
Efficiency	49.8	63.3	68.1	68.8	67.1	62.5
Speed	1783.2	1769.8	1754	1737.3	1713.9	1677.8
Line amperes	8.39	9.24	10.6	12.4	14.8	18.3


ABB Motors and Mechanical Inc.


WINDING # 35WGF092

1 HP 1 PH 60 HZ 1730 RPM 115 V 3524L


TORQUES(LB-FT): PO=8.59 PU=7.38 LR=11.3 LRA=80

Typical performance - not guaranteed values.




35LYS154
510-520 = 14.28
521-528 = 15.15
529-535 = 16.03
536-546 = 17.41
4.72
2.06
.12
1.88
.19 KEY
1.38 LONG
Ø6.45
Ø4.500
4.497
Ø.6250
.6245
X-PROOF NAMEPLATE
BALDOR
PT. NO. 35CB3500
4 SLOTS
.34 WIDE
2.99
2.76
.67
4.32
Ø6.66
6.95
45°
45°
4 HOLES
.38-16 TAP
.56 DEEP
Ø5.88 B.C.
6.80
3.50
3.44
LEAD HOLE
.50 N.P.T.
2.49
2.49
5.38
3.31
6.62
.0015 (MAX)
CLEARANCE
(EA END)
.09
.38
.006
.004
1.00
(MIN)
DRIVE END DETAIL
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: REMOVE FAN SHOVE DIM
REV: B
VERSION: 02
REVISED: 11:21:28 08/13/2024
TDR: 000001237998
MODEL NO. 35LYS154
REF: -
BY: USCHHOL5
B
BALDOR - RELIANCE®
HORZ 56C XPFC 35L UL CL I-GP D,CL II-GP F&G W/ATO
35LYS154

CD0008



	LINE A	LINE B	JOIN	JOIN
HIGH STD	1	4	2,3,8	J,5
HIGH OPP	1	4	2,3,5	J,8
LOW STD	1,3,8	4	–	2,J,5
LOW OPP	1,3,5	4	–	2,J,8

NOTES:

1. STANDARD ROTATION IS CCW FACING END OPPOSITE SHAFT EXTENSION.
2. MULTIPLE CAPACITORS ARE CONNECTED IN PARALLEL UNLESS OTHERWISE SPECIFIED.
3. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0008

REV. DESC: REMOVE 2–TERMINAL THERMAL DETAIL, SEE CD0008A02			BALDOR ELECTRIC Co.
REV. LTR: F	VERSION: 01	TDR: 000000360649	
CD0008	FILE: \AAA\00007\408	REVISED: 10:56:54 04/18/2005	TYPE L, DV, REV, THERMAL, 7 LEADS
	MTL: –	BY: ENJOEP0	