
MASTER®
THE PROFESSIONAL'S CHOICE SINCE 1953

Master MAC-12F 12" High Velocity Floor Fan—1500 CFM, 1/5 HP, 120 Volt



- DURABLE—great for your home, garage, barn, or workshop
- POWERFUL—steel construction
- INDUSTRY-LEADING—high airflow for up to 1500 CFM
- Machined industrial motor, tilt-angle head, all metal construction, and more
- 1-year limited warranty

Product Description

When you need to cool down quickly, look no further than Master's industry-leading 12" High Velocity Floor Fan. The heat of summer is no match for its powerful, direct-drive motor and long-lasting steel construction. Plus, the tilt-angle head lets you direct the airflow wherever it's most convenient. Whether you're in the barn, relaxing at home, or working in the garage, this fan will do the job while giving your A/C and wallet a rest. ***Master – built for power.***



©2024 Pinnacle Climate Technologies

Features and Benefits

- Great for your home, garage, barn, or workshop
- Powerful steel construction
- High airflow for up to 1500 CFM
- 1/5 HP industrial motor
- Machined tilt-angle head
- Rock-solid, all metal safety grille
- 3 speed settings
- Balanced blades for optimal air flow
- 1-year limited warranty

Key Specs

Model Number	MAC-12F
Brand	Master
Warranty	1-year limited warranty
Net Weight (lb.)	7
Air Flow (CFM)	750 / 1350 / 1500
Motor Size (HP)	1/5
Speed Settings	3
Volts	120
Amps	0.6
Product Dimensions (L x W x H) (in.)	17 x 7 x 17

Master is a registered trademark of Pinnacle Climate Technologies, Inc.

©2024 Pinnacle Climate Technologies

04/2024