

Mulberry Wallplates

When U.S. made wallplates are specified for the job or needed to meet an ARRA requirement, make Mulberry your first choice!

Every metal wallplate in this catalog is manufactured right here in the USA!

In addition, we offer:

- More than 7,000 different wallplates, with most in stock
- The industry's widest variety of materials, openings, combinations and colors
- A choice of over 40 painted metal, stainless steel, brass and other metal finishes
- Plus, our unbreakable thermoplastic wallplates available in 4 colors
- Standard metal wallplate configurations from 1 to 10-gang and thermoplastic from 1 to 6 gang
- In-house engraving and silk-screening capability
- Custom wallplates available in special sizes or with custom openings or markings



Unsurpassed Quality, Selection & Service!

Mulberry Wallplates

Standard Size

WALLPLATES



83



93, 97, 70



68



95



99



98



85



84



44



86



82



58



51



88



87



94



65



66



69



64



220



221



222



214



215



32



34



33



36



38

Wallplates Color Guide

Princess Size



73



54



57, 53



76



75



79



74



78



43



218



225

Standard Size - Steel

- 44 Almond Semi-Gloss (44000)
- 51 Red Semi-Gloss (51000)
- 58 Gray Semi-Gloss (58000)
- 64 Polished Brass (64000)
- 65 Bank Bronze (65000)
- 66 Satin Bronze (66000)
- 68 Stainless Steel-304 Type-Mirror (68000)
- 69 Statuary Bronze (69000)
- 70 Stainless Steel-304 Type (93000)
- 82 Brown Semi-Gloss (82000)
- 83 Polished Chrome (83000)
- 84 Ivory Semi-Gloss (84000)
- 85 White Wrinkle (85000)
- 86 White Semi-Gloss (86000)
- 87 Black Matte (87000)
- 88 Aluminum Painted Steel (88000)
- 93 Stainless Steel-304 Type (93000)
- 94 Satin Brass (94000)
- 95 Clear Anodized Aluminum (95000)
- 96 Satin Brass-.060" (96000)
- 97 Stainless Steel-430 Type (97000)
- 98 Brown Wrinkle (98000)
- 99 Ivory Wrinkle (99000)
- 214 Hammered Copper (21400)
- 215 Hammered Black (21500)
- 220 Regal Black (22000)
- 221 Regal Copper (22100)
- 222 Regal Gold (22200)




Princess Size - Steel

- 43 Almond Wrinkle
- 53 Stainless Steel-304 Type (93000)
- 54 Satin Brass (54000)
- 57 Stainless Steel-430 Type (97000)
- 73 Polished Chrome (73000)
- 74 Ivory Semi-Gloss (74000)
- 75 White Wrinkle (75000)
- 76 White Semi-Gloss (76000)
- 78 Brown Wrinkle (78000)
- 79 Ivory Wrinkle (79000)
- 218 Polished Brass over steel (21800)
- 225 Brushed Brass over steel (22500)

Standard & Midi Size - Thermoplastic

- 32 White Thermoplastic (32000)
- 33 Light Almond Thermoplastic (33000)
- 34 Ivory Thermoplastic (34000)
- 36 Red Thermoplastic (36000)
- 38 Brown Thermoplastic (38000)


Full Scale Dimensions




STANDARD TOLERANCE $\pm 0.0313''$

Screw Hole Dimensions


Standard Size




Examples:



Blank



Toggle
Single
Receptacle



Interchangeable
(Despard)
GFI

Refer to the dimensional drawings within our Opening Selector Guide

Dimensions by Style

Standard Shape

1 gang	4.5" x 2.75"
2 gang	4.5" x 4.562"
3 gang	4.5" x 6.375"
4 gang	4.5" x 8.187"
5 gang	4.5" x 10.00"
6 gang	4.5" x 11.812"
7 gang	4.5" x 13.625"
8 gang	4.5" x 15.437"
9 gang	4.5" x 17.25"
10 gang	4.5" x 19.062"
11 gang	4.5" x 20.875"
12 gang	4.5" x 22.687"
13 gang	4.5" x 24.50"
14 gang	4.5" x 26.312"
15 gang	4.5" x 28.125"
16 gang	4.5" x 29.937"
17 gang	4.5" x 31.75"
18 gang	4.5" x 33.562"
19 gang	4.5" x 35.375"
20 gang	4.5" x 37.187"

Jumbo / Oversize (SL)

1 gang	5.5" x 3.50"
2 gang	5.5" x 5.50"
3 gang	5.5" x 7.50"
4 gang	5.5" x 9.50"
5 gang	5.5" x 11.50"
6 gang	5.5" x 13.50"
7 gang	5.5" x 15.50"
8 gang	5.5" x 17.50"

Princess Shape (PRL)

1 gang	5" x 2.75"
2 gang	5" x 4.562"
3 gang	5" x 6.375"
4 gang	5" x 8.187"
5 gang	5" x 10.00"
6 gang	5" x 11.812"

Maxi Shape (MP)

1 gang	5" x 3.50"
--------	------------

Thermoplastic Standard Size

1 gang	4.5" x 2.76"
2 gang	4.5" x 4.57"
3 gang	4.5" x 6.38"
4 gang	4.5" x 8.19"
5 gang	4.5" x 10.03"
6 gang	4.5" x 11.81"

Thermoplastic Midi Size

1 gang	4.88" x 3.11"
2 gang	4.88" x 4.92"
3 gang	4.88" x 6.77"
4 gang	4.88" x 8.58"



STANDARD TOLERANCE ± 0.0313 "

Dimensions for Deep and Narrow Plates see
Pages A64 - A66.

Note: Standard Size and Jumbo/Oversize plates (beveled edge) can be made available in custom sizes.
Princess and Maxi Shape plates, as well as thermoplastic plates, are only available up to 6 gangs.

Material Specifications

S - Standard Shape



P - Princess Shape

Steel (Prepared to Underwriters Laboratories, Inc. specifications)	Finish	Shape	Thickness	Finish Designator	Catalog Page
Almond (ALM)	smooth semi-gloss	S	.030	44000	A11-22
Almond Wrinkle (DA-PRL)	hard baked wrinkle	P	.030	43000	A23-32
Aluminum Paint (CDA)	smooth semi-gloss	S	.030	88000	A11-22
Black Paint (BL)	matte	S	.030	87000	A11-22
Brown Paint (BK)	smooth semi-gloss	S	.030	82000	A11-22
Brown Paint (DB)	hard baked wrinkle	S	.030	98000	A11-22
Brown Paint (DB-PRL)	hard baked wrinkle	P	.030	78000	A23-32
Chrome Plate (CA)	mirror polish	S	.030	83000	A37-46
Chrome Plate (CA-PRL)	mirror polish	P	.030	73000	A47-56
Gray	smooth semi-gloss	S	.030	58000	A11-22
Ivory (IA)	smooth semi-gloss	S	.030	84000	A11-22
Ivory (IA-PRL)	smooth semi-gloss	P	.030	74000	A23-32
Ivory (DI)	hard baked wrinkle	S	.030	99000	A11-22
Ivory (DI-PRL)	hard baked wrinkle	P	.030	79000	A23-32
Red (RA)	smooth semi-gloss	S	.030	51000	A11-22
White (WA)	smooth semi-gloss	S	.030	86000	A11-22
White (WA-PRL)	smooth semi-gloss	P	.030	76000	A23-32
White (DW)	hard baked wrinkle	S	.030	85000	A11-22
White (DW-PRL)	hard baked wrinkle	P	.030	75000	A23-32
Hammered Copper	textured / matte	S	.030	21400	A61-63
Hammered Black	textured / matte	S	.030	21500	A61-63
Regal Black	textured / matte	S	.030	22000	A61-63
Regal Copper	textured / matte	S	.030	22100	A61-63
Regal Gold	textured / matte	S	.030	22200	A61-63
Zinc Coat (AUNF)	unfinished	S	.030	89000	A11-22
Zinc Coat (AUNF-PRL)	unfinished	P	.030	80000	A23-32

Material Specifications

Stainless Steel

Grade	Finish	Shape	Thickness	U.S. Bureau Standards Symbol	Finish Designator	Catalog Page
*Type 304 (304SS)	#4 Fine Satin	S	.030	US #32D	93000	A37-46
*Type 304 (304SS-PRL)	#4 Fine Satin	P	.030	US #32D	53000	A47-56
*Type 304 (304-6SS)	#4 Fine Satin	S	.060	US #32D	70000	A37-46
*Type 304 (304SP)	Mirror Polish	S	.030	US #32	68000	A37-46
Type 430 (SS)	#4 Fine Satin	S	.030	US #32	97000	A37-46
Type 430 (SS-PRL)	#4 Fine Satin	P	.030	US #32D	57000	A47-56

* 304 Stainless steel is a specification grade that consists of 18% chromium and 8% nickel. It is non-magnetic and corrosion resistant. It is ideal for hospitals, schools and other public institutions, as well as computer rooms.

Aluminum

Clear Anodized (4AA)	Matte, Smooth	S	.040	-	95000	A37-46
----------------------	---------------	---	------	---	-------	--------

Brass & Bronze*

Statuary Bronze Dark (4DBR)	Antique finish over solid brass	S	.040	US #20	69000	A37-46
Bank Bronze Medium (4ABR)	Antique finish over solid brass	S	.040	US #108	65000	A37-46
Satin Brass (4BB) (solid brass)	Satin #4 Polish	S	.040	US #4	94000	A37-46
Satin Brass (4BB-PRL) (solid brass)	Satin #4 Polish	P	.040	US #4	54000	A47-56
Satin Brass (6BB) (solid brass)	Satin #4 Polish	S	.060	US #4	96000	A37-46
Satin Bronze (4SBR)	Satin #4 Polish	S	.040	US #10	66000	A37-46
Polished Brass (4PB) (solid brass)	Mirror Finish	S	.040	US #3	64000	A37-46
Polished Brass (plated steel)	Mirror Finish	P	.040	-	21800	A47-56
Satin Brass (plated steel)	Satin #4 Polish	P	.040	-	22500	A47-56



* Lacquered to prevent oxidation

Thermoplastic

Light Almond	33000	A72-79
Ivory	34000	A72-79
Red	36000	A72-79
White	32000	A72-79
Brown	38000	A72-76

PAINTED METAL

Standard Size



	White Semi-Gloss (WA)	White Wrinkle (DW)	Ivory Semi-Gloss (IA)	Ivory Wrinkle (DI)	Brown Semi-Gloss (BK)	Brown Wrinkle (DB)	Almond Semi-Gloss (ALM)	Black Matte (BL)	Gray Semi-Gloss	Red Semi-Gloss (RA)	Aluminum Semi-Gloss (CDA)	Zinc Coat (AUNF) Unfinished
4 Blanks (Box Mntg. 3.281") (4B)	86154	85154	84154	99154	82154	98154		87154	58154	51154	88154	89154
5 Blanks (Box Mntg. 3.281") (5B)	86155	85155	84155	99155	82155	98155		87155	58155	51155	88155	89155
6 Blanks (Box Mntg. 3.281") (6B)	86156	85156	84156	99156	82156	98156		87156	58156	51156	88156	89156
7 Blanks (Box Mntg. 3.281") (7B)	86157	85157	84157	99157	82157	98157		87157	58157	51157	88157	89157
8 Blanks (Box Mntg. 3.281") (8B)	86158	85158	84158	99158	82158	98158		87158	58158	51158	88158	89158
9 Blanks (Box Mntg. 3.281") (9B)	86159	85159	84159	99159	82159	98159		87159	58159	51159	88159	89159
10 Blanks (Box Mntg. 3.281") (10B)	86160	85160	84160	99160	82160	98160		87160	58160	51160	88160	89160
Block Duplex/GFI Recept. (SRM)	86401	85401	84401	99401	82401	98401	44401	87401	58401	51401	88401	89401
2 Block Duplex/GFI Recept. (2SRM)	86402	85402	84402	99402	82402	98402	44402	87402	58402	51402	88402	89402
3 Block Duplex/GFI Recept. (3SRM)	86403	85403	84403	99403	82403	98403	44403	87403	58403	51403	88403	89403
4 Block Duplex/GFI Recept. (4SRM)	86404	85404	84404	99404	82404	98404	44404	87404	58404	51404	88404	89404
5 Block Duplex/GFI Recept. (5SRM)	86405	85405	84405	99405	82405	98405	44405	87405	58405	51405	88405	89405
6 Block Duplex/GFI Recept. (6SRM)	86406	85406	84406	99406	82406	98406	44406	87406	58406	51406	88406	89406

PAINTED METAL WALLPLATES - STANDARD SIZE