



TEGERA® 450

Learn more

CUT AND HEAT PROTECTION COMBINED

Glove with high CRF cut protection for versatile assembly work. Knitted with 13gg CRF® Technology for solid cut C performance. Durable nitrile foam coating on palm for improved grip performance. Dirt-masking dark grey and black allow for extended product life. Withstands contact heat up to 100°C.

CHARACTERISTICS

- Flexible
- Durable
- Good grip
- Comfortable

FUNCTIONS

- Withstands contact heat up to 100°C

CRF®

ORIGINAL EXCELLENT dermatest 02 2022 dermatest-guarantee.com

OEKO TEX® STANDARD 100 SE 14-214 RISE

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Cut injuries, Abrasion injuries, Grazes, Scratches, lacerations, Contact with dirt

PRIMARY ENVIRONMENTS OF USE

Cut risk environments, Dry environments, Moist environments, Dirty environments

PRIMARY AREAS OF USE

Assembly, Inspection work, Engineering

PRIMARY INDUSTRIES OF USE

Agriculture, forestry and fishing, Automotive manufacturing, Automotive repair and maintenance, Basic metals manufacturing, Electrical equipment manufacturing, Machinery and equipment manufacturing, Metal manufacturing and fabrication, Mining and quarrying, Transport equipment manufacturing

TYPE OF WORK

Medium weight

SPECIFICATION

TYPE Cut resistant gloves, Heat protection gloves
CATEGORY Cat. II
KNITTING GAUGE (GG) 13
LINING MATERIAL CRF® Technology, Glass fibre thread, HPPE, Nylon, Polyester, Spandex
LENGTH 220-270 mm
DEXTERITY 5
GRIP DESIGN Smooth finish
COLOUR Black
PAIRS PER: BUNDLE/CARTON 12/120
DISPLAY TYPE Bag with euro slot
DIPPING Palm-dipped
DIPPING MATERIAL Nitrile foam
CUFF STYLE Knitwrist cuff
CUFF MATERIAL Textile
CUT RESISTANCE (EN ISO 13997) Cut resistance level C
CUT RESISTANCE (EN ISO 13997) TDM: 13.4 N
INNER MATERIAL SPECIFICATION HPPE (High performance polyethylene), Glass fibre thread, Polyester, Nylon, Elastane
OUTER MATERIAL SPECIFICATION Nitrile

COMPLIANCE

CE Cat. II

EAC TP TC 019:2011

EN ISO 21420:2020

EN 388:2016+A1:2018 4X44C

EN 407:2020 (No flame protection) X1XXXX

ANSI/ISEA 105-2024 A1 4 5

Contact heat rating valid for palm area only

FEATURES

Cut protection

SIZE		ARTICLE NUMBER	EAN
5	XXS	450-5	7340118445830
6	XS	450-6	7340118310558
7	S	450-7	7392626073319
8	M	450-8	7392626073333
9	L	450-9	7392626073357
10	XL	450-10	7392626073272
11	XXL	450-11	7392626073296

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.