



TEGERA® 441

Learn more

CUT PROTECTION GLOVE FOR OILY ENVIRONMENTS

A versatile cut protection glove with CRF® technology and high durability. Suitable for work in oily and greasy environments as it has a nitrile dipped knuckle and palm with a sandy finish for good grip. The glove can withstand contact heat up to 100°C/212°F.

CHARACTERISTICS

- Very durable
- Good grip

FUNCTIONS

- Withstands contact heat up to 100°C
- Oil and grease resistant

CRF®

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Cut injuries, Scratches, lacerations, Contact with dirt, Contact with oil and fat

PRIMARY ENVIRONMENTS OF USE

Cut risk environments, Oily and greasy environments, Dirty environments, Harsh environments

PRIMARY AREAS OF USE

Machine operating, Building and construction, Metalwork

PRIMARY INDUSTRIES OF USE

Agriculture, forestry and fishing, Automotive manufacturing, Automotive repair and maintenance, Basic metals manufacturing, Building and construction, Electrical equipment manufacturing, Machinery and equipment manufacturing, Metal manufacturing and fabrication, Mining and quarrying, Oil and gas extraction, Transport equipment manufacturing

TYPE OF WORK

Medium weight

SPECIFICATION

TYPE Cut resistant gloves, Heat protection gloves
CATEGORY Cat. II
KNITTING GAUGE (GG) 13
LINING MATERIAL CRF® Technology, HPPE, Nylon, Spandex
LENGTH 230-275 mm
DEXTERITY 5
GRIP DESIGN Sandy finish
COLOUR Grey
PAIRS PER: BUNDLE/CARTON 6/60
DISPLAY TYPE Bulk pack
DIPPING 3/4 dipped
DIPPING MATERIAL Nitrile, Nitrile foam
CUFF STYLE Knitwrist cuff
CUFF MATERIAL Textile
CUT RESISTANCE (EN ISO 13997) Cut resistance level B
CUT RESISTANCE (EN ISO 13997) TDM: 5.9 N
INNER MATERIAL SPECIFICATION HPPE (High performance polyethylene), Nylon, Elastane
OUTER MATERIAL SPECIFICATION Nitrile

COMPLIANCE

CE Cat. II

EAC TP TC 019:2011

EN 420:2003 +A1:2009

EN 388:2016 4X43B

EN 407:2004 X1XXXX

Contact heat rating valid for palm area only

FEATURES

Cut protection

SIZE		ARTICLE NUMBER	EAN
6	XS	441-6	7340118356709
7	S	441-7	7340118356792
8	M	441-8	7340118356884
9	L	441-9	7340118356976
10	XL	441-10	7340118357065
11	XXL	441-11	7340118357157

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.