ABB BALDOR RELIANCE

Customer information packet

EL3501

.33HP, 1740RPM, 1PH, 60HZ, 56, 3418LC, TEFC, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/5/2026 4:53:22 PM

Specifications

Enclosure	TEFC
Frame	56
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Cap Start, Cap Run
Output @ Frequency	.330 HP @ 60 HZ
Phase	1
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	115.0 V @ 60 HZ
	230.0 V @ 60 HZ
Agency Approvals	C UR US
	CSA
	CURUS
	CURUSEEV
	NEMA PREMIUM (OLD LOGO)
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	1.600 A @ 230.0 V
	3.200 A @ 115.0 V
Design Code	-
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	77.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK

Part Detail

Revision	AK
Type	AC
Mech. spec.	34G375
Base	
Status	PRD/A
Elec. spec.	34WGX028
Layout	34LYG375
Eff. date	10-29-2024
CD Diagram	CD0055
Poles	04
Leads	6#18
Proprietary	False
Created date	01-01-0001

Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	1.6 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	J
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	6 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3418LC
Mounting Arrangement	F1
Number of Poles	4
Overall Length	11.97 IN
Power Factor	88
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.35
Shaft Diameter	0.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1740 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None

Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP2117L									
CAT.NO.	EL3501								
SPEC.	34G375X28G1								
HP	.33								
VOLTS	115/230								
AMP	3.2/1.6								
RPM	1740								
FRAME	56	**HZ**	60	**PH**	1				
SER.F.	1.35	**CODE**	J	**DES**	-	**CL**	F		
NEMA-NOM-EFF	77	**PF**	88						
RATING	40C AMB-CONT								
CC									
DE	6203	**ODE**	6203						
ENCL	TEFC	**SN**							
	SFA 4.2/2.1								

Accessories

Part number	Description	Multiplier
34-171	C FACE KIT	A8

AC Induction Motor Performance Data
Record # 20835
Typical performance - not guaranteed values

Winding: 34WGX028-R002	**Type:** 3418LC	**Enclosure:** TEFC

Nameplate Data				**230 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			.33	**Full Load Torque**	1 LB-FT
Volts			115/230	**Start Configuration**	direct on line
Full Load Amps			3.2/1.6	**Breakdown Torque**	2.6 LB-FT
R.P.M.			1740	**Pull-up Torque**	2.3 LB-FT
Hz	60	**Phase**	1	**Locked-rotor Torque**	3.4 LB-FT
NEMA Design Code	-	**KVA Code**	J	**Starting Current**	11 A
Service Factor (S.F.)			1.35	**No-load Current**	0.7 A
NEMA Nom. Eff.	77	**Power Factor**	88	**Line-line Res. @ 25ºC**	7.34 Ω A Ph 5.89 Ω B Ph
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	31°C
S.F. Amps			4.2/2.1	**Temp. Rise @ S.F. Load**	37°C

Load Characteristics 230 V, 60 Hz, 0.33 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	60	80	83	87	90	90	91
Efficiency	50.6	68.6	75.5	77.3	77.7	76.1	77.9
Speed	1782	1772	1759	1741	1724	1703	1717
Line amperes	0.9	1	1.3	1.6	1.9	2.3	2.1


ABB Motors and Mechanical Inc.

WINDING # 34WGX028


0.33 HP 1 PH 60 HZ 1740 RPM 230 V 3418LC

TORQUES(LB-FT): PO=2.6 PU=2.3 LR=3.4 LRA=11

Typical performance - not guaranteed values.



34LYG375



34LYG375


CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION

REV. DESC: LOAD TO SOLIDWORKS			
REV: E	VERSION: 04	REVISED: 03:58:39 08/09/2022	TDR: 000001194274
34LYG375	MODEL NO. 34LYG375		REF: -
	BY: ENFRAJ0		

BALDOR - RELIANCE®

HORZ 34LC NEMA 56 TEFC

CD0055



	LINE A	LINE B	JOIN
HIGH STD	1	4,5	2,3,8
HIGH OPP	1	4,8	2,3,5
LOW STD	1,3,8	2,4,5	–
LOW OPP	1,3,5	2,4,8	–

NOTES:

1. STANDARD ROTATION IS CCW FACING END OPPOSITE SHAFT EXTENSION.
2. OPTIONAL THERMOSTAT IS PROVIDED WHEN SPECIFIED.
3. MULTIPLE CAPACITORS ARE CONNECTED IN PARALLEL UNLESS OTHERWISE SPECIFIED.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0055

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: D	BY: JLP	REVISED: 04/08/99 1:17	TDR: 0178636
CD0055		FILE: AAA00007414	MDL: –
		MTL: –	TYPE LC, DV, REV, 6 LEADS