



SAFETY DATA SHEET

1. Identification

Important information

*** This Safety Data Sheet is only authorised for use by HP for HP Original products. Any unauthorised use of this Safety Data Sheet is strictly prohibited and may result in legal action being taken by HP. ***

Product identifier

F9K02Series

Other means of identification

None.

Recommended use

Inkjet printing. For use only in inkjet printing

Recommended restrictions

None known.

Manufacturer/Importer/Supplier/Distributor information

HP Inc.
1501 Page Mill Road
Palo Alto, CA 94304-1112
United States

Telephone

650-857-1501

HP Inc. health effects line

(Toll-free within the US)

1-800-457-4209

(Direct)

1-760-710-0048

HP Inc. Customer Care Line

(Toll-free within the US)

1-800-474-6836

(Direct)

1-208-323-2551

Email:

hpcustomer.inquiries@hp.com

2. Hazard(s) identification

Physical hazards

Not classified.

Health hazards

Sensitization, skin

Category 1

Environmental hazards

Not classified.

OSHA defined hazards

Not classified.

Label elements



Signal word

Warning

Hazard statement

May cause an allergic skin reaction.

Precautionary statement

Prevention

Avoid breathing dust/fume/gas/mist/vapors/spray. Contaminated work clothing should not be allowed out of the workplace. Wear protective gloves/protective clothing/eye protection/face protection.

Response

IF ON SKIN: Wash with plenty of water. If skin irritation or rash occurs: Get medical advice/attention. Take off contaminated clothing and wash it before reuse.

Storage

Not available.

Disposal

Dispose of contents/container in accordance with local/regional/national/international regulations.

Hazard(s) not otherwise classified (HNOC)

Complete toxicity data are not available for this specific formulation.

Potential routes of overexposure to this product are skin and eye contact. Inhalation of vapor and ingestion are not expected to be significant routes of exposure for this product under normal use conditions.

3. Composition/information on ingredients**Mixtures**

Chemical name	Common name and synonyms	CAS number	%
Water		7732-18-5	75-85
Cyclo Amide*		Proprietary*	<10
Yellow pigment*		Proprietary*	<5
1,2-Benzisothiazolin-3-one (Benzisothiazolinone)		2634-33-5	<0.1
2-Methyl-2h-isothiazol-3-one (Methylisothiazolinone)		2682-20-4	<0.1

Composition comments *Proprietary This ink supply contains an aqueous ink formulation. This product has been evaluated using criteria specified in 29 CFR 1910.1200 (Hazard Communication Standard).

4. First-aid measures

Inhalation	Remove to fresh air. If symptoms persist, get medical attention.
Skin contact	Wash affected areas thoroughly with mild soap and water. Get medical attention if irritation develops or persists.
Eye contact	Do not rub eyes. Immediately flush with large amounts of clean, warm water (low pressure) for at least 15 minutes or until particles are removed. If irritation persists get medical attention.
Ingestion	If ingestion of a large amount does occur, seek medical attention.
Most important symptoms/effects, acute and delayed	Not available.

5. Fire-fighting measures

Suitable extinguishing media	Dry chemical, CO2, water spray or regular foam.
Unsuitable extinguishing media	None known.
Specific hazards arising from the chemical	Not applicable.
Special protective equipment and precautions for firefighters	Not available.
Specific methods	None established.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures	Wear appropriate personal protective equipment.
Methods and materials for containment and cleaning up	Dike the spilled material, where this is possible. Absorb with inert absorbent such as dry clay, sand or diatomaceous earth, commercial sorbents, or recover using pumps.
Environmental precautions	Do not let product enter drains. Do not flush into surface water or sanitary sewer system.

7. Handling and storage

Precautions for safe handling	Avoid contact with skin, eyes and clothing.
Conditions for safe storage, including any incompatibilities	Keep out of the reach of children. Keep away from excessive heat or cold.

8. Exposure controls/personal protection

Biological limit values	No biological exposure limits noted for the ingredient(s).
Exposure guidelines	Exposure limits have not been established for this product.
Appropriate engineering controls	Not available.
Individual protection measures, such as personal protective equipment	
Eye/face protection	Wear safety glasses with side shields (or goggles).

Skin protection	
Hand protection	Use protective gloves made of: Nitrile rubber.
Other	Wear appropriate chemical resistant clothing.
Respiratory protection	Not available.
Thermal hazards	Not available.
General hygiene considerations	Handle in accordance with good industrial hygiene and safety practice.

9. Physical and chemical properties

Appearance

Physical state	Liquid.
Form	Not available.
Color	Yellow
Odor	Not available.
Odor threshold	Not available.
pH	8 - 10
Melting point/freezing point	Not available.
Initial boiling point and boiling range	Not available.
Flash point	> 230.0 °F (> 110.0 °C)
Evaporation rate	Not available.
Flammability (solid, gas)	Not available.
Upper/lower flammability or explosive limits	
Flammability limit - lower (%)	Not available.
Flammability limit - upper (%)	Not available.
Explosive limit - lower (%)	Not available.
Explosive limit - upper (%)	Not available.
Vapor pressure	Not available.
Vapor density	Not available.
Solubility(ies)	
Solubility (water)	Not available.
Partition coefficient (n-octanol/water)	Not available.
Auto-ignition temperature	Not available.
Decomposition temperature	Not available.
Viscosity	Not available.
Other information	For other VOC regulatory data/information see Section 15.
Oxidizing properties	Not determined
Specific gravity	1 - 1.1
VOC	< 182 g/l

10. Stability and reactivity

Reactivity	Not available.
Chemical stability	Stable under recommended storage conditions.
Possibility of hazardous reactions	None known.
Conditions to avoid	Not available.
Incompatible materials	Incompatible with strong bases and oxidizing agents.
Hazardous decomposition products	Upon decomposition, this product may yield gaseous nitrogen oxides, carbon monoxide, carbon dioxide and/or low molecular weight hydrocarbons., fluorinated hydrocarbons and hydrogen fluoride.

11. Toxicological information

Information on likely routes of exposure

Inhalation	Under normal conditions of intended use, this material is not expected to be an inhalation hazard.
Skin contact	Contact with skin may result in mild irritation.
Eye contact	Contact with eyes may result in mild irritation.
Ingestion	Ingestion is not a likely route of exposure.

Symptoms related to the physical, chemical and toxicological characteristics Not available.

Information on toxicological effects

Acute toxicity Based on available data, the classification criteria are not met.

Components	Species	Test Results
-------------------	----------------	---------------------

1,2-Benzisothiazolin-3-one (Benzisothiazolinone) (CAS 2634-33-5)

Acute

Dermal

LD50	Rat	> 2000 mg/kg
------	-----	--------------

Oral

LD50	Rat	490 mg/kg
------	-----	-----------

2-Methyl-2h-isothiazol-3-one (Methylisothiazolinone) (CAS 2682-20-4)

Acute

Dermal

LD50	Rat	242 mg/kg
------	-----	-----------

Inhalation

LC50	Rat	0.11 mg/l, 4 h
------	-----	----------------

Oral

LD50	Rat	120 mg/kg
------	-----	-----------

Skin corrosion/irritation Based on available data, the classification criteria are not met. Non irritant in rabbit (OECD 404)

Serious eye damage/eye irritation Based on available data, the classification criteria are not met.

Respiratory or skin sensitization

Respiratory sensitization Based on available data, the classification criteria are not met.

Skin sensitization May cause an allergic skin reaction.

Germ cell mutagenicity Based on available data, the classification criteria are not met.

Carcinogenicity Based on available data, the classification criteria are not met.

IARC Monographs. Overall Evaluation of Carcinogenicity

Not listed.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1053)

Not listed.

US. National Toxicology Program (NTP) Report on Carcinogens

Not listed.

Reproductive toxicity Based on available data, the classification criteria are not met.

Specific target organ toxicity - single exposure Based on available data, the classification criteria are not met.

Specific target organ toxicity - repeated exposure Based on available data, the classification criteria are not met.

Aspiration hazard Based on available data, the classification criteria are not met.

Further information Complete toxicity data are not available for this specific formulation

12. Ecological information

Aquatic toxicity No information available.

Ecotoxicity No information available.

Product	Species	Test Results
---------	---------	--------------

F9K02Series		
Aquatic		
Fish	LC50	Fathead minnow (<i>Pimephales promelas</i>) > 750 mg/l, 96 Hours

Components	Species	Test Results
------------	---------	--------------

1,2-Benzisothiazolin-3-one (Benzisothiazolinone) (CAS 2634-33-5)		
--	--	--

<i>Acute</i>		
Other	EC50	Pseudokirchnerella subcapitata 70 - 150 µg/l, 72 h OECD (201)

Aquatic		
<i>Acute</i>		
Crustacea	EC50	Daphnia magna 2.9 mg/l, 48 h (OECD 202)
Fish	LC50	Oncorhynchus mykiss 2.15 mg/l, 96 h (OECD 203)
		Sheepshead minnow (<i>Cyprinodon variegatus</i>) 16.7 mg/l, 96 h EPA 540/9-85-006

2-Methyl-2h-isothiazol-3-one (Methylisothiazolinone) (CAS 2682-20-4)		
--	--	--

<i>Acute</i>		
Other	EC50	Pseudokirchnerella subcapitata 0.138 - 0.22 mg/l, 120 h (OECD 201)

<i>Chronic</i>		
	NOEC	Pseudokirchnerella subcapitata 0.05 mg/l, 120 h (OECD 201)

Aquatic		
<i>Acute</i>		
Crustacea	EC50	Daphnia magna 1.6 mg/l, 48 h (OECD 202)
	LC50	Daphnia magna 0.934 mg/l, 48 h (OECD 202)
Fish	LC50	Oncorhynchus mykiss 4.77 mg/l, 96 h (OECD 203)

Persistence and degradability Not available.

Bioaccumulative potential Not available.

Bioconcentration factor (BCF)	
1,2-Benzisothiazolin-3-one (Benzisothiazolinone)	6.62, (OECD 305) Species: Bluegill (<i>Lepomis macrochirus</i>)
2-Methyl-2h-isothiazol-3-one (Methylisothiazolinone)	48.1, Viscera (1972) Species: Bluegill (<i>Lepomis macrochirus</i>) 5.75, Carcass (1972) Species: Bluegill (<i>Lepomis macrochirus</i>)

Mobility in soil Not available.

Other adverse effects Not available.

13. Disposal considerations

Disposal instructions Do not allow this material to drain into sewers/water supplies. Dispose of waste material according to Local, State, Federal, and Provincial Environmental Regulations. HP's Planet Partners (trademark) supplies recycling program enables simple, convenient recycling of HP original inkjet and LaserJet supplies. For more information and to determine if this service is available in your location, please visit <http://www.hp.com/recycle>.

14. Transport information

DOT

UN number	Not available.
UN proper shipping name	Not Regulated
Transport hazard class(es)	
Class	Not available.
Subsidiary risk	-
Packing group	Not available.
Environmental hazards	
Marine pollutant	No
Special precautions for user	Not available.

IATA

UN number	Not available.
------------------	----------------

UN proper shipping name Not Regulated
Transport hazard class(es)
Class Not available.
Subsidiary risk -
Packing group Not available.
Environmental hazards No
Special precautions for user Not available.

IMDG

UN number Not available.
UN proper shipping name Not Regulated
Transport hazard class(es)
Class Not available.
Subsidiary risk -
Packing group Not available.
Transport hazard class(es)
Marine pollutant No
EmS Not available.
Special precautions for user Not available.

ADR

UN number Not available.
UN proper shipping name Not Regulated
Transport hazard class(es)
Class Not available.
Subsidiary risk -
Hazard No. (ADR) Not available.
Tunnel restriction code Not available.
Packing group Not available.
Environmental hazards No
Special precautions for user Not available.

Further information Not a dangerous good under DOT, IATA, ADR, IMDG, or RID.

Transport in bulk according to Annex II of MARPOL73/78 and the IBC code: Not applicable.

15. Regulatory information

US federal regulations US TSCA 12(b): Does not contain listed chemicals.
US EPA TSCA Inventory: All chemical substances in this product comply with all rules or orders under TSCA.

Toxic Substances Control Act (TSCA)

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

CERCLA Hazardous Substance List (40 CFR 302.4)

Not listed.

SARA 304 Emergency release notification

Not regulated.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1053)

Not listed.

Superfund Amendments and Reauthorization Act of 1986 (SARA)

SARA 302 Extremely hazardous substance

Not listed.

SARA 311/312 Hazardous chemical Yes

Classified hazard categories Respiratory or skin sensitization

Other federal regulations

Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List

No intentionally added HAP substances.

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

Not regulated.

Safe Drinking Water Act (SDWA)

Not regulated.

Other information

VOC content (less water, less exempt compounds) = < 946 g/L (U.S. requirement, not for emissions)
VOC data based on formulation (Organic compounds minus solids)

Clean Air Act (CAA)

No intentionally added HAPS substances

Regulatory information

All chemical substances in this HP product have been notified or are exempt from notification under chemical substances notification laws in the following countries: US (TSCA), EU (EINECS/ELINCS), Switzerland, Canada (DSL/NDSL), Australia, Japan, Philippines, South Korea, New Zealand, and China.

16. Other information, including date of preparation or last revision**Issue date**

11-Jun-2016

Revision date

10-Dec-2021

Version #

14

Other information

This SDS was prepared in accordance with USA OSHA Hazard Communications regulation (29 CFR 1910.1200).

Disclaimer

This safety data sheet is meant to convey information about HP inks (toners) provided in HP Original ink (toner) supplies. If our Safety Data Sheet has been provided to you with a refilled, remanufactured, compatible or other non-HP Original supply please be aware that the information contained herein was not meant to convey information about such products and there could be considerable differences from information in this document and the safety information for the product you purchased. Please contact the seller of the refilled, remanufactured or compatible supplies for applicable information, including information on personal protective equipment, exposure risks and safe handling guidance. HP does not accept refilled, remanufactured or compatible supplies in our recycling programs. This Safety Data Sheet document is provided without charge to customers of HP. Data is the most current known to HP at the time of preparation of this document and is believed to be accurate. It should not be construed as guaranteeing specific properties of the products as described or suitability for a particular application. This document was prepared to the requirements of the jurisdiction specified in Section 1 above and may not meet regulatory requirements in other countries.

Revision information

1. Product and Company Identification: Product and Company Identification

Hazard(s) identification: Hazard statement

Hazard(s) identification: Disposal

Hazard(s) identification: Prevention

Hazard(s) identification: Response

Hazard(s) identification: GHS Signal Words

Hazard(s) identification: GHS Symbols

Hazard(s) identification: Supplemental information

Composition / Information on Ingredients: Ingredients

Toxicological information: Corrosivity

Toxicological information: Skin contact

Explanation of abbreviations

ACGIH	American Conference of Governmental Industrial Hygienists
CAS	Chemical Abstracts Service
CERCLA	Comprehensive Environmental Response Compensation and Liability Act
CFR	Code of Federal Regulations
COC	Cleveland Open Cup
DOT	Department of Transportation
EPCRA	Emergency Planning and Community Right-to-Know Act (aka SARA)
IARC	International Agency for Research on Cancer
NIOSH	National Institute for Occupational Safety and Health
NTP	National Toxicology Program
OSHA	Occupational Safety and Health Administration
PEL	Permissible Exposure Limit
RCRA	Resource Conservation and Recovery Act
REC	Recommended
REL	Recommended Exposure Limit
SARA	Superfund Amendments and Reauthorization Act of 1986
STEL	Short-Term Exposure Limit
TCLP	Toxicity Characteristics Leaching Procedure
TLV	Threshold Limit Value
TSCA	Toxic Substances Control Act
VOC	Volatile Organic Compounds