marathon®

Other Purpose Motors

Model No: 215TTDW7205
Catalog No: Y469

Other Purpose Motor, 5 & 1.25 HP, 3 Ph, 60 & 60 Hz, 460 & 460 V, 1800 RPM, 215T Frame, DP

©2026 Marathon, All Rights Reserved.

marathon®

Product Information Packet: Model No: 215TTDW7205, Catalog No: Y469 Other Purpose Motor, 5 & 1.25 HP, 3 Ph, 60 & 60 Hz, 460 & 460 V, 1800 RPM, 215T Frame, DP

Nameplate Specifications

Phase	**3**	Output HP	**5 & 1.25 Hp**
Output KW	**3.7 & 0.93 kW**	Voltage	**460 & 460 V**
Speed	**1765 & 885 r/min**	Synchronous RPM	**1800 & 900 r/min**
Service Factor	**1.15 & 1.15**	Frame	**215T**
Enclosure	**Drip Proof**	Thermal Protection	**No Protection**
Efficiency	**86.5 & 72 %**	Ambient Temperature	**40 °C**
Frequency	**60 & 60 Hz**	Current	**6.8 & 3.1 A**
Power Factor	**83**	Duty	**Continuous**
Insulation Class	**F**	Design Code	**2VT**
KVA Code	**K**	Drive End Bearing Size	**6307**
Opp Drive End Bearing Size	**6206**	UL	**Recognized**
CSA	**Y**	CE	**Y**
IP Code	**22**	Number of Speeds	**2**

Technical Specifications


Electrical Type	**Squirrel Cage Induction Run**	Starting Method	**Across The Line**
Poles	**4//8**	Rotation	**Selective Clockwise**
Resistance Main	**3.2 O**	Mounting	**Rigid Base**
Motor Orientation	**Horizontal**	Drive End Bearing	**Ball**
Opp Drive End Bearing	**Ball**	Frame Material	**Rolled Steel**
Shaft Type	**T**	Overall Length	**17.3 in**
Frame Length	**11.15 in**	Shaft Diameter	**1 3/8 in**
Shaft Extension	**3.47 in**	Assembly/Box Mounting	**F1/F2 Capable**


Drawings

Connection Drawing	**A-EE7317**	Outline Drawing	**A-SS86500-1115**

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created: 16/10/2026

Uncontrolled Copy





NOTES:
1. NAMEPLATE TO BE READ FROM C'BOX SIDE OF MOTOR.
2. BOX CAN BE MOUNTED IN 90° STEPS.
3. BOX CAN BE MOUNTED ON OPPOSITE SIDE BY REMOVING BRACKETS AND TURNING FRAME 180°. (EXCEPT AS NOTED.)

DASH	FR.	C	BS	MOUNTING
1115	213/15T	17.30	6.93	F1/F2
1240	213/15T	18.55	8.18	F1 ONLY

DRAWING REVISION	REVISION BY	REV DATE/ © DATE
U	SB	04/22/2026
REQUEST NUMBER	APPROVED BY	DATE
CR-0026044	RMS	04/22/2026

REQUEST NUMBER DESCRIPTION
DRAWING TITLE BLOCK UPDATED

COPYRIGHT (PER REVISION DATE) MARATHON ELECTRIC, LLC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF MARATHON ELECTRIC, LLC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.

TOLERANCES (EXCEPT AS NOTED):

DEC.	INCH	mm	ANGLE
.X	±0.1	[±3]	±7' 30"
.XX	±0.03	[±0.8]	
.XXX	±0.005	[±0.13]	
.XXXX	±0.0005	[±0.013]	

REMOVE BURRS & BREAK SHARP EDGES: .003/.015 [.08/.38] X 45 °
CORNER FILLETS: R.02 [.5]
MACHINED SURFACES: 200 INCH / 5.1 mm
mm DIMENSIONS IN [BRACKETS] ARE FOR REFERENCE ONLY

DRAWN BY	SMC
DATE	04/13/1993
APPROVED BY	DRN
DATE	04/13/1993
REFERENCE	
THIRD ANGLE PROJECTION	

marathon™

DESCRIPTION
OUTLINE
210 FR - BB - TS DR. PR.

MATERIAL	PROCESS/FINISH

SIZE	DRAWING NUMBER	SHEET
A	SS86500	1 OF 1

LOW SPEED

(1U) T1 — L1
(1V) T2 — L2
(1W) T3 — L3
(2U) T11
(2V) T12
(2W) T13

INSULATE EACH SEPARATELY

HIGHSPEED


(1U) T1
(1V) T2
(1W) T3

INSULATE EACH SEPARATELY

(2U) T11 — L1
(2V) T12 — L2
(2W) T13 — L3

TO REVERSE ROTATION ON EITHER SPEED: INTERCHANGE ANY 2 LEADS ON THE WINDING IN USE.

THREE PHASE, SINGLE VOLT, 6 LEAD
2 SPEED REVERSIBLE MOTOR



VIEW OF TERMINAL END

DRAWING REVISION: D	REVISION BY: SB	REV DATE/© DATE: 10/08/2025	PRIMARY DIMENSIONS ARE INCH mm DIMENSIONS IN [BRACKETS] ARE FOR REFERENCE ONLY	DRAWN BY: LZ	marathon™
REQUEST NUMBER: CR-0024284	APPROVED BY: RMS	DATE: 10/08/2025		DATE: 01-05-1994	
REQUEST NUMBER DESCRIPTION: DRAWING TITLE BLOCK UPDATED				APPROVED BY: GK	DESCRIPTION: CONN DIAGRAM-INTERNAL, 3 PHASE - SINGLE - 2 SPEED REVERSIBLE
				DATE: 01-17-1994	
				REFERENCE	MATERIAL / PROCESS/FINISH
				THIRD ANGLE PROJECTION	SIZE: A; DRAWING NUMBER: EE7317; SHEET: 1 OF 1

COPYRIGHT (PER REVISION DATE) MARATHON ELECTRIC, LLC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF MARATHON ELECTRIC, LLC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.

Uncontrolled Copy

MARATHON ELECTRIC CORPORATION


TYPICAL PERFORMANCE CURVE for AC MOTOR

Customer CATALOG **Curve at** 460 **Volts** **HP** 5&1.25 **PHASE** 3

60 **HZ**

Model No 215TTDW7205 5 **HP** **VOLTS** 460&460

Catalog No Y469 **HZ** 60&60 **RPM** 1765&885



#N/A

FL TORQUE	15	#N/A	**FL AMPS**	6.8	
BD TORQUE	16.6	#N/A	**PU TORQUE**	2.0	#N/A
LR TORQUE	5.2	#N/A	**LR AMPS**	9.4	
WINDING	K215(4-8)111-2	**Prepared By**	SRIKANTH	**Date**	6/21/2017

Uncontrolled Copy

CERTIFICATION DATA SHEET

Model#:	215TTDW7205 AA	**WINDING#:**	K215(4-8)111 NONE 2
CONN. DIAGRAM:	A-EE7317	**ASSEMBLY:**	F1/F2 CAPABLE
OUTLINE:	A-SS86500-1115		

TYPICAL MOTOR PERFORMANCE DATA

HP	KW	SYNC. RPM	F.L. RPM	FRAME	ENCLOSURE	KVA CODE	DESIGN
5&1 1/4	3.70&0.93	900	1765&885	215T	DP	K	2VT

PH	Hz	VOLTS	FL AMPS	START TYPE	DUTY	INSL	S.F	AMB°C	ELEVATION
3	60/60	460	6.8&3.1	ACROSS THE LINE	CONTINUOUS	F4	1.15/1.15	40	3300

FULL LOAD EFF: 86.5&72	3/4 LOAD EFF: 68	1/2 LOAD EFF: 62	GTD. EFF	ELEC. TYPE	NO LOAD AMPS
FULL LOAD PF: 83&54	3/4 LOAD PF: 45.5	1/2 LOAD PF: 36	66.4	SQ CAGE IND RUN	2.6

F.L. TORQUE	LOCKED ROTOR AMPS	L.R. TORQUE	B.D. TORQUE	F.L. RISE°C
7.6 LB-FT	9.4	5.2 LB-FT 68	16.56 LB-FT 218	45

SOUND PRESSURE @ 3 FT.	SOUND POWER	ROTOR WK^2	MAX. WK^2	SAFE STALL TIME	STARTS /HOUR	APPROX. MOTOR WGT
62 dBA	72 dBA	0.8 LB-FT^2	- LB-FT^2	10 SEC.	-	98 LBS.

*** SUPPLEMENTAL INFORMATION ***

DE BRACKET TYPE	ODE BRACKET TYPE	MOUNT TYPE	ORIENTATION	SEVERE DUTY	HAZARDOUS LOCATION	DRIP COVER	SCREENS	PAINT
STANDARD	STANDARD	RIGID	HORIZONTAL	FALSE	NONE	FALSE	NONE	BLUE (ENAMEL)

BEARINGS		GREASE	SHAFT TYPE	SPECIAL DE	SPECIAL ODE	SHAFT MATERIAL	FRAME MATERIAL
DE	OPE						
BALL 6307	BALL 6206	POLYREX EM	T	NONE	NONE	AISI 1045 (C-240)	ROLLED STEEL

THERMO-PROTECTORS				THERMISTORS	CONTROL	SPACE /n HEATERS
THERMOSTATS	PROTECTORS	WDG RTDs	BRG RTDs			
NONE	NOT	NONE	NONE	NONE	FALSE	NONE VOLTS

If Inverter equals NONE, contact factory for further information

INVERTER TORQUE: NONE
INV. HP SPEED RANGE: NONE

ENCODER: NONE
NONE NONE
NONE NONE PPR

BRAKE: NONE NONE
NONE P/N NONE
NONE NONE
NONE FT-LB NONE V NONE Hz

* NOTES *

DATE: 06/20/2017 08:57:44 AM
FORM 3531 REV.3 02/07/99
** Subject to change without notice.