SECTION 1. PRODUCT AND COMPANY IDENTIFICATION

Material name : ZEP MOLD STAIN & MILDEW STAIN REMOVER 1GL 4CT

Material number : ZUMILDEW128

Manufacturer or supplier's details

Company : Zep Inc.

Address : 350 Joe Frank Harris Parkway, SE
Emerson, GA 30137

Telephone : Compliance Services - 877-428-9937

Emergency telephone numbers

For SDS Information	:	Compliance Services - 877-428-9937
For a Medical Emergency	:	877-541-2016 Toll Free - All Calls Recorded
For a Transportation Emergency	:	CHEMTREC: 800-424-9300 - All Calls Recorded. In the District of Columbia 202-483-7616

Recommended use of the chemical and restrictions on use

Recommended use : BATHROOM CARE

Note: This product is labeled as a consumer product in accordance with the United States Consumer Product Safety Commission regulations. The warnings presented below in this Safety Data Sheet (SDS) comply with the 2012 OSHA Hazard Communication Standard (GHS - Globally Harmonized System of Classification and Labeling). The requirements for the labeling and warnings of consumer products may differ from those required for GHS based hazard communication.

SECTION 2. HAZARDS IDENTIFICATION

Emergency Overview

Appearance	liquid
Colour	colourless
Odour	slight chlorine

GHS Classification

Skin corrosion : Category 1
Serious eye damage : Category 1

GHS label elements

Hazard pictograms :



Corrosion

Signal word : Danger

Hazard statements : H314 Causes severe skin burns and eye damage.

Precautionary statements : **Prevention:**
P264 Wash skin thoroughly after handling.
P280 Wear protective gloves/ protective clothing/ eye protection/ face protection.
Response:
P301 + P330 + P331 IF SWALLOWED: Rinse mouth. Do NOT induce vomiting.
P303 + P361 + P353 IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower.
P304 + P340 + P310 IF INHALED: Remove person to fresh air and keep comfortable for breathing. Immediately call a POISON CENTER/doctor.
P305 + P351 + P338 + P310 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Immediately call a POISON CENTER/doctor.
P363 Wash contaminated clothing before reuse.
Disposal:
P501 Dispose of contents/container in accordance with local regulation.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Substance / Mixture : Mixture

Hazardous components

Chemical name	CAS-No.	Concentration [%]
sodium hypochlorite	7681-52-9	>= 3 - < 5

The exact percentages of disclosed substances are withheld as trade secrets.

SECTION 4. FIRST AID MEASURES

General advice : Move out of dangerous area.
Consult a physician.
Show this safety data sheet to the doctor in attendance.
Do not leave the victim unattended.

If inhaled : If unconscious, place in recovery position and seek medical advice.
If symptoms persist, call a physician.

In case of skin contact : Immediate medical treatment is necessary as untreated wounds from corrosion of the skin heal slowly and with difficulty.
Wash off immediately with plenty of water for at least 15 minutes.
Remove contaminated clothing and shoes.
Wash contaminated clothing before reuse.
If skin irritation persists, call a physician.

In case of eye contact	:	Small amounts splashed into eyes can cause irreversible tissue damage and blindness. Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Continue rinsing eyes during transport to hospital. Remove contact lenses. Protect unharmed eye. If eye irritation persists, consult a specialist.
If swallowed	:	Clean mouth with water and drink afterwards plenty of water. Keep respiratory tract clear. DO NOT induce vomiting unless directed to do so by a physician or poison control center. Never give anything by mouth to an unconscious person. If symptoms persist, call a physician. Take victim immediately to hospital.
Most important symptoms and effects, both acute and delayed	:	Symptoms may include blistering, irritation, burns, and pain. Causes severe skin burns and eye damage. Review section 2 of SDS to see all potential hazards.
Notes to physician	:	Treat symptomatically. Symptoms may be delayed.

SECTION 5. FIREFIGHTING MEASURES

Suitable extinguishing media	:	Water spray jet Alcohol-resistant foam Carbon dioxide (CO2) Dry chemical
Unsuitable extinguishing media	:	High volume water jet
Specific hazards during firefighting	:	Do not allow run-off from fire fighting to enter drains or water courses.
Hazardous combustion products	:	No hazardous combustion products are known
Specific extinguishing methods	:	Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
Further information	:	Collect contaminated fire extinguishing water separately. This must not be discharged into drains. Fire residues and contaminated fire extinguishing water must be disposed of in accordance with local regulations.
Special protective equipment for firefighters	:	Wear self-contained breathing apparatus for firefighting if necessary.

SECTION 6. ACCIDENTAL RELEASE MEASURES

Personal precautions,	:	Use personal protective equipment.

protective equipment and emergency procedures
Environmental precautions : Prevent product from entering drains.
Prevent further leakage or spillage if safe to do so.
If the product contaminates rivers and lakes or drains, inform respective authorities.

Methods and materials for containment and cleaning up : Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust).
Keep in suitable, closed containers for disposal.

SECTION 7. HANDLING AND STORAGE

Advice on safe handling : Do not breathe vapours/dust.
Avoid contact with skin and eyes.
For personal protection see section 8.
Smoking, eating and drinking should be prohibited in the application area.
To avoid spills during handling keep bottle on a metal tray.
Dispose of rinse water in accordance with local and national regulations.

Conditions for safe storage : Keep container tightly closed in a dry and well-ventilated place.
Containers which are opened must be carefully resealed and kept upright to prevent leakage.
Observe label precautions.
Electrical installations / working materials must comply with the technological safety standards.

Materials to avoid : Do not store near acids.
Oxidizing agents

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Components with workplace control parameters

Components	CAS-No.	Value type (Form of exposure)	Control parameters / Permissible concentration	Basis
sodium hypochlorite	7681-52-9	STEL	2 mg/m3	US WEEL

Engineering measures : effective ventilation in all processing areas

Personal protective equipment

Respiratory protection : In case of insufficient ventilation, wear suitable respiratory equipment.

Hand protection
Material : Protective gloves
Remarks : The suitability for a specific workplace should be discussed

with the producers of the protective gloves.

Eye protection	:	Wear face-shield and protective suit for abnormal processing problems. Tightly fitting safety goggles
Skin and body protection	:	Impervious clothing Choose body protection according to the amount and concentration of the dangerous substance at the work place.
Hygiene measures	:	When using do not eat or drink. When using do not smoke. Wash hands before breaks and at the end of workday.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance	:	liquid
Colour	:	colourless
Odour	:	slight chlorine
Odour Threshold	:	No data available
pH	:	12.5 - 13.0
Melting point/freezing point	:	No data available
Boiling point	:	> 100 °C
Flash point	:	does not flash
Evaporation rate	:	1
Upper explosion limit	:	No data available
Lower explosion limit	:	No data available
Vapour pressure	:	No data available
Relative vapour density	:	No data available
Density	:	1.04 g/cm3
Solubility(ies)		
Water solubility	:	soluble
Partition coefficient: n-octanol/water	:	No data available
Auto-ignition temperature	:	not determined
Thermal decomposition	:	No data available
Viscosity		
Viscosity, kinematic	:	No data available

SECTION 10. STABILITY AND REACTIVITY

Reactivity	:	Stable
Chemical stability	:	Stable under normal conditions.
Possibility of hazardous reactions	:	No decomposition if stored and applied as directed.
Conditions to avoid	:	No data available
Incompatible materials	:	Acids Aluminium Metals Oxidizing agents Reducing agents Ammonia
Hazardous decomposition products	:	Carbon oxides Chlorine

SECTION 11. TOXICOLOGICAL INFORMATION

Potential Health Effects

Aggravated Medical Condition	:	None known.
Symptoms of Overexposure	:	Symptoms may include blistering, irritation, burns, and pain. Causes severe skin burns and eye damage. Review section 2 of SDS to see all potential hazards. Treat symptomatically. Symptoms may be delayed.

Carcinogenicity:

IARC	No component of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.
ACGIH	No component of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by ACGIH.
OSHA	No component of this product present at levels greater than or equal to 0.1% is on OSHA's list of regulated carcinogens.
NTP	No component of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.

Acute toxicity

Product:

Acute oral toxicity	:	Acute toxicity estimate : > 5,000 mg/kg Method: Calculation method

Skin corrosion/irritation

Product:

Remarks: Extremely corrosive and destructive to tissue.

Serious eye damage/eye irritation

Product:

Remarks: May cause irreversible eye damage.

Respiratory or skin sensitisation

No data available

Germ cell mutagenicity

No data available

Carcinogenicity

No data available

Reproductive toxicity

No data available

STOT - single exposure

No data available

STOT - repeated exposure

No data available

Aspiration toxicity

No data available

Further information

Product:

Remarks: No data available

SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity

No data available

Persistence and degradability

No data available

Bioaccumulative potential

Product:

Partition coefficient: n-octanol/water : Remarks: No data available

Mobility in soil

No data available

Other adverse effects

No data available

Product:

Regulation	40 CFR Protection of Environment; Part 82 Protection of Stratospheric Ozone - CAA Section 602 Class I Substances
Remarks	This product neither contains, nor was manufactured with a Class I or Class II ODS as defined by the U.S. Clean Air Act Section 602 (40 CFR 82, Subpt. A, App.A + B).

Additional ecological information : An environmental hazard cannot be excluded in the event of unprofessional handling or disposal., Toxic to aquatic life with long lasting effects.

SECTION 13. DISPOSAL CONSIDERATIONS

Disposal methods

Waste from residues : The product should not be allowed to enter drains, water courses or the soil.
Do not contaminate ponds, waterways or ditches with chemical or used container.
Dispose of in accordance with local regulations.

Contaminated packaging : Empty remaining contents.
Dispose of as unused product.
Do not re-use empty containers.

SECTION 14. TRANSPORT INFORMATION

Transportation Regulation: 49 CFR (USA):
UN1791, Hypochlorite solutions, 8, III - Limited quantity

Transportation Regulation: IMDG (Vessel):
UN1791, HYPOCHLORITE SOLUTION, 8, III - Limited quantity

Transportation Regulation: IATA (Cargo Air):
UN1791, Hypochlorite solution, 8, III

Transportation Regulation: IATA (Passenger Air):
UN1791, Hypochlorite solution, 8, III

Transportation Regulation: TDG (Canada):
UN1791, HYPOCHLORITE SOLUTION, 8, III - Limited quantity

The product as delivered to the customer conforms to packaging requirements for shipment by road under US Department of Transportation (DOT) regulations. Additional transportation classifications noted above are for reference only, and not a certification or warranty of the suitability of the packaging for shipment under these alternative transport regulations.

SECTION 15. REGULATORY INFORMATION

TSCA list : No substances are subject to a Significant New Use Rule.

No substances are subject to TSCA 12(b) export notification requirements.

EPCRA - Emergency Planning and Community Right-to-Know Act

CERCLA Reportable Quantity

Components	CAS-No.	Component RQ (lbs)	Calculated product RQ (lbs)
sodium hypochlorite	7681-52-9	100	3143

SARA 304 Extremely Hazardous Substances Reportable Quantity

This material does not contain any components with a section 304 EHS RQ.

SARA 311/312 Hazards : Skin corrosion or irritation
Serious eye damage or eye irritation

SARA 302 : No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

SARA 313 : This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

California Prop. 65

This product does not contain any chemicals known to State of California to cause cancer, birth defects, or any other reproductive harm.

The components of this product are reported in the following inventories:

DSL All components of this product are on the Canadian DSL
TSCA On TSCA Inventory

For information on the country notification status for other regions please contact the manufacturer’s regulatory group.

Inventory Acronym and Validity Area Legend:

TSCA (USA), DSL (Canada), NDSL (Canada)

SECTION 16. OTHER INFORMATION

Further information

NFPA:

HEALTH	3
FLAMMABILITY	0
INSTABILITY	0
SPECIAL HAZARD.	

0 = not significant, 1 =Slight,
2 = Moderate, 3 = High
4 = Extreme

HMIS III:

HEALTH	3
FLAMMABILITY	0
PHYSICAL HAZARD	0

0 = not significant, 1 =Slight,
2 = Moderate, 3 = High
4 = Extreme, * = Chronic

OSHA - GHS Label Information:

Hazard pictograms :



Corrosion

Signal word : **Danger:**
Hazard statements : Causes severe skin burns and eye damage.
Precautionary statements :

Prevention: Wash skin thoroughly after handling. Wear protective gloves/ protective clothing/ eye protection/ face protection.
Response: IF SWALLOWED: Rinse mouth. Do NOT induce vomiting. IF ON SKIN (or

hair): Take off immediately all contaminated clothing. Rinse skin with water/shower. IF INHALED: Remove person to fresh air and keep comfortable for breathing. Immediately call a POISON CENTER/doctor. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Immediately call a POISON CENTER/doctor. Wash contaminated clothing before reuse.

Disposal: Dispose of contents/container in accordance with local regulation.

Version:	2.2
Revision Date:	10/01/2023
Print Date:	10/27/2026

We believe the statements, technical information and recommendations contained herein are reliable, but they are given without warranty or guarantee of any kind. The information in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. Users should make their own investigations to determine the suitability and applicability of the information for their particular purposes. This SDS has been prepared by the Compliance Services organization supporting this manufacturer, supplier or distributor.