



TEGERA® 8830R

Learn more

AT RISK OF CUTS WHEN IT IS COLD AND DRY

Glove with cold protection in combination with high cut protection (Level D), nitrile-foam palm dipped with pattern for good grip. Food approved, 10 gg and CRF cut resistance technology. The glove is durable, soft and warm and the nitrile foam dipping gives a sandy feeling. Perfect for good grip when there is cut risks in cold and dry environments.

CHARACTERISTICS

- High level of protection
- Flexible
- Durable
- Good grip
- Comfortable
- Warm

FUNCTIONS

- Withstands contact heat up to 250°C
- Approved for handling foodstuffs
- Reinforcement between index finger and thumb

CRF®

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF
Cut injuries, Scratches, lacerations, Contact with cold

PRIMARY ENVIRONMENTS OF USE
Cut risk environments, Dry environments, Cold environments, Moist environments

PRIMARY AREAS OF USE
Building and construction, Construction, Machine driving

PRIMARY INDUSTRIES OF USE
Automotive repair and maintenance, Agriculture, forestry and fishing, Facility management services, Basic metals manufacturing, Transportation and logistics, Building and construction, Mining and quarrying, Warehousing

TYPE OF WORK
Medium weight

SPECIFICATION
TYPE Cold insulation gloves, Cut resistant gloves, Heat protection gloves
CATEGORY Cat. II
LINING Winter-lined
KNITTING GAUGE (GG) 10
LINING MATERIAL Acrylic, CRF® Technology, HPPE, Polyester, Stainless steel fibre yarn
LENGTH 250-285 mm
DEXTERITY 4
GRIP DESIGN Foam grip pattern
COLOUR Black
PAIRS PER: BUNDLE/CARTON 6/72
DISPLAY TYPE Hangtag with euro slot
DIPPING Palm-dipped
DIPPING MATERIAL Nitrile foam
CUFF STYLE Knitwrist cuff
CUFF MATERIAL Textile
CUT RESISTANCE (EN ISO 13997) Cut resistance level D
CUT RESISTANCE (EN ISO 13997) TDM: 22 N
INNER MATERIAL SPECIFICATION Acrylic, HPPE (High performance polyethylene), Stainless steel fibre yarn, Polyester
OUTER MATERIAL SPECIFICATION Nitrile

COMPLIANCE
CE Cat. II

EAC TP TC 019:2011

EN ISO 21420:2020

EN 388:2016+A1:2018 4X42D

EN 407:2020 (No flame protection) X2XXXX

EN 511:2006 01X

ANSI A5 CUT

ANSI 5 ABR

Contact heat rating valid for palm area only

FEATURES
Cut protection

Warm lining

SIZE		ARTICLE NUMBER	EAN
6	XS	8830R-6	7340118452715
7	S	8830R-7	7340118387864
8	M	8830R-8	7340118387956
9	L	8830R-9	7340118388045
10	XL	8830R-10	7340118388137
11	XXL	8830R-11	7340118388229
12	3XL	8830R-12	7340118408514

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.