LED-DISPLAY

PCE-G1



- **Ingress protection type: IP 54 rating**
- **Large, easy-to-read 1 mm / 3.9 in tall LED digits**
- **Temperature and relative humidity values are displayed every 2 seconds (in**
- **2-second intervals)**
- **Displays temperature in degrees Celsius (°C) only**
- **Ready for wall mounting**
- **Long life**
- **Excellent readability**
- **High accuracy**

The environmental tester is intended for stationary measurement of relative humidity and temperature and direct display on a large display. This large display consists of a large monochrome display and is protected according to IP 54.

The measured variables are displayed alternately: relative humidity (2 s) and temperature (2 s). The sensors of the humidity and temperature meter are calibrated at the factory. However, an ISO calibration certificate can also be ordered as an option. Simple, accurate and robust.

Specification

Relative humidity	
Measuring range up to	10 ... 95 %RH
Resolution	1 %RH
Accuracy	±2% RH
Temperature	
Measuring range up to	0 ... 60 °C
Resolution	1 °C
Accuracy	±1°C

General technical data	
cable length	1 m
Display Typ	LCD
Current consumption measuring device	20 mA DC
Response time	4 s
Dimensions	Sensor 50 x 70 x 20 mm
Sensoren	Capacitive, Pt1000
Visibility	50 m
Protection class (device)	IP54
Power supply	230 V / 50 ... 60 Hz
Operating conditions	0 ... 60 °C , 0 ... 95 %RH
Storage conditions	0 ... 60 °C , 0 ... 80 %RH
Dimensions (L x W x H)	175 x 175 x 75 mm
Weight	1300 g

PCE Americas Inc. dba PCE Instruments
1201 Jupiter Park Drive, Suite 8
Jupiter, FL 33458
USA

Phone: +1-561-320-9162
info@pce-americas.com