•TRUSTED QUALITY SINCE 1921•
RUST-OLEUM® SPECIALTY

RUST-OLEUM® GLITTER SPRAYS

DESCRIPTION AND USES

Rust-Oleum® Glitter Sprays are designed to provide a sparkle finish on many surfaces including wood, metal, wicker, ceramic, pottery, craft foam, paper, plastic, and more.

For added protection, topcoat with Rust-Oleum Glitter Sealer. The clear topcoat helps prevent Glitter from flaking and fading while maintaining the sparkle finish. Use of any other clear topcoat may dull glitter shine. For use on interior items only. For best color results, spray a Rust-Oleum Stops Rust or 2X undercoat of a similar color.

PRODUCTS

SKU	DESCRIPTION (10.25 oz. Aerosol)
267736	Glitter Clear Sealer
268045	Glitter Red
277781	Glitter Kelly Green
299424	Glitter Midnight Black
299425	Glitter Royal Blue
299426	Glitter Pearl White
301495	Glitter Gold
301814	Glitter Silver
301818	Glitter Bright Pink
302573	Glitter Turquoise
342607	Glitter Multi Color Purple
344697	Glitter Rose Gold
344696	Glitter Copper
398582	Glitter Rainbow

PRODUCT APPLICATION

SURFACE PREPARATION

Remove all dirt, grease, oil, salt, and chemical contaminants by washing the surface with a commercial detergent, or other suitable cleaning method. Rinse with fresh water and allow to thoroughly dry. Remove loose paint and rust with a wire brush or sandpaper. Lightly sand glossy surfaces to create a surface profile.

WARNING! If you scrape, sand, or remove old paint from any surface, you may release lead paint dust. LEAD IS TOXIC. EXPOSURE TO LEAD DUST CAN CAUSE SERIOUS ILLNESS, SUCH AS BRAIN DAMAGE, ESPECIALLY IN CHILDREN. PREGNANT WOMEN SHOULD ALSO AVOID EXPOSURE. Wear a NIOSH approved respirator to control lead exposure. Clean up carefully with a HEPA vacuum and a wet mop. Before you start, find out how to protect yourself and your family by contacting the National Lead Information Hotline at 1-800-424-LEAD or log on to www.epa.gov/lead.

PRODUCT APPLICATION (cont.)

PRIMING

Use of a Rust-Oleum Stops Rust or 2X primer or basecoat provides excellent adhesion and hiding and is especially recommended for bare wood and metal. A primer is not recommended for craft foam and paper.

APPLICATION

Use outdoors or in a well-ventilated area such as an open garage. Use when temperature is between 50ºF (10ºC) and 90ºF (32ºC) and humidity is below 65% to ensure proper drying. Do not apply to surfaces that, when heated, exceed 200°F (93°C). Avoid spraying in very windy and dusty conditions. Cover surrounding area to protect from spray mist.

Shake can vigorously for one minute after the mixing ball begins to rattle. If mixing ball fails to rattle, DO NOT STRIKE CAN. Contact Rust-Oleum. Shake often during use. Hold can upright 12-14” from surface and spray in a steady back-and-forth motion, slightly overlapping each stroke. Keep the can the same distance from the surface. Keep the can in motion while spraying. Apply two or more light coats a few minutes apart. **Do not use near open flame.**

DRY & RECOAT

Dry and recoat times are based on 77ºF and 50% relative humidity. Allow more time at cooler temperatures. Dries to touch in 20 minutes, to handle in 1 hour, and fully dry in 24 hours. Recoat at any time.

CLEAN-UP

When finished spraying, clear valve by turning can upside down and pushing spray button for 5 seconds. Clean-up wet paint with xylene or mineral spirits. Properly discard empty container. Do not burn or place in home trash compactor.

CLOGGING

If the valve clogs, twist and pull off spray tip and rinse in a solvent such as mineral spirits. Do not insert any object into can valve opening.

Form: GDH-857
Rev.: 011526

	TECHNICAL DATA	SPC-31

•TRUSTED QUALITY SINCE 1921•
RUST-OLEUM®
SPECIALTY

RUST-OLEUM® GLITTER SPRAYS

PHYSICAL PROPERTIES

		GLITTER SPRAYS
Resin Type		Acrylic
Pigment Type		Glitter Flake
MIR		0.95 Max
Fill Weight		10.25 ounces
Practical Coverage (assumes 15% material loss)		3-5 sq. ft./can (Colors) 6-10 sq. ft./can (Clear)
Dry Times at 77ºF (25ºC) and 50% Relative Humidity	**Touch**	20 minutes
	Handle	1 hour
	Recoat	Anytime
Shelf Life		5 years
Flash Point		-141°F (-96°C)
Safety Information		For additional information, see SDS

Calculated values are shown and may vary from the actual manufactured material.

The technical data and suggestions for use contained herein are correct to the best of our knowledge, and offered in good faith. The statements of this literature do not constitute a warranty, express, or implied, as to the performance of these products. As conditions and use of our materials are beyond our control, we can guarantee these products only to conform to our standards of quality, and our liability, if any, will be limited to replacement of defective materials. All technical information is subject to change without notice.