

THICKNESS METER

PCE-TG 300-N05



- » **Large measuring range**
- » **Various sensors available**
- » **Battery operation**
- » **Error and voids detection**
- » **Internal measurement data memory**
- » **Print via Bluetooth**

The PCE-TG 300-N05 is a thickness meter with special sensors for various applications. In general, the wall thicknesses of all homogeneous materials can be measured with the thickness meter. For damping or scattering materials such as plastic or cast a special sensor is available. An angled 90° sensor also enables measurements at hard-to-reach measuring points. The speed of sound can be set freely on the thickness meter and thus adapted to a wide variety of materials.

The measured values are displayed directly on the easy-to-read TFT color display. Due to the internal memory, which can be read out via the optionally available software, different measuring points can be clearly stored. The non-destructive ultrasound measuring method enables the measurement even on end products. Thanks to the Echo-Echo working mode, even coated workpieces can be measured.

Specification

Material thickness	
Measurement range up to	0,65 ... 600 mm
Resolution	0,01 mm
Accuracy	±0.04 mm H[mm] (<10 mm); ±0.4 % H[mm] (>10 mm); H refers to the material thickness of the workpiece
Sensor	
Designation	PCE-TG-N05
Measurement range up to	1 ... 600 mm
Battery type	Ultrasound
Frequency	5 MHz
Measurable materials	Metals--Plastic--Ceramics--Epoxy resin--Glass--Other homogeneous materials
Minimum diameter of pipes	20 mm
Dimension	Ø 10 mm
Additional description	Normal measurement

General technical data	
Units	mm
Display type	TFT colour display
Display size	2,4 Inch
Storage medium	Internal memory
Storage capacity	10000 Values
Memory capacity (additional information)	Non-volatile memory
Interface	Bluetooth, Mini-USB
Operating time	100 h
Automatic power-off from...to	2 ... 10 min.
Automatic power-off can be deactivated	Yes
Adjustable sound velocity	1422 ... 6400 m/s
Menu language	German, English, French, Spanish, Italian
(Rechargeable) battery	4 x 1,5 V AA battery , Alkali-manganese
Capacity	3000 mAh
Operating conditions	0 ... 50 °C , 0 ... 80 % RH
Storage conditions	-20 ... 70 °C , 0 ... 80 % RH
Dimensions (L x W x H)	185 x 97 x 40 mm
Other dimensions	Sensor PCE-TG-N05 Ø 10 mm
Weight	375 g