



UN38.3 测试概要

Test summary of UN38.3

电池或电池组说明 Description of cell or battery: 型号 Model No.: 112265 名称 Name: 锂离子电池 Li-ion Battery 类型 Type: Lithium ion battery 额定值 Rating: 3.7V, 1500mAh, 5.55Wh 形状 Description: 棱柱形 Prismatic 质量 Mass: Approx. 27.9g	测试实验室名称及联系信息 Name and contact information of the test laboratory: 名称 深圳沃特检验集团股份有限公司 Name: Waltek Testing Group Co., Ltd. 地址 中国广东省东莞市厚街镇莞太路厚 Address: 街段 77 号 No. 77, Houjie Section, Guantai Road, Houjie Town, Dongguan City, Guangdong, China 电话 +86-769-2267 6998 Tel No.: 邮箱 info@waltek.com.cn Email: 网址 www.waltek.com.cn Website:
电池、电池组或生产厂商名称及联系信息 Name and contact information of cell, battery, or product manufacturer: 名称 东莞市金赛尔电池科技有限公司 Name: DONGGUAN GOLDEN CEL BATTERY CO., LTD. 地址 广东省东莞市塘厦镇蛟乙塘银湖工业区 11 号 Address: No.11, Yinhu Industrial Park, JiaoYiTang Village, TangXia Town, DongGuan City, GuangDong Province 电话 0769-82195301 Tel No.: 邮箱 services@cellbattery.com Email: 网址 www.celbattery.com Website:	唯一的试验报告识别号码 A unique test report identification number: WTX25D11315038B 试验报告签发日期 Issue date of the test report: 2026-01-11 参考所使用《试验和标准手册》第 8 修订版 Reference to the revised edition of the Manual of Test and Criteria used: Rev.8 试验结果表 List of tests conducted and results: 高度模拟 Altitude Simulation Pass 温度试验 Thermal Test Pass 振动 Vibration Pass 冲击 Shock Pass 外部短路 External short circuit Pass <input type="checkbox"/> 撞击/ Impact <input checked="" type="checkbox"/> 挤压/Crush Pass 过充电 Overcharge Pass 强制放电 Forced discharge Pass
签字人姓名和职务 Name and Title of Signatory:  秦林伟 Deval Qin / 授权签字人 Designated Reviewer 签发日期 Issue Date: 2026-01-11	