

AUTOMOTIVE TESTER / STROBOSCOPE

PCE-LES 103UV-365



- » **3 UVA high-performance LEDs**
- » **Flash colour: 365 ... 370 nm**
- » **Flash frequency adjustable in FPM and Hz**
- » **Intensity: 202 $\mu\text{W}/\text{cm}^2$ at 30 cm**
- » **Digital pulse width modulation**
- » **Phase shift: - 360 ° ... + 360 °**
- » **Quick adjustment using x2 and \div 2 buttons**
- » **Intuitive control buttons and clear display**

Motion analysis of rotating machines is quick and easy with our Automotive Tester / Stroboscope. The Automotive Tester / Stroboscope is equipped with 3 UVA high-power LEDs, which together generate a light intensity of 202 $\mu\text{W}/\text{cm}^2$ at a distance of 30 cm. With the Automotive Tester / Stroboscope, you can set the flash frequency in both FPM and Hz. It is also small, handy and mains-independent thanks to the rechargeable battery.

The Automotive Tester / Stroboscope is operated intuitively using the 10 buttons, allowing quick adjustments to be made. The phase shift allows the observation point to be moved variably. The pulse width can be used to set the duration and therefore also the intensity of the flash frequency. The display brightness can be selected in the settings menu and the display can also be switched off after a period of inactivity, which extends the battery life. The Automotive Tester / Stroboscope is supplied with a USB-C charging cable in a service bag.

Automotive Tester / Stroboscopes are indispensable tools for monitoring and inspecting production facilities, e.g. in the printing and textile industries. But also for general maintenance and inspection tasks in all industrial sectors. They also enable non-contact speed and vibration measurement: if the flash frequency of the Automotive Tester / Stroboscope matches the movement frequency, the measured object appears stationary.

Specification

Frequency	
Measurement range up to	60 ... 9999,99 FPM
Resolution	0,01 FPM
Accuracy	±0.001 % of the setting or ±1 LSD
Frequency	
Measurement range up to	10000 ... 300000 FPM
Resolution	0,1 FPM
Accuracy	±0.001 % of the setting or ±1 LSD
Frequency	
Measurement range up to	1 ... 5000 Hz
Accuracy	±0.001 % of the setting or ±1 LSD

General technical data	
Display type	LC colour display
Display size	2,8 Inch
Operating time	4,5 h
Operating time additional information	at flash frequency 100 Hz, 1 %, display brightness 70 %
Automatic power-off from...to	2 ... 10 min.
Automatic power-off can be deactivated	Yes
Luminous intensity	405 µW/cm ² @ 20 cm @ 1000 Hz, 1% 202 µW/cm ² @ 30 cm @ 1000 Hz, 1% 74 µW/cm ² @ 50 cm @ 1000 Hz, 1%
Light colour	UV light (365 ... 370 nm)
Phase shift	-360 ... 360 °
Pulse width	0.01 ... 1 % of pulse duration Resolution: 0.01 % 0.01 ° ... 3.60 ° of 360 ° Resolution: 0.01 °
Menu language	Turkish, English, Polish, Spanish, German, Chinese, Russian, French, Italian, Dutch
Protection class (device)	IP52
Power supply	5V DC, 2A
(Rechargeable) battery	1 x 7,4 V internal, Lithium-ion battery
Capacity	2200 mAh
Operating conditions	-20 ... 60 °C, 35 ... 85 % RH
Storage conditions	-20 ... 60 °C, 35 ... 85 % RH
Dimensions (L x W x H)	165 x 90 x 35 mm
Weight	284 g