DATA SHEET

Premium Efficiency Motor: **PEWWE50-18-326TC** **60 Hz**

WorldWide Electric Corporation
1 (800) 808-2131
Worldwideelectric.net

Document Generated: 14-Oct-2024
Document ID:

Customer:

MOTOR INFORMATION

HP	50
RPM	1800
Phase	3
Frequency	60Hz
Voltage	230/460 V
Frame Size	326TC
Enclosure	TEFC
Degree of Protection	IP55
Service Factor	1.25
Poles	4
Full Load Speed	1775
Insulation Class	F
Temp Rise	80˚C
NEMA Code Letter	G
Duty Cycle	S1 / Continuous
Slip	1.40%
NEMA Design	B
Moment of Inertia	6.89 lb.ft.^2
Locked Rotor Time (Hot)	12 seconds
Sound Pressure Level	72 dB(A)
Number of Starts	2 Cold/ 1 Hot
Max Ambient Temperature	40˚C
Max Elevation	1000 m.a.s.l (3300 f.a.s.l)
Mounting	F1
Rotation	Bi-Directional
Area of Classification	Class 1 Division 2 Groups A,B,C,D T3C(160°C)
Inverter Rating	10:1 CT / 20:1 VT PWM Type
Standard	NEMA MG-1
Approvals	CSA-US, CE

ADDITIONAL DATA

F2 Suitable	Yes
Shaft Material	1045 Carbon Steel
Connection Diagram	230 / 460 V - 12 Lead Δ
Approximate Weight	578 lbs.

EFFICIENCY/POWER FACTOR

LOAD	EFF	P. F.
100%	94.5 %	0.86
75%	94.9 %	0.82
50%	94.7 %	0.73

TORQUE

FULL LOAD	LRT	BDT
148 lb.ft.	160 %	260 %

AMPERAGE INFORMATION

	230V	460V
Full Load Amps	115A	57.6A
Locked Rotor Amps	725A	362.5A
No Load Current	42A	21A
Usable at 208V	127A	

BEARING INFORMATION


DE Bearing	6312 C3
ODE Bearing	6311 C3
Grease Type	SKF LGHP 2
DE Regreasing Interval	4000 Hours
ODE Regreasing Interval	4000 Hours

This document is the property of WorldWide Electric Corporation and may not be reproduced without express authorization

MOTOR DRAWING

Premium Efficiency Motor: **PEWWE50-18-326TC**

WorldWide Electric Corporation
1 (800) 808-2131
Worldwideelectric.net



DIMENSION - INCHES

MOUNTING					A	B	C	D	G	J	P	O	T	AB
E	2F1	2F	H	BA										
6.25	10.5	12	0.66	5.25	15.276	14.921	30.967	8	0.984	2.756	15.571	15.913	2.441	13.813

SHAFT & KEY					
S	ES	R	N-W	AH	U
0.5	3.91	1.845	5.25	5	2.125

TERMINAL BOX				
AA	XB	XC	XD	XF
2	2.471	10.826	8.976	11.248

FLANGE					
AJ	AK	BB	BD	BF	BC
11	12.5	0.25	13.78	5/8-11	0.25

This document is the property of WorldWide Electric Corporation and may not be reproduced without express authorization

PERFORMANCE CURVES


Premium Efficiency Motor: **PEWWE50-18-326TC**


WorldWide Electric Corporation
1 (800) 808-2131
Worldwideelectric.net

Document Generated:	14-Oct-2024
Document ID:	

Customer:

Motor Type	PEWWE					
Output Rating (HP)	50		FL Speed	1775		
Full Load Torque	148	lb.ft	LRT (%FLT)	160	460 volt FLA	57.6
Rotor Wk^2	6.89	lb-ft^2	BDT (%FLT)	260	230 volt FLA	115





This document is the property of WorldWide Electric Corporation and may not be reproduced without express authorization.


NAMEPLATE / WIRING

Premium Efficiency Motor: **PEWWE50-18-326TC**

WorldWide Electric Corporation
1 (800) 808-2131
Worldwideelectric.net

Document Generated: 14-Oct-2024 Document ID:	Customer:

SAMPLE NAMEPLATE DATA



Model	PEWWE50-18-326TC						
HP	50	S.F.	1.25	IP	IP55	Encl	TEFC
Frame	326TC	P.F.	0.86	Code	G	Type	
Voltage	230/460 V	Hz	60Hz	Ins Cl	F	Ambient	40°C
Amps	115/57.6	RPM	1775	Design	B	DE Brng	6312 C3
Nom.Eff.	FL 94.5%	3/4	94.9%			ODE Brng	6311 C3
Class 1 Division 2 Groups A,B,C,D T3C(160°C)						Grease type:	SKF LGHP 2

50Hz

50 HP	200/400 V	135/67. A	1475 rpm
		Eff. 92.7%	

This document is the property of WorldWide Electric Corporation and may not be reproduced without express authorization