

Garant**Circular mill, with thread steel, Type: 16/M5****Order data**

Order number	217253 16/M5
GTIN	4062406060060
Item class	21Q

Description**Version:****Extra-slim version** for thread milling.**Note:**The actual groove depth $S_{\max}$ is calculated as follows: $(D-d_1) / 2$.**Technical description**

Thread depth	15 mm
Overhang L_1	15 mm
maximum cutting depth $S_{\max}$	6.5 mm
Internal $\varnothing d_1$	9.5 mm
Thread size M	M5 mm
Shank type	with thread
Overall length L_{tot}	18.5 mm
Through-coolant	yes
for insert type	P16
smallest hole $\varnothing D$	14 - 22 mm

Set of insert screws	219818 (8IP; 1.2 Nm)
Material of milling tool	with thread steel
Tool exchange	PowerCard
Type of product	Circular mills