



TVS-872N-i3-8G (Legacy)

CPU	Intel® Core™ i3 Processor
CPU Architecture	64-bit x86
Graphic Processors	Intel® UHD Graphics 630
Floating Point Unit	Yes
Encryption Engine	Yes (AES-NI)
Hardware-accelerated Transcoding	Yes
System Memory	8 GB SODIMM DDR4 (2 x 4 GB)
Maximum Memory	32 GB (2 x 16 GB)
Memory Slot	2 x SODIMM DDR4
Flash Memory	5GB (Dual boot OS protection)
Drive Bay	8 x 3.5-inch SATA 6Gb/s, 3Gb/s
Drive Compatibility	3.5-inch bays: 3.5-inch SATA hard disk drives 2.5-inch SATA hard disk drives 2.5-inch SATA solid state drives
Hot-swappable	Yes
M.2 Slot	2 x M.2 2280 PCIe Gen3 x2 slots Compatible with NVMe SSD PCIe Gen 3 and above. Please refer to https://www.qnap.com/compatibility/ for compatibility.
SSD Cache Acceleration Support	Yes
GPU pass-through	Yes
Gigabit Ethernet Port (RJ45)	2
5 Gigabit Ethernet Port (5G/2.5G/1G/100M)	1 x 5GbE(5G/2.5G/1G/100M)

Wake on LAN (WOL)	Yes
Jumbo Frame	Yes
PCIe Slot	2 Slot 1: PCIe Gen 3 x16 (CPU) Slot 2: PCIe Gen 3 x4 (PCH)
USB 3.2 Gen 1 port	1
USB 3.2 Gen 2 (10Gbps) Port	2 x Type-C USB 3.2 Gen 2 10Gbps 2 x Type-A USB 3.2 Gen 2 10Gbps
IR Sensor	Yes (QNAP RM-IR004 & MCE)
HDMI™ Output	1, HDMI™ 2.0 (up to 3840 x 2160 @ 60Hz)
Audio Input	1 x 3.5mm microphone input jacks
Audio Output	1 x built-in speaker, 1 x 3.5mm line out jack (for amplifiers or speakers)
Form Factor	Tower
LED Indicators	HDD 1-8, Status, LAN, USB port, M.2 port
LCD Display/ Button	Yes
Buttons	Power, Reset, USB Copy
Dimensions (HxWxD)	7.41 × 12.96 × 11.01 inch
Weight (Net)	15.56 lbs
Weight (Gross)	20.26 lbs
Operating Temperature	0 - 40 °C (32°F - 104°F)
Storage Temperature	-20 - 70°C (-4°F - 158°F)
Relative Humidity	5-95% RH non-condensing, wet bulb: 27°C (80.6°F)
Power Supply Unit	250W, 100-240V
Power Consumption: HDD Sleep Mode	41.47 W
Power Consumption: Operating Mode, Typical	65.03 W Tested fully populated with WD10EFRX hard drives.
Fan	System fan: 2 x 120mm, 12VDC CPU fan: 2 x 60mm blower fan
System Warning	Voice prompts or Buzzer
Kensington Security Slot	Yes
Standard Warranty	2

Max. Number of Concurrent Connections (CIFS) - with Max. Memory	2500
---	------

Note: Use only QNAP memory modules to maintain system performance and stability. For NAS devices with more than one memory slot, use QNAP modules with identical specifications and refer to the hardware user manual to install compatible QNAP memory modules.

Warning: Using unsupported modules may degrade performance, cause errors, or prevent the operating system from starting. QNAP reserves the right to replace partial parts or accessories if the original is no longer available from its manufacturer/supplier. Any replacement would be fully tested and verified to meet strict compatibility and stability guidelines and will deliver identical performance to the original.

The terms HDMI, HDMI High-Definition Multimedia Interface, HDMI trade dress and the HDMI Logos are trademarks or registered trademarks of HDMI Licensing Administrator, Inc.

Product images are for illustrative purposes only and may differ from the actual product. Due to differences in monitors, colors of products may also appear different to those shown on the site.

Designs and specifications are subject to change without notice.