



# Cannabis Hemp

## Water Based Scent Additive for Fog, Haze, Snow & Bubble Juice

### Safety Data Sheet

**Froggy's Fog LLC**  
 302 Rutherford Lane  
 Columbia, TN 38401  
 United States  
 Phone: (615) 469-4906

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

Version: 2023.1  
 Revision Date: 08/16/2023

#### SECTION 1: Identification of the Substance/Mixture and of the Company

##### 1.1. Product Identifier

Product Form : Mixture  
 Product Name : Cannabis Hemp - Water Based Scent Additive for Fog, Haze, Snow & Bubble Juice  
 Product Code : WBS-CANN

##### 1.2. Intended Use of the Product

Use of the Substance/Mixture : Fragrance  
 Recommended Use : Fragrance

##### 1.3. Supplier

**Froggy's Fog LLC**  
 302 Rutherford Lane  
 Columbia, TN 38401  
 1-615-469-4906  
 www.froggysfog.com

##### 1.4. Emergency Telephone Number

Emergency Telephone Number : 1-800-424-9300 Outside USA and Canada +1 703-741-5970 (collect calls accepted)  
 For Chemical Emergency, Spill, Leak, Fire, Exposure, or Accident Call CHEMTREC Day or Night. Within USA and Canada: 1-800-424-9300. Outside USA and Canada: +1 703-741-5970 (collect calls accepted)  
 : IF SWALLOWED CALL YOUR POISON CONTROL CENTER AT 1-800-222-1222

#### SECTION 2: Hazard(s) Identification

##### 2.1. Classification of the Chemical in Accordance with Paragraph (d) of §1910.1200

GHS Hazard Symbols:



**GHS-US Classification:** Hazardous to the aquatic environment – Acute Category 3  
**GHS Signal Word:** Warning  
**GHS Hazard** May cause an allergic skin reaction.; Harmful to aquatic life.

**GHS Precautions:**

- Safety Precautions:** Contaminated work clothing should not be allowed out of the workplace. Avoid release to the environment. Wear protective gloves/protective clothing/eye protection/face protection.
- First Aid Measures (Response):** IF ON SKIN: Wash with plenty of soap and water. If skin irritation or rash occurs: Get medical advice/attention. Wash contaminated clothing before reuse.
- Disposal:** Dispose of contents/container in accordance with local/regional/national/international regulation for hazardous wastes.

**SECTION 3: Composition/Information on Ingredients**

Chemical Name	CAS #	%
Benzenemethanol, .alpha.-methyl-, 1-acetate	93-92-5	10 - 30
2H-1-Benzopyran-2-one	91-64-5	1 – 5
Bicyclo[3.1.1]heptane, 6,6-dimethyl-2-methylene-, (1S,5S)-	18172-67-3	0.1 - 1

The specific chemical identity and/or exact percentage (concentration) of composition has been withheld as a trade secret.

**SECTION 4: First-Aid Measures**

**4.1. Description of First Aid Measures**

- Inhalation : This material does not present a hazard if inhaled. Remove individual to fresh air after an airborne Exposure if any symptoms develop, as a precautionary measure.
- Eyes : Flush eyes with plenty of water for at least 20 minutes retracting eyelids often. Tilt the head to prevent chemical from transferring to the uncontaminated eye. Get immediate medical attention.
- Skin contact : Wash with soap and water.
- Ingestion : No hazard in normal industrial use. Do not induce vomiting. Seek medical attention if symptoms develop. Provide medical care provider with this MSDS.

**4.2. Most Important Symptoms and Effects (Acute)**

No Data Available

**4.3. Most Important Symptoms and Effects (Chronic)**

No Data Available

**4.4. Notes to Doctor**

No additional first aid information available

**SECTION 5: Firefighting Measures**

**5.1. Flammability Summary**

Combustible at elevated temperatures.

## 5.2. Extinguishing Media (Suitable and Unsuitable)

- Extinguishing media : Use alcohol resistant foam, carbon dioxide, dry chemical, or water spray when fighting fires. Water or foam may cause frothing if liquid is burning but it still may be a useful extinguishing agent if carefully applied to the fire. Do not direct a water stream directly into the hot burning liquid.
- Extinguishing media advised against : No data available.

## 5.3. Fire and/or Explosion Hazards

Material may be ignited if preheated to temperatures above the flash point in the presence of a source of ignition.

## 5.4. Firefighters Methods and Protection

Do not enter fire area without proper protection including self-contained breathing apparatus and full protective equipment. Fight fire from a safe distance and a protected location due to the potential of hazardous vapors and decomposition products.

## 5.5. Hazardous Combustion Products

Carbon Oxides

# SECTION 6: Accidental Release Measures

## 6.1. Personal Precautions and Equipment

No health effects expected from the clean-up of this material if contact can be avoided. Follow personal protective equipment recommendations found in Section 8 of this MSDS.

## 6.2. Methods for Clean-Up

No special spill clean-up considerations. Collect and discard in regular trash.

# SECTION 7: Handling and Storage

## 7.1. Handling Technical Measures and Precautions

Mildly irritating material. Avoid unnecessary exposure.

## 7.2. Storage Technical Measures and Conditions

Store in a cool dry place. Isolate from incompatible materials.

## 7.3. Materials to Avoid/Chemical Incompatibility

Strong oxidizing agents. Strong bases. Strong acids.

## SECTION 8: Exposure Controls/Personal Protection

### 8.1. Engineering Measures

No exposure limits exist for the constituents of this product. No engineering controls are likely to be required to maintain operator comfort under normal conditions of use.

### 8.2. Individual Protection Measures/Personal Protective Equipment

<b>Respiratory Protection:</b>
No respiratory protection required under normal conditions of use.
<b>Skin Protection:</b>
Not normally considered a skin hazard. Where use can result in skin contact, practice good personal hygiene. Wash hands and other exposed areas with mild soap and water before eating, drinking, and when leaving work.
<b>Gloves:</b>
No information available

### 8.3. Control Parameters

Chemical Name	ACGIH TLV-TWA	ACGIH STEL	OSHA PEL
No Data Available			

## SECTION 9: Physical and Chemical Properties

Physical State:	Liquid
Color:	Clear
Odor:	Comparable to Standard
Odor Threshold:	ND
pH:	Not Available
Melting Point/Freezing Point:	37°F
Initial Boiling point:	201 – 203°F
Flash Point:	201°F
Evaporation Rate:	Not Available
Flammability (Solid, Gas):	No Data Available
Upper Flammable/Explosive Limit:	Not Available
Lower Flammable/Explosive Limit:	Not Available
Vapor Density:	> 1
Relative Density (Specific Gravity):	0.8795
Solubility in Water:	Soluble in water – No
Octanol/Water Partition Coefficient:	> 6
Decomposition Temperature:	300
Volatiles, % by weight:	15.86
Bulk Density:	7.335

## SECTION 10: Stability and Reactivity

### 10.1. Reactivity

No Data Available.

### 10.2. Chemical Stability

Stable under normal conditions.

### 10.3. Possibility of Hazardous Reactions

No Data Available.

### 10.4. Conditions to Avoid

Temperatures above the high flash point of this combustible material in combination with sparks, open flames, or other sources of ignition. Heat flame sparks.

### 10.5. Materials to Avoid/Chemical Incompatibility

Strong oxidizing agents. Strong bases. Strong acids.

### 10.6. Hazardous Decomposition Products

Carbon Oxides.

## SECTION 11: Toxicological Information

### 11.1. Information on Toxicological Effects

**Most Important Symptoms:** No Data Available

**Chemical Interactions That Change Toxicity:** None Known

**Immediate (Acute) Health Effects by Route of Exposure:**

**Long-Term (Chronic) Health Effects:**

**Carcinogenicity:** None of the substances have been shown to cause cancer in long term animal studies. Not a carcinogen according to NTP, IARC, or OSHA.

**Reproductive toxicity:** No data available to indicate product or any components present at greater than 0.1% may cause birth defects.

**Germ cell mutagenicity:** No data available to indicate product or any components present at greater than 0.1% is mutagenic or genotoxic.

**Component Toxicology Data:**

Chemical Name	CAS Number	LD50/LC50
No data available		

**Has the chemical been classified as a Carcinogen by NTP, IARC or OSHA**

Chemical Name	OSHA Carcinogen	IARC Carcinogen	NTP Carcinogen
No Data Available			

## SECTION 12: Ecological Information

### 12.1. Overview

This material is not expected to be harmful to the ecology.

### 12.2. Mobility in Soil

No Data Available

### 12.3. Persistence

No Data Available

### 12.4. Bioaccumulation

No Data Available

### 12.5. Other Adverse Effects

No Data Available

### 12.6. Ecotoxicity Data

Chemical Name	CAS Number	Aquatic EC50 Crustacea	Aquatic ERC50 Algae	Aquatic LC50 Fish
No Data Available				

## SECTION 13: Disposal Considerations

**Waste Description for Spent Product:** Spent or discarded material is not expected to be a hazardous waste.

**Waste Description for Empty Packaging:** No Data Available

**Disposal Methods:** DO NOT DUMP INTO ANY SEWERS, ON THE GROUND, OR INTO ANY BODY OF WATER. All disposal practices must be in compliance with all Federal, State/Provincial and local laws and regulations. Regulations may vary in different locations. Waste characterizations and compliance with applicable laws are the sole responsibility of the waste generator. As your supplier, we have no control over the management practices or manufacturing processes of parties handling or using this material. The information presented here pertains only to the product when used as intended, according to this MSDS. For unused and uncontaminated product, the preferred options include sending to a licensed and permitted incinerator or other thermal destruction device. Various federal, state or provincial agencies may have specific regulations concerning the transportation, handling, storage, use or disposal of this product which may not be covered in this MSDS. The user shall have to review these regulations to ensure full compliance with all applicable regulations.

## SECTION 14: Transport Information

**US DOT Ground Shipping Description:** Not Restricted  
**IATA Shipping Description:** Not Restricted  
**IMDG Shipping Description:** Not Restricted

## SECTION 15: Regulatory Information

**TSCA Status:** All components in this product are on the TSCA Inventory.  
**California Prop 65:** Does not contain any chemicals listed on California Proposition 65.

Chemical Name	CAS #	Regulation	% Range
N590 Polycyclic aromatic compounds (PACs)	91-64-5	SARA 313	1 - 5

## SECTION 16: Other Information

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations  
Revision date : 8/16/2023

### Disclaimer:

Important: While the descriptions, data and information contained herein are presented in good faith and believed to be accurate, it is provided for your guidance only. Because many factors may affect processing or application/use, we recommend that you perform an assessment to determine the suitability of the product for your particular purpose prior to use. Nothing herein should be interpreted as a recommendation to infringe existing patents or violate any laws or regulations. No warranties of any kind, either expressed or implied, including fitness for a particular purpose are made regarding the product described. We assume NO responsibility for any injuries resulting from misuse or misapplication of this product or that might be sustained because of inhalation, ingestion, absorption or other contact with this product. In no case shall the descriptions, information, or data provided be considered a part of our terms and conditions of sale. Further, the descriptions, data and information furnished hereunder are given gratis. No obligation or liability for the description, data and information given are assumed. All such being given and accepted at your risk.