

BL0925 MST BOLEX 12QT CS

Version 1.0

Revision Date 06/16/2015

Print Date 12/08/2016

SECTION 1. PRODUCT AND COMPANY IDENTIFICATION

Material name : BL0925 MST BOLEX 12QT CS

Material number : 000000000001038799

Manufacturer or supplier's details

Company : Zep Inc.

Address : 1310 Seaboard Industrial Blvd., NW
Atlanta, GA 30318

Telephone : 404-352-1680

Emergency telephone numbers**For SDS Information** : Compliance Services 1-877-428-9937**For a Medical Emergency** : 877-541-2016 Toll Free - All Calls Recorded**For a Transportation Emergency** : CHEMTREC: 800-424-9300 - All Calls Recorded.
In the District of Columbia 202-483-7616**SECTION 2. HAZARDS IDENTIFICATION****Emergency Overview**

Appearance	liquid
Colour	opaque, white
Odour	pungent

GHS ClassificationSkin corrosion : Category 1A
Serious eye damage : Category 1
Specific target organ toxicity - single exposure : Category 3 (Respiratory system)**GHS Label element**

Hazard pictograms :



Signal word : Danger

Hazard statements : H314 Causes severe skin burns and eye damage.
H335 May cause respiratory irritation.Precautionary statements : **Prevention:**
P261 Avoid breathing dust/ fume/ gas/ mist/ vapours/ spray.
P264 Wash skin thoroughly after handling.
P271 Use only outdoors or in a well-ventilated area.
P280 Wear protective gloves/ protective clothing/ eye protection/ face protection.
Response:
P301 + P330 + P331 IF SWALLOWED: Rinse mouth. Do NOT

BL0925 MST BOLEX 12QT CS

Version 1.0

Revision Date 06/16/2015

Print Date 12/08/2016

induce vomiting.

P303 + P361 + P353 IF ON SKIN (or hair): Remove/ Take off immediately all contaminated clothing. Rinse skin with water/ shower.

P304 + P340 + P310 IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing.

Immediately call a POISON CENTER or doctor/ physician.

P305 + P351 + P338 + P310 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Immediately call a POISON CENTER or doctor/ physician.

P363 Wash contaminated clothing before reuse.

Storage:

P403 + P233 Store in a well-ventilated place. Keep container tightly closed.

P405 Store locked up.

Disposal:

P501 Dispose of contents/container in accordance with local regulation.

Potential Health Effects**Carcinogenicity:****IARC**

No component of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.

ACGIH

No component of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by ACGIH.

OSHA

No component of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA.

NTP

No component of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Substance / Mixture : Mixture

Hazardous components

Chemical Name	CAS-No.	Concentration [%]
HYDROCHLORIC ACID	7647-01-0	>= 20 - < 25

SECTION 4. FIRST AID MEASURES

General advice : Move out of dangerous area.
Consult a physician.
Show this safety data sheet to the doctor in attendance.
Do not leave the victim unattended.

If inhaled : If unconscious place in recovery position and seek medical advice.

BL0925 MST BOLEX 12QT CS

Version 1.0

Revision Date 06/16/2015

Print Date 12/08/2016

- If breathed in, move person into fresh air.
If breathing is irregular or stopped, administer artificial respiration.
- In case of skin contact : Wash off immediately with plenty of water for at least 15 minutes.
If on clothes, remove clothes.
Get medical attention if irritation develops and persists.
- In case of eye contact : If in eyes, rinse with water for 15 minutes.
Remove contact lenses.
Protect unharmed eye.
If eye irritation persists, consult a specialist.
- If swallowed : Keep respiratory tract clear.
DO NOT induce vomiting unless directed to do so by a physician or poison control center.
Never give anything by mouth to an unconscious person.
If symptoms persist, call a physician.
-

SECTION 5. FIREFIGHTING MEASURES

- Suitable extinguishing media : Alcohol-resistant foam
Carbon dioxide (CO₂)
Dry chemical
- Unsuitable extinguishing media : High volume water jet
- Specific hazards during firefighting : Do not allow run-off from fire fighting to enter drains or water courses.
- Hazardous combustion products : Chlorine compounds
- Specific extinguishing methods :

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
- Further information : Collect contaminated fire extinguishing water separately. This must not be discharged into drains.
Fire residues and contaminated fire extinguishing water must be disposed of in accordance with local regulations.
- Special protective equipment for firefighters : Wear self-contained breathing apparatus for firefighting if necessary.
-

SECTION 6. ACCIDENTAL RELEASE MEASURES

- Personal precautions, protective equipment and emergency procedures : Use personal protective equipment.
- Environmental precautions : Prevent product from entering drains.
Prevent further leakage or spillage if safe to do so.

BL0925 MST BOLEX 12QT CS

Version 1.0

Revision Date 06/16/2015

Print Date 12/08/2016

If the product contaminates rivers and lakes or drains inform respective authorities.

Methods and materials for containment and cleaning up : Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust).
Keep in suitable, closed containers for disposal.

SECTION 7. HANDLING AND STORAGE

Advice on safe handling : Avoid exposure - obtain special instructions before use.
Avoid contact with skin and eyes.
For personal protection see section 8.
Smoking, eating and drinking should be prohibited in the application area.
Provide sufficient air exchange and/or exhaust in work rooms.
To avoid spills during handling keep bottle on a metal tray.
Dispose of rinse water in accordance with local and national regulations.

Conditions for safe storage : Keep container tightly closed in a dry and well-ventilated place.
Observe label precautions.
Electrical installations / working materials must comply with the technological safety standards.

Materials to avoid : Store and keep away from, reducing agents, bases and alkalies.

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION**Components with workplace control parameters**

Components	CAS-No.	Value type (Form of exposure)	Control parameters / Permissible concentration	Basis
HYDROCHLORIC ACID	7647-01-0	C	2 ppm	ACGIH
		C	5 ppm 7 mg/m ³	NIOSH REL
		C	5 ppm 7 mg/m ³	OSHA Z-1
		C	5 ppm 7 mg/m ³	OSHA P0

Personal protective equipment

Respiratory protection : Use respiratory protection unless adequate local exhaust ventilation is provided or exposure assessment demonstrates that exposures are within recommended exposure guidelines.

Hand protection
Remarks

: The suitability for a specific workplace should be discussed with the producers of the protective gloves.

BL0925 MST BOLEX 12QT CS

Version 1.0

Revision Date 06/16/2015

Print Date 12/08/2016

Eye protection	: Ensure that eyewash stations and safety showers are close to the workstation location. Tightly fitting safety goggles Wear face-shield and protective suit for abnormal processing problems.
Skin and body protection	: impervious clothing Choose body protection according to the amount and concentration of the dangerous substance at the work place.
Hygiene measures	: When using do not eat or drink. When using do not smoke. Wash hands before breaks and at the end of workday.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance	: liquid
Colour	: opaque, white
Odour	: pungent
Odour Threshold	: no data available
pH	: < 1
Melting point/freezing point	: no data available
Boiling point	: no data available
Flash point	: not applicable
Evaporation rate	: no data available
Upper explosion limit	: no data available
Lower explosion limit	: no data available
Vapour pressure	: no data available
Relative vapour density	: 1.112
Density	: no data available
Solubility(ies)	
Water solubility	: soluble
Partition coefficient: n-octanol/water	: no data available
Thermal decomposition	: no data available
Viscosity	
Viscosity, kinematic	: no data available

SECTION 10. STABILITY AND REACTIVITY

BL0925 MST BOLEX 12QT CS

Version 1.0

Revision Date 06/16/2015

Print Date 12/08/2016

Reactivity	: Stable
Chemical stability	: Stable under normal conditions.
Possibility of hazardous reactions	: No decomposition if stored and applied as directed.
Conditions to avoid	: no data available
Incompatible materials	: Alkali metals
Hazardous decomposition products	: No decomposition if stored normally.

SECTION 11. TOXICOLOGICAL INFORMATION**Acute toxicity**

no data available

Skin corrosion/irritation**Product:**

Remarks: Extremely corrosive and destructive to tissue.

Serious eye damage/eye irritation**Product:**

Remarks: May cause irreversible eye damage.

Respiratory or skin sensitisation

no data available

Germ cell mutagenicity

no data available

Carcinogenicity

no data available

Reproductive toxicity

no data available

HYDROCHLORIC ACID:**STOT - single exposure**

no data available

STOT - repeated exposure

no data available

Aspiration toxicity

no data available

Further information**Product:**

BL0925 MST BOLEX 12QT CS

Version 1.0

Revision Date 06/16/2015

Print Date 12/08/2016

Remarks: no data available

SECTION 12. ECOLOGICAL INFORMATION**Ecotoxicity**

no data available

Persistence and degradability

no data available

Bioaccumulative potential**Product:**

Partition coefficient: n-octanol/water : Remarks: no data available

Mobility in soil

no data available

Other adverse effects

no data available

Product:

Regulation 40 CFR Protection of Environment; Part 82 Protection of Stratospheric Ozone - CAA Section 602 Class I Substances

Remarks This product neither contains, nor was manufactured with a Class I or Class II ODS as defined by the U.S. Clean Air Act Section 602 (40 CFR 82, Subpt. A, App.A + B).

Additional ecological information : no data available

SECTION 13. DISPOSAL CONSIDERATIONS**Disposal methods**Waste from residues : Do not dispose of waste into sewer.
Do not contaminate ponds, waterways or ditches with chemical or used container.
Dispose of in accordance with local regulations.Contaminated packaging : Empty remaining contents.
Dispose of as unused product.
Do not re-use empty containers.

BL0925 MST BOLEX 12QT CS

Version 1.0

Revision Date 06/16/2015

Print Date 12/08/2016

SECTION 14. TRANSPORT INFORMATION

Transportation Regulation: 49 CFR (USA):
ORM-D, CONSUMER COMMODITY

Transportation Regulation: IMDG (Vessel):
UN1760, CORROSIVE LIQUID, N.O.S., (HYDROCHLORIC ACID), 8, II - Limited quantity

Transportation Regulation: IATA (Cargo Air):
UN1760, Corrosive liquid, n.o.s., (HYDROCHLORIC ACID), 8, II - Limited quantity

Transportation Regulation: IATA (Passenger Air):
UN1760, Corrosive liquid, n.o.s., (HYDROCHLORIC ACID), 8, II - Limited quantity

Transportation Regulation: TDG (Canada):
UN1760, CORROSIVE LIQUID, N.O.S., (HYDROCHLORIC ACID), 8, II - Limited quantity

SECTION 15. REGULATORY INFORMATION**EPCRA - Emergency Planning and Community Right-to-Know Act****CERCLA Reportable Quantity**

Components	CAS-No.	Component RQ (lbs)	Calculated product RQ (lbs)
HYDROCHLORIC ACID	7647-01-0	5000	*

*: Calculated RQ exceeds reasonably attainable upper limit.

SARA 304 Extremely Hazardous Substances Reportable Quantity

This material does not contain any components with a section 304 EHS RQ.

SARA 311/312 Hazards : Acute Health Hazard

SARA 302 : SARA 302: No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

SARA 313 : SARA 313: This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

California Prop 65 This product does not contain any chemicals known to State of California to cause cancer, birth defects, or any other reproductive harm.

The components of this product are reported in the following inventories:

TSCA On TSCA Inventory
DSL All components of this product are on the Canadian DSL.
AICS On the inventory, or in compliance with the inventory
NZIoC On the inventory, or in compliance with the inventory

BL0925 MST BOLEX 12QT CS

Version 1.0

Revision Date 06/16/2015

Print Date 12/08/2016

PICCS

On the inventory, or in compliance with the inventory

IECSC

On the inventory, or in compliance with the inventory


Inventory Acronym and Validity Area Legend:

AICS (Australia), DSL (Canada), IECSC (China), REACH (European Union), ENCS (Japan), ISHL (Japan), KECI (Korea), NZIoC (New Zealand), PICCS (Philippines), TSCA (USA)

SECTION 16. OTHER INFORMATION

Further information

NFPA:



HMIS III:

HEALTH	3
FLAMMABILITY	0
PHYSICAL HAZARD	0

0 = not significant, 1 = Slight,
2 = Moderate, 3 = High
4 = Extreme, * = Chronic

OSHA GHS Label Information:

Hazard pictograms



Signal word

: **Danger:**

Hazard statements

: Causes severe skin burns and eye damage. May cause respiratory irritation.

Precautionary statements

:

Prevention: Avoid breathing dust/ fume/ gas/ mist/ vapours/ spray. Wash skin thoroughly after handling. Use only outdoors or in a well-ventilated area. Wear protective gloves/ protective clothing/ eye protection/ face protection.

Response: IF SWALLOWED: Rinse mouth. Do NOT induce vomiting. IF ON SKIN (or hair): Remove/ Take off immediately all contaminated clothing. Rinse skin with water/ shower. IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing. Immediately call a POISON CENTER or doctor/ physician. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Immediately call a POISON CENTER or doctor/ physician. Wash contaminated clothing before reuse.

Storage: Store in a well-ventilated place. Keep container tightly closed. Store locked up.

Disposal: Dispose of contents/container in accordance with local regulation.

Version:	1.0
Revision Date:	06/16/2015
Print Date:	12/08/2016

We believe the statements, technical information and recommendations contained herein are reliable, but they are given without warranty or guarantee of any kind. The information in this

BL0925 MST BOLEX 12QT CS

Version 1.0

Revision Date 06/16/2015

Print Date 12/08/2016

document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. Users should make their own investigations to determine the suitability and applicability of the information for their particular purposes. This SDS has been prepared by the Compliance Services organization supporting this manufacturer, supplier or distributor.

Zep Inc. markets products under well recognized and established brand names such as Zep®, Zep Commercial®, Zep Professional®, Enforcer®, National Chemical™, Selig™, Misty®, Next Dimension™, Petro®, i-Chem®, TimeMist®, TimeWick™, MicrobeMax®, Country Vet®, Konk®, Original Bike Spirits®, Blue Coral®, Black Magic®, Rain-X®, Niagara National™, FC Forward Chemicals®, Rexodan®, Mykal™, and a number of private labeled brands.