



P65

Technical Data



Color	Black
Sizes Available	OS
Packaging	Bagged Each
Packed	72 Pair/Case
Case Dimensions (in)	18.86 x 128.50 x 11.81
Case Weight (lbs)	13.23
Country of Origin	Taiwan
Lens	Mirror
Frame Style	Foam-Lined
Lens Color	Silver
Frame Fit	Universal
Lens Coating	Anti-Scratch, Anti-Fog
Bridge	Rubber
Temple	Bayonet, Rubber Tips
Base Curve	8
Certifications	ANSI Z87.1, TAA Compliant

Bouton® Optical Fuselage™

Full Frame Safety Glasses with Black Frame, Foam Padding, Silver Mirror Lens and Anti-Scratch / Anti-Fog Coating

- Flame resistant soft foam padding forms a seal to keep out dust and airborne particles
- Comes with both temples AND elastic headband strap
- Temples and strap snap in or out...easily converts from a safety glass to a dust goggle and back
- Bayonet nylon temples with rubber tips for a secure fit
- Molded nose bridge design to fit the vast majority of users
- 8 Base curve lens
- Meets ANSI Z87.1+
- ⚠ **WARNING:** Reproductive Harm - www.P65Warnings.ca.gov

Applications

- Dusty Work Areas
- Outdoor Work
- Drivers
- Marine
- Drilling Rig

SKU Information

SKU	FRAME COLOR	LENS	LENS COLOR	LENS	UPC	UPC (INNER)	UPC (CASE)
				COATING			
250-50-0420	Black	Clear	Clear	AS/AF	616314062414	01616314062413	02616314062412
250-50-0421	Black	Tinted	Gray	AS/AF	616314062421	01616314062420	02616314062429
250-50-0422	Black	I/O	Clear	AS/AF	616314153310	01616314153319	02616314153318
250-50-0425	Black	Mirror	Silver	AS/AF	616314156564	01616314156563	02616314156562
250-50-0426	Black	Mirror	Blue	AS/AF	616314156571	01616314156570	02616314156579
250-50-0429	Black	Tinted	Amber	AS/AF	616314062438	01616314062437	02616314062436
250-50-0520	Black	Clear	Clear	AS/FL360	616314209543	01616314209542	02616314209541
250-50-0521	Black	Tinted	Gray	AS/FL360	616314209550	01616314209559	02616314209558

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated