ABB BALDOR RELIANCE

Customer information packet

CFSWDM3714T-E

10HP, 1770RPM, 3PH, 60HZ, 215TC, 3756M, TEFC, F
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/5/2026 4:19:19 PM

Specifications

Enclosure	TEFC
Frame	215TC
Frame Material	Stainless Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	10.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	CSA
	CSA EEV
	NEMA PREMIUM
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	26.700 A @ 208.0 V
	25.000 A @ 230.0 V
	12.500 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	92.4 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard

Part Detail

Revision	Q
Type	AC
Mech. spec.	37Q242
Base	
Status	PRD/A
Elec. spec.	37WGS251
Layout	37LYQ242
Eff. date	09-22-2023
CD Diagram	CD0180
Poles	04
Leads	9#14
Proprietary	False
Created date	08-03-2017

Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	12.5 a
Insulation Class	H
Inverter Code	Inverter Ready
KVA Code	K
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3756M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	22.12 IN
Power Factor	81
Product Family	WD All SS Encapsulated
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1770 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None

Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP4427AAA05												
CAT #	CFSWDM3714T-E					**LBS**						
SPEC	37Q242S251G1					**ENCL**	TEFC					
SER #						**CC**	010A	**IP**	69			
HP	10			**MAG CUR**	12.6/6.3							
VOLTS	230/460							**NEMA NOM. EFF**	92.4			
AMPS	25/12.5						**PF**	81				
RATING	40C AMB-CONT											
RPM	1770					**MAX RPM**	2700					
FRAME	215TC	**HZ**	60	**CODE**	K	**CLASS**	H					
SER.F.	1.15	**SF AMP**				**PH**	3	**DES**	B			
DE	6307			**ODE**	6307							
LUBRICATION	POLYREX EM											
ID LOGO	**VPWM**	**CHP**	60	**TO**	90	1.5:1						
ID LOGO	**WK2**	1.38	**CT**	15	**TO**	60	4:1					
ID LOGO	**SL HZ**	1	**VT**	6	**TO**	60	10:1					
										QR		
YR												

AC Induction Motor Performance Data
Record # 62567
Typical performance - not guaranteed values

Winding: 37WGS251-R016	**Type:** 3756M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			10	**Full Load Torque**	29.9 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			25/12.5	**Breakdown Torque**	102 LB-FT
R.P.M.			1770	**Pull-up Torque**	53.6 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	74.2 LB-FT
NEMA Design Code	B	**KVA Code**	K	**Starting Current**	105 A
Service Factor (S.F.)			1.15	**No-load Current**	5.44 A
NEMA Nom. Eff.	92.4	**Power Factor**	81	**Line-line Res. @ 25ºC**	0.799 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	76°C
S.F. Amps				**Temp. Rise @ S.F. Load**	93°C
				Locked-rotor Power Factor	31.7
				Rotor inertia	1.38 LB-FT2

Load Characteristics 460 V, 60 Hz, 10 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	43	65	76	81	83	84	82
Efficiency	88	92.6	93	92.9	92.2	91.5	92.5
Speed	1793	1786	1778	1770	1762	1752	1765
Line amperes	6.18	7.79	10	12.5	15.3	18.3	14.2


ABB Motors and Mechanical Inc.


WINDING # 37WGS251

10 HP 3 PH 60 HZ 1770 RPM 460 V 3756M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=102 PU=53.6 LR=74.2 LRA=105





37LYQ242
717-735 = 19.49
736-744 = 20.68
745-750 = 21.37
751-756 = 22.12
LASER ETCHED WARNING LABEL
LASER ETCHED NAMEPLATE
6.03
.26
3.12
.31 KEY 2.38 LONG
10.18
Ø8.500 8.497
Ø8.97
Ø1.3750 1.3745
6 HOLES Ø.41
.50
5.50
4.50
7.00
8.000
4 DRAIN HOLES W/PLUGS 90° APART (EACH END)
9.24
Ø9.51
45°
45°
TOP OF WARNING LABEL
TOP OF NAMEPLATE
2.00
9.98
5.25
5.19
LEAD HOLE 1.00 N.P.T.
4 HOLES .50-13 UNC ↧1.00 Ø7.25 B.C.
4.25
4.25
7.38
4.75
9.50
.177±.020 (EA. END)
6307
FRONT END DETAIL
SNAP RING BRG. RETAINER
LIP SEAL (EA. END)
AXIAL FACE SEAL (EA. END)
6307
PULLEY END DETAIL
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: ADD DIM TO AXIAL SEAL LOCATION
REV: C
VERSION: 03
REVISED: 07:28:51 07/28/2026
TDR: 000001276312
MODEL NO. 37LYQ242
REF: -
BY: USALMAZ
B
BALDOR - RELIANCE®
STD HORZ 213-5TC TEFC M WD11/12
37LYQ242

CD0180







NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0180

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: D	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\148	REVISED: 10:25:29 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, DV, 9 LEADS, DELTA CONNECTION

SH 1 of 1