

PUMP: 100% CAST IRON CONSTRUCTION

 **EXTENDED LIFETIME WARRANTY**
 **SILENTAIR**

FEATURES

- **PATENTED PRESSURE LUBRICATED PUMP**
Rated 70,000HR Life Expectancy.
- **PATENTED SILENT AIR SYSTEM**
Lowering the decibels by more than 50% - Providing 4 layers of air filtration.
- **PREMIUM INDUSTRIAL MOTORS**
Low 1750 RPM's.
- **POWDER COATED ASME CERTIFIED TANKS**
200 PSI rating
- **MANUAL BALL VALVE TANK DRAIN**
Easy access to drain tank moisture.
- **QUALITY COMPONENTS**
We use B-style belts to ensure smooth operation. Top quality pressure switches, 100% brass valves, ASME certified tank, powder coated 13G Steel with premium grade expanded metal belt guards.
- **ETL CERTIFIED**
Tested to all safety standards.



WITH SILENT AIR TECHNOLOGY

EMAX Compressor 350 series provides all the quality without all the added cost the features can add. EMAX has designed a revolutionary air system like no other! Engineered and manufactured in the USA our patented Silent Air System dissipates compressor intake noise by channeling the intake air through a series of baffle plates. This low-profile system adds 4 levels of air filtration along with making the compressor quiet, reducing noise levels by as much as 50%. Now that's being seen but not heard! Our Industrial Plus series come with standard features and only the best quality components. All backed by the best warranty in the industry.

TECH SPECS

| | ES05V080I1 | ES07V080V1 | ES10V080V1 |
|--------------|-----------------|-----------------|-----------------|
| RUNNING HP | 5 | 7.5 | 10 |
| CFM 100PSI | 19 | 31 | 38 |
| MAX PSI | 175 | 175 | 175 |
| PUMP RPM | 800 | 640 | 800 |
| MOTOR RPM | 1750 | 1750 | 1750 |
| MOTOR PHASE | Single | single | single |
| DIMENSIONS | 42" x 34" x 75" | 38" x 42" x 73" | 38" x 42" x 73" |
| WEIGHT | 625 | 768 | 834 |
| TANK GALLONS | 80 | 80 | 80 |

