

Hand Crank and Motor Driven Reels

Series 30000 - Air/Water/Oil - 1/2", 3/4", 1" I.D.

- Designed for rugged applications requiring long lengths of hose and large storage capacity
- All-bolted unitized construction, full flow swivel and heavy gauge steel frame, spool, and drum ensure longest service life
- Vibration-proof, self-locking fasteners are ideal for industrial use
- Optional lock pin to prevent spool rotation when the reel is not in use, S600874



Removable gooseneck makes hose installation easy.



CA32112 L

Drive Type	Swivel Size	Width of Spool	Motor Voltage/H.P.
A - Air motor	2 - 1/2" (13 mm) I.D.	See "F" Dimension	Blank
B - Bevel crank	3 - 3/4" (19 mm) I.D.	06 - 6" (152 mm)	12D - 12 V DC
C - Hand crank	6 - 1/4" (6 mm) Dual	12 - 12" (305 mm)	4A - 1 1/2 HP air motor
E - Electric motor	7 - 1" (25 mm) I.D.	18 - 18" (457 mm)	
	8 - 1/2" (13 mm) I.D.		
	pressure wash		
Fluid Path Type			Pressure
A - Gooseneck			L - 1000 PSI (69 bar)
H - Heavy duty gooseneck (1" only)			M - 3000 PSI (207 bar)

NOTE: Chart is for reference only. Not all options available in every combination. Reels cannot be ordered by selecting from this chart.

Additional Series 30000 Models

Pressure Wash - Page 23

Welding Gas - Page 35

Garden Reels - Page 24

Welding Cable - Page 37

Hose I.D.	1/4"	3/8"	1/2"	3/4"	1"
	6 mm	10 mm	13 mm	19 mm	25 mm
Hose O.D.	.530"	.710"	.850"	1.188"	1.375"
	13 mm	18 mm	22 mm	30 mm	35 mm
"F" Width	Hose Capacity				
6"	200'	140'	100'	50'	N/A
(152 mm)	61 m	43 m	30 m	15 m	
12"	425'	300'	200'	100'	50'
(305 mm)	130 m	91 m	61 m	(30 m)	(15 m)
18"	625'	450'	325'	175'	100'
(457 mm)	191 m	137 m	(99 m)	(54 m)	(31 m)

E	F	17 3/4" (451 mm)
6 3/8" (162 mm)		
D		20 1/4" (514 mm)
E		11 3/8" (289 mm)
	Ø .531 (4) Places	9" (229 mm)
		12 3/4" (324 mm)

Model without hose & bumper	Shipping Weight	Hose Capacity						Max Pressure	NPT(F) Reel Inlet	NPT(F) Reel Outlet	D		E		F	
	lbs kg	I.D.	O.D.	Length				psi bar	in	in	in mm	in mm	in mm	in mm	in mm	in mm
Manual Hand Crank Hose Reels Maximum Temperature 210 °F (99 °C)																
CA32106 L	40 18	1/2 13	.750 19	100 30			1000 69		1/2	1/2	9 3/4 248	19 3/4 502	6		152	
CA32112 L	46 21	1/2 13	.750 19	200 61			1000 69		1/2	1/2	15 3/4 400	25 3/4 654	12		305	
CA32118 L	51 23	1/2 13	.750 19	325 99			1000 69		1/2	1/2	21 3/4 552	31 3/4 806	18		457	
CA32106 M	42 19	1/2 13	.850 22	100 30			3000 207		1/2	1/2	9 3/4 248	19 3/4 502	6		152	
CA32112 M	46 21	1/2 13	.850 22	200 61			3000 207		1/2	1/2	15 3/4 400	25 3/4 654	12		305	
CA32118 M	52 24	1/2 13	.850 22	325 99			3000 207		1/2	1/2	21 3/4 552	31 3/4 806	18		457	
CA33106 L	41 19	3/4 19	1.075 27	50 15			1000 69		3/4	3/4	9 3/4 248	19 3/4 502	6		152	
CA33112 L	46 21	3/4 19	1.075 27	100 30			1000 69		3/4	3/4	15 3/4 400	25 3/4 654	12		305	
CA33118 L	51 23	3/4 19	1.075 27	175 53			1000 69		3/4	3/4	21 3/4 552	31 3/4 806	18		457	
CA33112 M	47 21	3/4 19	1.188 30	100 30			3000 207		3/4	3/4	15 3/4 400	25 3/4 654	12		305	
CH37118 L*	64 29	1 25	1.375 35	100 30			1000 69		1	1	21 3/4 552	34 1/4 870	18		457	
Electric Motor Driven Hose Reels Maximum Temperature 210 °F (99 °C)																
EA32112 L12D	64 29	1/2 13	.750 19	200 61			1000 69		1/2	1/2	15 3/4 400	23 7/8 606	12		305	
EA32118 L12D	68 31	1/2 13	.750 19	325 99			1000 69		1/2	1/2	21 3/4 552	29 5/8 752	18		457	
EA33106 L12D	63 29	3/4 19	1.075 27	50 15			1000 69		3/4	3/4	9 3/4 248	19 5/8 498	6		152	
EA33112 L12D	68 31	3/4 19	1.075 27	100 30			1000 69		3/4	3/4	15 3/4 400	23 7/8 606	12		305	
EA33118 L12D	68 31	3/4 19	1.075 27	175 53			1000 69		3/4	3/4	21 3/4 552	29 5/8 752	18		457	
EH37118 L12D*	82 37	1 25	1.375 35	100 30			1000 69		1	1	21 3/4 552	31 7/8 787	18		457	
Air Motor Driven Hose Reels Filter, regulator, lubricator required. Maximum Temperature 210 °F (99 °C)																
AA33106 L4A	59 27	3/4 19	1.075 27	50 15			1000 69		3/4	3/4	9 3/4 248	17 1/4 438	6		152	

CAUTION: To prevent drum damage fully extend and pressurize hose and rewind on the reel. *All 1 in. reel models have an 8 in. (203 mm) diameter drum.

Many more reel models available in addition to chart. Refer to reelcraft.com for details.